

DTS26W25-37HD [V001] ✓ ACTIVE

TE Internal #: YDTS26W25-37HDV001
TE Internal Description: PLUG ASSY
Mil-Spec: [D38999/26WJ37HD]
[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Cd (4.9% in Plating) Pb (1.2% in Contact Lead-Copper Alloy) Decamethylcyclopentasiloxane (D5) (5% in Insert subassembly) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-D38999-DTS7N
D38999: Square Flange, 25-37 insert



TE Part # CAT-D38999-DTS16H
Jam Nut: D38999, 25-37 Insert

Customers Also Bought



TE Part #CAT-HST-BSTS
BSTS/BSTS-FR Heat Shrink Tubing



TE Part #ZPF000000000007174
983-0RS 08-98 PN



TE Part #358279-000
382C312-50-01-0



TE Part #ZPF000000000001261
097-0267-16 A1267



TE Part #1616058-6
A703CD (FAA/PMA)=RELAY



TE Part #1617147-5
JMGAP-26P = M39016/17-030P



TE Part #1617807-5
FC-335-SY8= RELAY, 3PST



TE Part #YDTS20Y13-98XNV001
HERM RECP

Documents

Datasheets & Catalog Pages
DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS
English