
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.- .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	LC20–0056–12 / ECO–12–010512	28MAY2012	DM	BJ
	D	LC20–0094–13 / ECO–13–014496	09SEP2013	DM	BJ
	E	LC20–0031–16 / ECO–16–005675	14APR2016	DM	BJ
	F	LC20–0085–16 / ECO–16–011010	21JUL2016	DM	BJ
	G	LC20–0060–19 / ECO–19–010173	29JUN2019	DM	BJ



1. BODY STRENGTH: 10,000 lbs.
   PULLING EYE STRENGTH: 6000 lbs.
2. 1710730–1 WILL BE REPLACED BY 1710730–6 IN THE FUTURE.

40,000 AMPERE RMS, ASYMMETRICAL	25,000 AMPERE RMS, SYMMETRICAL	900 AMPERE RMS	60 HERTZ	200 kV	35 kV AC
MOMENTARY CURRENT	THREE SECOND CURRENT	CONTINUOUS CURRENT ALLOWABLE RATING: (PER ANSI C37–32.3.2.1 2002)	FREQUENCY	BASIC IMPULSE INSULATION LEVEL (BIL)	VOLTAGE
SHORT TIME CURRENT					
RATINGS					

YOKE SIZE IN ILD ASSEMBLY	PART NO.
X–SMALL	1710730–6
XX–LARGE	1710730–5
X–LARGE	1710730–4
LARGE	1710730–3
SMALL	1710730–2
X–SMALL	1710730–1

1710730

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –
FINISH –

DWN D. MURUGIAH 12FEB2010
CHK S. KAMEL 29MAR2010
APVD B. JOHNSON 29MAR2010
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT 0
CUSTOMER DRAWING

TE Connectivity

NAME INLINE DISCONNECT SWITCH ASSEMBLY WITHOUT TAPS, AMPACT, 35 kV, 900 Amp – –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1710730	–

SCALE NTS SHEET 1 OF 1 REV G

1471–9 (1/15)