Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Cc Wu	**Contact Title**	PROD COMPLIANCE ENGINEER
Company Unique ID	-	**Response Date**	2013-07-17	**Contact Email**	cc.wu@te.com		
Contact Phone Number	(86)21-33259321						

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	521347-2	**Amount**	1159.2	**Version**	-	**Identity**	
Manufacturer Item Name		**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	521467-1				1.0	534.5	mg	
Material	2	PA66				1.0	534.5	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	99.0	1.0	529.155	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	5.345	mg	
Sub-Item	1	63559-6				1.0	624.7	mg	
Material	2	Brass				1.0	616.4	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.006164	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0175	1.0	172.69987	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.3082	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.06164	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.3082	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.6164	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	440.726	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.006164	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.06164	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.003082	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.2328	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.06164	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.3082	mg	
Material	2	Tin Plate				1.0	8.3	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	8.2585	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.0332	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0083	mg	