

HEAVY DUTY CONNECTORS

Contents

Introduction	4
General Overview of Heavy Duty Connectors.....	4
TE Heavy Duty Connectors - Applications.....	6
HDC Component Overview.....	8
Selection Guide	9
Terminal Type	13
Inserts	14
HA Series.....	14
HE Series	15
HEE Series	17
HEEE Series.....	18
HVE Series	19
HD Series.....	20
HDD Series.....	22
HQ Series & HSB Series	23
HEAV Series	24
HK & HWK Series	25
Modular Inserts	27
HMN Modular Connectors Overview	27
HMN Series	29
HCM Series	40
Tools and Accessories	44
Contacts	48
Contact - 5A Series.....	48
Contact - 100A Series	49
Contact - DD & EE series.....	48
Contact - MM series.....	49
Contacts - High Mating Cycle Series	50

HPC Series	52
HPC 200A	53
HPC 250A	53
HPC 350A	53
Insert Mounting Elements	54
Coding Pin	55
Hoods and Housings IP65	56
H3A Hoods and Housings.....	56
H8A Thermoplastic and H10A & H16A Metal Hoods and Housings.....	57
H32A Metal Hoods and Housings	58
H6B Metal Hoods and Housings.....	59
H10B Metal Hoods and Housings	61
H16B Metal Hoods and Housings	63
H24B Metal Hoods and Housings	65
H32B with 2 Levers on the Hoods and Housings	67
H48B Metal Hoods and Housings	68
EMC Hoods and Housings	69
HB (IP65) Series Central lever locking.....	70
Hoods and Housings IP68	71
H3APR (IP68) Hoods and Housings	71
HBPR (IP68) Hoods and Housings	72
Cable Glands	76
Metal Cable Glands - Brass Nicked-plated.....	76
Nylon Cable Glands - Nylon Sealing Insert	77
Metal Cable Glands - Multiple Sealing Insert.....	79
Special Sealing Insert Glands	80
Metal Glands with Multiple Seal	81
Metal Clamp Glands with Multiple Seal	82
Metal Clamp Glands	82
Metal Lock Nuts.....	83
Metal Increases.....	84
Inside and Outside Thread Adapter	85

TE Connectivity's Heavy Duty Connectors

General Overview of Heavy Duty Connectors

Introduction

General Overview of Heavy Duty Connectors

Heavy Duty Connectors (HDC) are industrial connectors designed to transmit power, data and signal in very tough conditions. In environments with vibrations, risk of dust, temperature challenges and mechanical impact, TE Connectivity (TE)'s HDC connectors provide a reliable solution with solid aluminum or thermoplastic hoods and housings with protection degree from IP65 up to IP69k. Approved according to EN/IEC 61984 standard, TE's HDC connectors range from 1A to 650A, and are available with up to 288 contacts.

HDCs can satisfy electric and signal connection requirements of different fields and different situations. For customer's special requirement, we can provide customized design.

Please contact us.

KEY BENEFITS

- **Robustness:** designed to deliver reliable performance under the demanding operating and environmental conditions
- **Maximum flexibility:** multiple options to meet applications more accurately
- **Design freedom:** flexible designs so customers can choose/create a DIY interface for their equipment
- **Sustainability:** The industry-standardized interface and TE's global footprint help to reduce customer's supply chain risks

SPECIFICATIONS


- EN 60664-1
- EN 61984

KEY FEATURES

- Multiple insert families with up to 216 pins (standard) and up to 288 pins (HDC Dynamic) in a connector
- Space-saving HMN modular system - helping enable various power, signal, and data combinations in a single connector
- High-density solutions in HDC Dynamic Connector with up to 48 pins in one modular insert
- Reduced total cost using stamped and formed contacts in HDC Dynamic Connector modular system
- Lightweight and compact thermoplastic connectors are available
- TIC-LOQ Connector latest self-locking technology design allows easy installation
- High current / high mating cycle solution

PRODUCT CERTIFICATIONS





TE Connectivity's Heavy Duty Connectors

HDC Application Introduction

Introduction

TE Heavy Duty Connectors – Applications



BESS

TE provides high power, high safety, temperature sensor monitor solution in residential / commercial / substation BESS application.

- **HPC series**
 - Power transfer range: 1500V 350A/250A/200A
 - Single pole with black and orange version
 - IP67 protection & UL 4128 certification/TUV PPP 51090B
 - NTC (Negative Temperature Coefficient) temperature sensor optional
- **HMN series**
 - Modular design
 - Wide rating range 5A - 250A
 - Integrated solution to transfer power, signal and data
- **Stacked hybrid series**
 - 70A, 120A optional
 - Hybrid all-in-one structure
 - Supports miniaturization

TE provides flexibility, high mating, high density and easy installation solution in robotics application

- **HMN series**
 - Modular design
 - Wide rating range 5A - 250A
 - Integrated solution to transfer power, signal and data
- **HD/HDD/HEEE/HQ/HK series**
 - High density solution
 - Space saving with compact design
- **TIC-LOQ Connector series**
 - Mate in 2 seconds via automatic locking
 - Easy mating in narrow space
 - One hand operation
- **AGV charging series**
 - High mating cycles (approximately 100,000 cycles)
 - Space saving with hybrid system
 - Low temperature rise aid charging efficiency
- **EMC Version Hoods and Housings**
 - 360° EMI protection
 - High corrosion resistance (500+ hours salt spray)



ROBOTICS

TE Connectivity's Heavy Duty Connectors

HDC Application Introduction

TE Heavy Duty Connectors – Applications



DATA CENTER

TE provide high reliability, high conduction performance, plastic enclosure solution with IP65 protection in Data Center application.

- Plastic enclosure series
 - High strength engineering plastics
 - Power transfer 40A & 70A with 3 to 7 pin
 - Cable to Cable / Cable to Panel
 - Easy installation with HMN & HQ insert

TE provides complete portfolio solution that can easily satisfy the various connection and space requirement in machinery application.

- HMN series
 - Modular design
 - Wide rating range 5A - 250A
 - Integrated solution to transfer power, signal and data
- HE/HA/HD series
 - Wide range of different versions regarding Pin quantities, connector size, capability for current and voltage requirements
 - Wide range of contacts available with different plating
 - Hoods and Housings with coating or EMC protection to fit various solutions requirements



MACHINERY

TE Connectivity's Heavy Duty Connectors

HDC Component Overview

Introduction

HDC Components Overview



HOODS & HOUSINGS

Extremely impact-resistant and robust surface due to powder coating to support the usage in harsh environment, available in many versions:

- Protection degrees IP65, IP67, IP68 and IP69k
- Standard, pressure-tight, EMC and corrosion resistant variants
- Anti-corrosion series with excellent protection against corrosion and environmental influences due to hard anodic oxidation layer (hard coating):
 - 500H salt spray test resistance (BPR/HCM)
 - 1000H salt spray test resistance (HIP-K)
- Available in standard and high construction version

CONTACT SYSTEMS

- 5A - 650A
- Crimp contacts: highest contact density, special tools necessary, vibration proof, gas-tight termination, suitable for termination with crimping machines
- Screw termination: no special tools necessary
- Spring clamp: no special tools necessary, vibration proof
- S&F(Stamping & Formed) contacts: Cost competitive, automation crimping

INSERT

- Certified approval according to TÜV, UL as well as CSA
- Flame-retardant materials according to UL94-V0
- Available for screw, crimp, cage clamp termination and S&F contacts
- Combination inserts for signal and power contacts in one insert - HK/HWK series, HMN modular system
- Up to 216 pins in one connector



HMN MODULAR SYSTEM



- High flexibility and possibility of customization
- Combination of different technologies within one connector: Power, Signal, Pneumatic, RJ45, D-Sub, USB, Quint
- Current up to 250A
- Voltage up to 1000V
- One-piece frame enabling tool less assembly
- Male and female in 1 frame possible
- HMN docking frame enables Blind mating


TE Connectivity's Heavy Duty Connectors

Selection Guide

SELECTION GUIDE

When selecting heavy duty connector, we need to choose as following:

Bulkhead Mounting Type	Surface Mounting Type
 <ul style="list-style-type: none">• Cable gland• Hood• Male contacts• Male insert• Female insert• Female contacts• Bulkhead mounting Housings	 <ul style="list-style-type: none">• Cable gland• Hood• Male contacts• Male insert• Female insert• Female contacts• Surface mounting Housings
(I) Side entry (II) Top entry	(III) Side entry (IV) Top entry

Cable to Cable Type
 <ul style="list-style-type: none">• Cable gland• Hood• Male contacts• Male insert• Female insert• Female contacts• Cable to cable coupling
(V) Side entry (VI) Top entry

TE Connectivity's Heavy Duty Connectors

Selection Guide

Selection Guide

Selection Guide

Insert	Type	Poles	Current	Voltage	Terminal	Contacts	Hoods/Housings
HA	HA-003	3+PE	10A	250V	Screw terminal	-	H3A
	HA-004	4+PE	10A	250V	Screw terminal	-	H3A
	HA-010	10+PE	16A	250V	Screw terminal	CEM/F(16A)	H10A
	HA-016	16+PE	16A	250V	Crimp terminal	DEM/F(16A)	H16A
	HA-003-S	3+PE	10A	400V	Spring terminal		H3A
	HA-004-S	4+PE	10A	400V	Spring terminal		H3A
H1A	H1A-012	12	6.5A	50V	Crimp terminal	CAM/F&DAM/F(5A)	H1A Adapter
HE	HE-006	6+PE	16A	500V	Screw terminal Crimp terminal Spring terminal Double spring	CEM/F(16A) DEM/F(16A)	H6B
	HE-010	10+PE	16A	500V			H10B
	HE-016	16+PE	16A	500V			H16B
	HE-024	24+PE	16A	500V			H24B
	HE-032	32+PE	16A	500V			H32B
	HE-048	48+PE	16A	500V			H48B
HEE	HEE-010	10+PE	16A	500V	Crimp terminal	CEM/F(16A) DEM/F(16A)	H6B
	HEE-018	18+PE	16A	500V			H10B
	HEE-032	32+PE	16A	500V			H16B
	HEE-046	46+PE	16A	500V			H24B
	HEE-064	64+PE	16A	500V			H32B
	HEE-092	92+PE	16A	500V			H48B
HEEE	HEEE-020	20+PE	16A	400V	Crimp terminal	CEM/F(16A)	H6B
	HEEE-032	32+PE	16A	400V		DEM/F(16A)	H10B
	HEEE-040	40+PE	16A	500V			H16B
	HEEE-048	48+PE	16A	400V			H16B
	HEEE-064	64+PE	16A	500V			H24B
	HEEE-072	72+PE	16A	400V			H24B
	HEEE-080	80+PE	16A	500V			H32B
	HEEE-096	96+PE	16A	400V			H32B
	HEEE-128	128+PE	16A	500V			H48B
	HEEE-144	144+PE	16A	400V			H48B
HVE	HVEC-010	10+PE+2	16A	830V	Crimp terminal	CEM/F(16A) DEM/F(16A)	H24B
HD	HD-007	7+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H3A
	HD-008	8	10A	50V			H3A
	HD-015	15+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H10A
	HD-025	25+PE	10A	250V			H16A
	HD-040	40+PE	10A	250V			H16B
	HD-050	50+PE	10A	250V			H32A
	HD-064	64+PE	10A	250V			H24B
	HD-080	80+PE	10A	250V			H32B
	HD-128	128+PE	10A	250V			H48B

TE Connectivity's Heavy Duty Connectors

Selection Guide

Selection Guide

Insert	Type	Poles	Current	Voltage	Terminal	Contacts	Hoods/Housings
HDD	HDD-016	16+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H6B
	HDD-024	24+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H6B
	HDD-042	42+PE	10A	250V	Rolled contacts	CJM/F(10A)	H10B
	HDD-072	72+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H16B
	HDD-108	108+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H24B
	HDD-144	144+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H32B
	HDD-216	216+PE	10A	250V	Crimp terminal	CDM/F(10A) DDM/F(10A)	H48B
HSB	HSB-006	HSB-006	35A	690V	Screw terminal	-	H16B
	HSB-012	HSB-012	35A	690V	Screw terminal	-	H32B
HEAV	HEAV-006	6+PE	16A	500V	Spring terminal	-	H6B
	HEAV-010	10+PE	16A	500V			H10B
	HEAV-016	16+PE	16A	500V			H16B
	HEAV-024	24+PE	16A	500V			H24B
	HEAV-032	32+PE	16A	500V			H32B
	HEAV-048	48+PE	16A	500V			H48B
HK&HWK	HK-4/0	4+PE	80A	690V	Screw terminal	-	H16B
	HK-4/2	4/2+PE	80/16A	690/400V	Screw terminal	-	H16B
	HK-4/8	4/8+PE	80/16A	400/400V	Screw terminal	-	H24B
	HK-6/36	6/36+PE	40/10A	690/160V	Crimp terminal	CMM/F(40A) DMM/F(40A) CDM/F(10A) DDM/F(10A)	H16B
	HK-8/24	8/24+PE	16/10A	230/400/160V	Crimp terminal	CEM/F&DEM/F(16A) CDM/F&DDM/F(10A)	H10B
	HK-12/2	12/2+PE	40/10A	690V/250V	Crimp terminal	CMM/F&DMM/F(40A) CDM/F&DDM/F(10A)	H16B
	HWK6/6	6/6+PE	40/16A	690/400V	Screw terminal	-	H16B
	HWK3/3/6	3/3/6+PE	100/40/16A	690/400/250V	Screw terminal	-	H24B
	HK-HDW3/1/ 1-23/16/47	23/16/47+PE	11/3.7/2.2A	400/300/32V	Stamping terminal	HD1/HD3 TAB/RECEPTACLE CONTACT	H10B (short rib/one rib)
	HK2/4-006	2/4	80/10A	250/60V	Crimp terminal	HSM/F(80A) HEM/F(10A)	N/A
HQ	HQ-002	2+PE	40A	400V	Crimp terminal	CMM/F&DMM/F(40A)	H3A
	HQ-002-P	2+PE	40A	830V	Crimp terminal	CMM/F&DMM/F(40A)	H3A
	HQ-003	3+PE	40A	400V	Crimp terminal	CMM/F&DMM/F(40A)	H3A
	HQ-003-P	3+PE	40A	830V	Crimp terminal	CMM/F&DMM/F(40A)	H3A
	HQ-005	5+PE	16A	400V	Crimp terminal	CEM/F&DEM/F(16A)	H3A
	HQ-007	7+PE	10A	400V	Crimp terminal	CDM/F&DDM/F(10A)	H3A
	HQ-008	8+PE	16A	500V	Crimp terminal	CEM/F&DEM/F(16A)	H8A
	HQ-012	12+PE	10A	400V	Crimp terminal	CDM/F&DDM/F(10A)	H3A
	HQ-017	17+PE	10A	250V	Crimp terminal	CDM/F&DDM/F(10A)	H8A
	HQ-021	21+PE	6.5A	50V AC/120V DC	Crimp terminal	CAM/F&DAM/F(5A)	H3A
	HQ4/2	4/2	40/10A	690V/250V	Crimp terminal	CMM/F&DMM/F(40A) CDM/F&DDM/F(10A)	H8A
	HQ-D-032	32	2.2V	32V	Crimp terminal	HD1 TAB/RECEPTACLE CONTACT	H3A
	HQ-4/4/6	4/4/6+PE	20/10/1.2A	600/250/30V	Crimp terminal	CDM/F(10A) DDM/F(10A); CEM/F(20A) DEM/F(20A) ETH-CP/CS-0.6(1.2A)	H3A
	BPSC	BPSC-12/2/4	12/2/4	70/20/5A	1000/400/25V	Crimp terminal	MCSM10-12 SCSF10-12/(70A); MCEM-4.0 SCEF2.5-4.0/(20A); MDAM-0.5 SDAF0.5-0.75(5A)

Selection Guide

TE Connectivity's Heavy Duty Connectors

Selection Guide

Selection Guide

Insert	Type	Poles	Current	Voltage	Terminal	Contacts	Frame
HMN	HMN-001	1	200A/250A	1000V	Crimp terminal	CHM/F&DHM/F(200A/250A)	H10A-T1 H6BN-T2 H10BN-T3 H16BN-T4 H24BN-T6
	HMN-D2	2	100A	1000V	Crimp terminal	CNM/F&DNM/F(100A)	
	HMN-002	2	70A/85A	1000V	Crimp terminal	CSM/F&DSM/F(70A/85A)	
	HMN-003	3	40A	690V	Crimp terminal	CMM/F&DMM/F(40A)	
	HMN-004	4	40A	830V	Crimp terminal	CMM/F&DMM/F(40A)	
	HMN-005	5	16A	400V	Spring terminal	-	
	HMN-006	6	16A	500V	Crimp terminal	CEM/F&DEM/F(16A)	
	HMN-006-P	6	16A	830V	Crimp terminal	CEM/F&DEM/F(16A)	
	HMN-008	8	16A	400V	Crimp terminal	CEM/F&DEM/F(16A)	
	HMN-012	12	10A	250V	Crimp terminal	CDM/F&DDM/F(10A)	
	HMN-017	17	10A	160V	Crimp terminal	CDM/F&DDM/F(10A)	
	HMN-020	20	16A	500V	Crimp terminal	CEM/F&DEM/F(16A)	
	HMN-025	25	5A	50V	Crimp terminal	CAM/F&DAM/F(5A)	
	HMN-009	9	5A	50V	Crimp terminal	CAM/F&DAM/F(5A)	
	HMN-RJ45	1	1A	50V	RJ45	-	
	HMN-USB	1	-	-	USB	-	
	HMN-PA2	2	-	-	Pneumatic contacts	-	
	HMN-PA3	3	-	-	Pneumatic contacts	-	
	HMN-Q1	2	16A/10A	50V	Shielding	Quintax-001	
	HMN-Q2	2	10A	50V	Shielding	Quintax-004	
HMN-Q3	2	5A	50V	Shielding	Quintax-008		
HMN-DM	-	-	-	-	-		
HMN-3/4	3(power)+ 4(signal)	40A(power)+ 10A(signal)	830V	Crimp terminal	CMM/F&DMM/F(40A)-power CDM/F&DDM/F(10A)-signal		
HMN-D3-2/6	3	1.2A	30V	Crimp terminal	Male: FOR 210 DATE: 40.A722.00 + 61.253.11; FOR 606 DATE: 40.A703.00 + 61.252.11) Female: FOR 210 DATE: 40.A711.00 + 60.279.11; FOR 606 DATE: 40.A702.00 + 60.278.11)		
HMN-RJ45 CAT6A	1	1A	50V	RJ45(CAT6A)	-		
HMN-HD1-32	32	2.2A	32V	Stamping terminal	HD1 TAB/RECEPTACLE CONTACT		

Insert	Type	Module units					Hoods/Housings
Frame	H10A-T1	1					H10A
	H6BN-T2	2					H6B
	H10BN-T3	3					H10B
	H16BN-T4	4					H16B
	H24BN-T6	6					H24B

Insert	Type	Poles	Current	Voltage	Terminal	Contacts	Frame
HCM	HCM250	1	250A	2000V	Crimp terminal	HCM250-MC/FC	H16BRP-2P-250 H24BPR-4P-250
	HCM350	1	350A	2000V	Crimp terminal	HCM350-MC/FC	H6BPR-1P-350 H16BPR-2P-350 H24BPR-3P-350 H32BRP-4P-350
	HCM650	1	650A	4000V	Crimp terminal	HCM650-MC/FC	H6BPR-1P-650 H24BPR-2P-650 H24BPR-3P-650

Insert	Type	Module units					Hoods/Housings
Frame	H16BRP-2P-250	2					H16BRP
	H24BPR-4P-250	4					H24BRP
	H6BPR-1P-350	1					H6BRP
	H16BPR-2P-350	2					H16BRP
	H24BPR-3P-350	3					H24BRP
	H32BRP-4P-350	4					H32BRP
	H6BPR-1P-650	1					H6BRP
	H24BPR-2P-650	2					H24BRP
H24BPR-3P-650	3					H24BRP	

TE Connectivity's Heavy Duty Connectors

Terminal Type

Terminal Type

Screw terminal

HA series
HE series
HSB series
HK series
HWK series



Inserts	Max.wire gauge		Stripping length L (mm)
	mm ²	AWG	
HA-003, HA-004	2.5	14	4.5
HE, HA	2.5	14	7.5
HE	4	12	7.5
HSB	6	10	11.5
HK, HWK	16	5	14

Crimp terminal

HD series
HDD series



Inserts	Max.wire gauge		Stripping length L (mm)
	mm ²	AWG	HDD/HD
HD HDD	0.5	20	8
	0.75	18	8
	1	18	8
	1.5	16	8
	2.5	14	8
4	12	6.2	

HE, HEE series
HEEE series



Inserts	Max.wire gauge		Stripping length L (mm)
	mm ²	AWG	
HE HEE HEEE	0.5	20	7.5
	0.75	18	7.5
	1	18	7.5
	1.5	16	7.5
	2.5	14	7.5
4	12	7.5	

Spring Terminal

HA series
HE series



Inserts	Max.wire gauge		Stripping length L (mm)
	mm ²	AWG	
HA, HE	0.14-2.5	26-14	11

Recommended tightening torque and size of screw driver

Size of screw	Connector type	Tightening torque [Nm]	Tightening torque [lbft]	Recommended size of screw driver
M3	Screw terminal HA-003/HA-004/HQ-005	0.25	0.2	0.4x2.5
M3	Screw terminal HA-010, HA-016	0.5	0.4	0.5x3.5 or ±size 1
M3	Screw terminal HE, HVAE fixing screws of all kinds, guiding pins and bushes	0.5	0.4	0.5x3.5
M4	Ground terminal HA, HE, HD, HDD	1.2	0.9	0.5x3.5 or ±size 1+2
M4	Terminal blocks HSB	1.2	0.9	0.8x4.5
M5	Ground terminal HSB	2	1.4	0.8x4.5 - 1.2x8.0









TE Connectivity's Heavy Duty Connectors




Inserts



HA Series

HA SERIES INSERTS CAN MATCH THE HA SERIES HOODS AND HOUSINGS.

Inserts

3+ 			3+ 			4+ 			4+ 		
Screw Terminal			Spring Terminal			Screw Terminal			Spring Terminal		
											
Type	PN		Type	PN		Type	PN		Type	PN	
Male (M)	HA-003-M	T2010032101-000	Male (M)	HA-003-MS	T2010033101-000	Male (M)	HA-004-M	T2010042101-000	Male (M)	HA-004-MS	T2010043101-000
Female (F)	HA-003-F	T2010032201-000	Female (F)	HA-003-FS	T2010033201-000	Female (F)	HA-004-F	T2010042201-000	Female (F)	HA-004-FS	T2010043201-000
Tech Data	Rated current: 10A Rated voltage: 250V Terminal: Screw terminal 2 Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 400V Terminal: Spring terminal 2 Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Terminal: Screw terminal 2 Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 400V Terminal: Spring terminal 2 Wiregauge: 0.5-2.5mm ²	
Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56	

10			16			16		
Screw Terminal			Screw Terminal			Crimp Terminal (Order crimp contacts separately)		
								
Type	PN		Type	PN		Type	PN	
Male (M)	HA-010-M	T2010102101-000	Male (M)	HA-016-M	T2010162101-000	Male (M)	HA-016-MC	T2010164101-000
Female (F)	HA-010-F	T2010102201-000	Female (F)	HA-016-F	T2010162201-000	Female (F)	HA-016-FC	T2010164201-000
Tech Data	Rated current: 16A Rated voltage: 250V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 250V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 250V Terminal: Crimp terminal Wiregauge: 0.14-4.0mm ²	
Hoods & Housings	For H10A series see page 57		Hoods & Housings	For H16A series see page 57		Hoods & Housings	For H16A series see page 57	

32			32		
Screw Terminal			Crimp Terminal (Order crimp contacts separately)		
					
Type	PN		Type	PN	
Male (M)	HA-016-M HA-016-M 17-32	T2010162101-000 T2010322101-000	Male (M)	HA-016-MC HA-016-MC 17-32	T2010164101-000 T2010324101-000
Female (F)	HA-016-F HA-016-F 17-32	T2010162201-000 T2010322201-000	Female (F)	HA-016-FC HA-016-FC 17-32	T2010164201-000 T2010324201-000
Tech Data	Rated current: 16A Rated voltage: 250V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 250V Terminal: Crimp terminal Wiregauge: 0.14-4.0mm ²	
Hoods & Housings	For H32A series see page 58		Hoods & Housings	For H32A series see page 58	

TE Connectivity's Heavy Duty Connectors

Inserts

HE Series

HE SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

6			6			6			6		
Screw Terminal			Spring Terminal			Crimp Terminal (Order crimp contacts separately)			Spring Terminal (Two terminals per contact)		
	Type	PN		Type	PN		Type	PN		Type	PN
Male (M)	HE-006-M	T2040062101-000	Male (M)	HE-006-MS	T2040063101-000	Male (M)	HE-006-MC	T2040064101-000	Male (M)	HE-006-MSS	T2040065101-000
Female (F)	HE-006-F	T2040062201-000	Female (F)	HE-006-FS	T2040063201-000	Female (F)	HE-006-FC	T2040064201-000	Female (F)	HE-006-FSS	T2040065201-000
Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Screw terminal 2 Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal 2 Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Crimp terminal 2 Wiregauge: 0.14-4mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal 2 Wiregauge: 0.5-2.5mm ²	
Hoods & Housings	For H6B series see page 59		Hoods & Housings	For H6B series see page 59		Hoods & Housings	For H6B series see page 59		Hoods & Housings	For H6B series see page 59	

10			10			10			10		
Screw Terminal			Spring Terminal			Crimp Terminal (Order crimp contacts separately)			Spring Terminal (Two terminals per contact)		
	Type	PN		Type	PN		Type	PN		Type	PN
Male (M)	HE-010-M	T2040102101-000	Male (M)	HE-010-MS	T2040103101-000	Male (M)	HE-010-MC	T2040104101-000	Male (M)	HE-010-MSS	T2040105101-000
Female (F)	HE-010-F	T2040102201-000	Female (F)	HE-010-FS	T2040103201-000	Female (F)	HE-010-FC	T2040104201-000	Female (F)	HE-010-FSS	T2040105201-000
Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Crimp terminal Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²	
Hoods & Housings	For H10B series see page 61		Hoods & Housings	For H10B series see page 61		Hoods & Housings	For H10B series see page 61		Hoods & Housings	For H10B series see page 61	

16			16			16			16			16		
Screw Terminal			Screw Terminal (gold plating)			Spring Terminal			Crimp Terminal (Order crimp contacts separately)			Spring Terminal (Two terminals per contact)		
	Type	PN		Type	PN		Type	PN		Type	PN		Type	PN
Male (M)	HE-016-M	T2040162101-000	Male (M)	HE-016-MG	T2040162111-000	Male (M)	HE-016-MS	T2040163101-000	Male (M)	HE-016-MC	T2040164101-000	Male (M)	HE-016-MSS	T2040165101-000
Female (F)	HE-016-F	T2040162201-000	Female (F)	HE-016-FG	T2040162211-000	Female (F)	HE-016-FS	T2040163201-000	Female (F)	HE-016-FC	T2040164201-000	Female (F)	HE-016-FSS	T2040165201-000
Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Crimp terminal Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²	
Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H16B series see page 63-64	

Inserts





TE Connectivity's Heavy Duty Connectors





Inserts





HE Series

HE SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

Inserts

32			32			32			32		
Screw Terminal			Spring Terminal			Crimp Terminal (Order crimp contacts separately)			Spring Terminal (Two terminals per contact)		
											
Type	Type	PN	Type	Type	PN	Type	Type	PN	Type	Type	PN
Male (M)	HE-016-M HE-016-M 17-32	T2040162101-000 T2040322101-000	Male (M)	HE-016-MS HE-016-MS 17-32	T2040163101-000 T2040323101-000	Male (M)	HE-016-MC HE-016-MC 17-32	T2040164101-000 T2040324101-000	Male (M)	HE-016-MSS HE-016-MSS 17-32	T2040165101-000 T2040325101-000
Female (F)	HE-016-F HE-016-F 17-32	T2040162201-000 T2040322201-000	Female (F)	HE-016-FS HE-016-FS 17-32	T2040163201-000 T2040323201-000	Female (F)	HE-016-FC HE-016-FC 17-32	T2040164201-000 T2040324201-000	Female (F)	HE-016-FSS HE-016-FSS 17-32	T2040165201-000 T2040325201-000
Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Crimp terminal Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²	
Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H32B series see page 67	

24			24			24			24		
Screw Terminal			Spring Terminal			Crimp Terminal (Order crimp contacts separately)			Spring Terminal (Two terminals per contact)		
											
Type	Type	PN	Type	Type	PN	Type	Type	PN	Type	Type	PN
Male (M)	HE-024-M HE-024-M	T2040242101-000 T2040242101-000	Male (M)	HE-024-MS HE-024-MS	T2040243101-000 T2040243101-000	Male (M)	HE-024-MC HE-024-MC	T2040244101-000 T2040244101-000	Male (M)	HE-024-MSS HE-024-MSS	T2040245101-000 T2040245101-000
Female (F)	HE-024-F HE-024-F	T2040242201-000 T2040242201-000	Female (F)	HE-024-FS HE-024-FS	T2040243201-000 T2040243201-000	Female (F)	HE-024-FC HE-024-FC	T2040244201-000 T2040244201-000	Female (F)	HE-024-FSS HE-024-FSS	T2040245201-000 T2040245201-000
Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Crimp terminal Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²	
Hoods & Housings	For H24B series see page 65-66		Hoods & Housings	For H24B series see page 65-66		Hoods & Housings	For H24B series see page 65-66		Hoods & Housings	For H24B series see page 65-66	





48			48			48			48		
Screw Terminal			Spring Terminal			Crimp Terminal (Order crimp contacts separately)			Spring Terminal (Two terminals per contact)		
											
Type	Type	PN	Type	Type	PN	Type	Type	PN	Type	Type	PN
Male (M)	HE-024-M HE-024-M 25-48	T2040242101-000 T2040482101-000	Male (M)	HE-024-MS HE-024-MS 25-48	T2040243101-000 T2040483101-000	Male (M)	HE-024-MC HE-024-MC 25-48	T2040244101-000 T2040484101-000	Male (M)	HE-024-MSS HE-024-MSS 25-48	T2040245101-000 T2040485101-000
Female (F)	HE-024-F HE-024-F 25-48	T2040242201-000 T2040482201-000	Female (F)	HE-024-FS HE-024-FS 25-48	T2040243201-000 T2040483201-000	Female (F)	HE-024-FC HE-024-FC 25-48	T2040244201-000 T2040484201-000	Female (F)	HE-024-FSS HE-024-FSS 25-48	T2040245201-000 T2040485201-000
Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Screw terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Crimp terminal Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Terminal: Spring terminal Wiregauge: 0.5-2.5mm ²	
Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H32B series see page 67	




TE Connectivity's Heavy Duty Connectors

Inserts

HEE Series

HEE SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

10			15			18			32		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
											
	Type	PN		Type	PN		Type	PN		Type	PN
Male (M)	HEE-010-M	T2050102101-000	Male (M)	HEE-015-M	T2800152101-000	Male (M)	HEE-018-M	T2050182101-000	Male (M)	HEE-032-M	T2050322101-000
Female (F)	HEE-010-F	T2050102201-000	Female (F)	HEE-015-F	T2800152201-000	Female (F)	HEE-018-F	T2050182201-000	Female (F)	HEE-032-F	T2050322201-000
Tech Data	Rated current:16A Rated voltage :500V Wiregauge:0.14-4.0mm ²		Tech Data	Rated current:16A Rated voltage :200V Wiregauge:1.5mm ²		Tech Data	Rated current:16A Rated voltage :500V Wiregauge:0.14-4.0mm ²		Tech Data	Rated current:16A Rated voltage :500V Wiregauge:0.14-4.0mm ²	
Hoods & Housings	For H6B series see page 59		Hoods & Housings	No need		Hoods & Housings	For H10B series see page 61-62		Hoods & Housings	For H16B series see page 63-64	

46			64			92		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HEE-046-M	T2050462101-000	Male (M)	HEE-032-M HEE-032-M 33-64	T2050322101-000 T2050642101-000	Male (M)	HEE-046-M HEE-046-M 47-92	T2050462101-000 T2050922101-000
Female (F)	HEE-046-F	T2050462201-000	Female (F)	HEE-032-F HEE-032-F 33-64	T2050322201-000 T2050642201-000	Female (F)	HEE-046-F HEE-046-F 47-92	T2050462201-000 T2050922201-000
Tech Data	Rated current:16A Rated voltage :500V Wiregauge:0.14-4.0mm ²		Tech Data	Rated current:16A Rated voltage :500V Wiregauge:0.14-4.0mm ²		Tech Data	Rated current:16A Rated voltage :500V Wiregauge:0.14-4.0mm ²	
Hoods & Housings	For H24B series see page 65-66		Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H48B series see page 68	





TE Connectivity's Heavy Duty Connectors

Inserts




HEEE Series

HEEE SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

Inserts

20			32			40			48		
Crimp Terminal			Crimp Terminal			Crimp Terminal			Crimp Terminal		
											
	Type	PN		Type	PN		Type	PN		Type	PN
Male (M)	HEEE-020-M	T2050202101-000	Male (M)	HEEE-032-M	T2050323101-000	Male (M)	HEEE-040-M	T2050402101-000	Male (M)	HEEE-048-M	T2050482101-000
Female (F)	HEEE-020-F	T2050202201-000	Female (F)	HEEE-032-F	T2050323201-000	Female (F)	HEEE-040-F	T2050402201-000	Female (F)	HEEE-048-F	T2050482201-000
Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.14-4.0mm ²	
Hoods & Housings	For H6B series see page 59		Hoods & Housings	For H10B series see page 61-62		Hoods & Housings	For H16B series see page 63-63		Hoods & Housings	For H16B series see page 63-64	

64			72			80		
Crimp Terminal			Crimp Terminal			Crimp Terminal		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HEEE-064-M	T2050643101-000	Male (M)	HEEE-072-M	T2050722101-000	Male (M)	HEEE-040-M HEEE-040-M 41-80	T2050402101-000 T2050802101-000
Female (F)	HEEE-064-F	T2050643201-000	Female (F)	HEEE-072-F	T2050722201-000	Female (F)	HEEE-040-F HEEE-040-F 41-80	T2050402201-000 T2050802201-000
Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.14-4.0mm ²	
Hoods & Housings	For H24B series see page 65-66		Hoods & Housings	For H24B series see page 65-66		Hoods & Housings	For H32B series see page 67	

96			128			144		
Crimp Terminal			Crimp Terminal			Crimp Terminal		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HEEE-048-M HEEE-048-M 49-96	T2050482101-000 T2050962101-000	Male (M)	HEEE-064-M HEEE-064-M 65-128	T2050643101-000 T2051283101-000	Male (M)	HEEE-072-M HEEE-072-M 73-144	T2050722101-000 T2051442101-000
Female (F)	HEEE-048-F HEEE-048-F 49-96	T2050482201-000 T2050962201-000	Female (F)	HEEE-064-F HEEE-064-F 65-128	T2050643201-000 T2051283201-000	Female (F)	HEEE-072-F HEEE-072-F 73-144	T2050722201-000 T2051442201-000
Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.14-4.0mm ²	
Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H48B series see page 68		Hoods & Housings	For H48B series see page 68	

TE Connectivity's Heavy Duty Connectors

Inserts

HVE Series

HVE SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

10 +2 additional contacts for safe high voltage connections

Crimp Terminal



	Type	PN
Male (M)	HVEC-010-M	T2300104101-000
Female (F)	HVEC-010-F	T2300104201-000
Tech Data	Rated current: 16A Rated voltage: 830V Wiregauge: 0.5-4.0 mm ²	
Hoods & Housings	For H24B series see page 65-66	

Inserts

TE Connectivity's Heavy Duty Connectors

Inserts

HD Series

HD SERIES INSERTS CAN MATCH THE HA AND HB SERIES HOODS AND HOUSINGS.

Inserts

7+ 			8			15		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HD-007-M	T2020072101-000	Male (M)	HD-008-M	T2020082101-000	Male (M)	HD-015-M	T2020152101-000
Female (F)	HD-007-F	T2020072201-000	Female (F)	HD-008-F	T2020082201-000	Female (F)	HD-015-F	T2020152201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 50V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H10A series see page 57	

15			25			25		
Rolled contacts (Order Rolled contacts separately)			Crimp Terminal (Order crimp contacts separately)			Rolled contacts (Order Rolled contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HD-015-M	T2020152101-000	Male (M)	HD-025-M	T2020252101-000	Male (M)	HD-025-M	T2020252101-000
Female (F)	HD-015-FJ	T2020153201-000	Female (F)	HD-025-F	T2020252201-000	Female (F)	HD-025-FJ	T2020253201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H10A series see page 57		Hoods & Housings	For H16A series see page 57		Hoods & Housings	For H16A series see page 57	

40			40			50		
Crimp Terminal (Order crimp contacts separately)			Rolled contacts (Order Rolled contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HD-040-M	T2020402101-000	Male (M)	HD-040-M	T2020402101-000	Male (M)	HD-025-M HD-025-M 25-50	T2020252101-000 T2020502101-000
Female (F)	HD-040-F	T2020402201-000	Female (F)	HD-040-FJ	T2020403201-000	Female (F)	HD-025-F HD-025-F 25-50	T2020252201-000 T2020502201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H32A series see page 58	

TE Connectivity's Heavy Duty Connectors



Inserts

HD Series

HD SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

64			64		
Crimp Terminal (Order crimp contacts separately)			Rolled contacts (Order Rolled contacts separately)		
					
	Type	PN		Type	PN
Male (M)	HD-064-M	T2020642101-000	Male (M)	HD-064-M	T2020642101-000
Female (F)	HD-064-F	T2020642201-000	Female (F)	HD-064-FJ	T2020643201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H24B series, see page 65-66		Hoods &Housings	For H24B series, see page 65-66	

80			80		
Crimp Terminal (Order crimp contacts separately)			Rolled contacts (Order Rolled contacts separately)		
					
	Type	PN		Type	PN
Male (M)	HD-040-M HD-040-M 41-80	T2020402101-000 T2020802101-000	Male (M)	HD-040-M HD-040-M 41-80	T2020402101-000 T2020802101-000
Female (F)	HD-040-F HD-040-F 41-80	T2020402201-000 T2020802201-000	Female (F)	HD-040-FJ HD-040-FJ 41-80	T2020403201-000 T2020802201-100
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H32B series, see page 67		Hoods &Housings	For H32B series, see page 67	

128			128		
Crimp Terminal (Order crimp contacts separately)			Rolled contacts (Order Rolled contacts separately)		
					
	Type	PN		Type	PN
Male (M)	HD-064-M HD-064-M 65-128	T2020642101-000 T2021282101-000	Male (M)	HD-064-M HD-064-M 65-128	T2020642101-000 T2021282201-000
Female (F)	HD-064-F HD-064-F 65-128	T2020642201-000 T2021282101-000	Female (F)	HD-064-FJ HD-064-FJ 65-128	T2020643201-000 T2021282201-100
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H48B series, see page 68		Hoods &Housings	For H48B series, see page 68	

Inserts

TE Connectivity's Heavy Duty Connectors

Inserts

HDD Series

HDD SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

Inserts

16			24			24		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Rolled contacts (Order Rolled contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HDD-016-M	T2030162101-000	Male (M)	HDD-024-M	T2030242101-000	Male (M)	HDD-024-M	T2030242101-000
Female (F)	HDD-016-F	T2030162201-000	Female (F)	HDD-024-F	T2030242201-000	Female (F)	HDD-024-FJ	T2030243201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H6B series see page 59		Hoods & Housings	For H6B series see page 59		Hoods & Housings	For H6B series see page 59	

42			42			72		
Crimp Terminal (Order crimp contacts separately)			Rolled contacts (Order Rolled contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HDD-042-M	T2030422101-000	Male (M)	HDD-042-M	T2030422101-000	Male (M)	HDD-072-M	T2030722101-000
Female (F)	HDD-042-F	T2030422201-000	Female (F)	HDD-042-FJ	T2030423201-000	Female (F)	HDD-072-F	T2030722201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H10B series see page 61-62		Hoods & Housings	For H10B series see page 61-62		Hoods & Housings	For H16B series see page 63-64	

144			108			216		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HDD-072-M HDD-072-M 73-144	T2030722101-000 T2031442101-000	Male (M)	HDD-108-M	T2031082101-000	Male (M)	HDD-108-M HDD-108-M 109-216	T2031082101-000 T2032162101-000
Female (F)	HDD-072-F HDD-072-F 73-144	T2030722201-000 T2031442201-000	Female (F)	HDD-108-F	T2031082201-000	Female (F)	HDD-108-F HDD-108-F 109- 216	T2031082201-000 T2032162201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H32B series see page 67		Hoods & Housings	For H24B series see page 65-66		Hoods & Housings	For H48B series see page 68	

TE Connectivity's Heavy Duty Connectors

Inserts

HQ Series & HSB Series

HQ SERIES INSERTS CAN MATCH THE HA SERIES HOODS AND HOUSINGS.

HSB SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

2+			2+			3+			3+			5+			7+		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
Type	PN		Type	PN		Type	PN		Type	PN		Type	PN		Type	PN	
Male (M)	HQ-002-M	T2080022101-000	Male (M)	HQ-002-PM	T2080023101-000	Male (M)	HQ-003-M	T2080032101-007	Male (M)	HQ-003-PM	T2080033101-007	Male (M)	HQ-005-M	T2080052101-000	Male (M)	HQ-007-M	T2080072101-000
Female (F)	HQ-002-F	T2080022201-000	Female (F)	HQ-002-PF	T2080023201-000	Female (F)	HQ-003-F	T2080032201-007	Female (F)	HQ-003-PF	T2080033201-007	Female (F)	HQ-005-F	T2080052201-000	Female (F)	HQ-007-F	T2080072201-000
Tech Data	Rated current: 40A Rated voltage: 400V Wiregauge: 1-10mm ²		Tech Data	Rated current: 40A Rated voltage: 830V Wiregauge: 1-10mm ²		Tech Data	Rated current: 40A Rated voltage: 400V Wiregauge: 1.5-10mm ²		Tech Data	Rated current: 40A Rated voltage: 830V Wiregauge: 1.5-10mm ²		Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 10A Rated voltage: 400V Wiregauge: 0.14-2.5mm ²	
Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H3A series see page 56	


8+			12+			17+			21+		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
Type	PN		Type	PN		Type	PN		Type	PN	
Male (M)	HQ-008-M	T2019092101-000	Male (M)	HQ-012-M	T2080122101-000	Male (M)	HQ-017-M	T2080172101-000	Male (M)	HQ-021-M	T2080212101-007
Female (F)	HQ-008-F	T2019092201-000	Female (F)	HQ-012-F	T2080122201-000	Female (F)	HQ-017-F	T2080172201-000	Female (F)	HQ-021-F	T2080212201-007
Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 10A Rated voltage: 400V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 6.5A Rated voltage: 50V AC / 120V DC Wiregauge: 0.08-0.52 mm ²	
Hoods & Housings	For H8A series see page 57		Hoods & Housings	For H3A series see page 56		Hoods & Housings	For H8A series see page 57		Hoods & Housings	For H3A series see page 56	

4/2+			HQ 4/4/6			6(CAT5)		
Crimp Terminal (Order crimp contacts separately)			Screw Terminal			Crimp Terminal (Order crimp contacts separately)		
Type	PN		Type	PN		Type	PN	
Male (M)	HQ-4/2-M	T2080062101-100	Male (M)	HQ-4/4/6-M	T2080142101-000	Male (M)	606E-C5-6P-E	T2080142101-100
Female (F)	HQ-4/2-F	T2080062201-100	Female (F)	HQ-4/4/6-F	T2080142201-000	Female (F)	606E-C5-6P-P	T2080142201-100
Tech Data	Rated current: 10A/40A Rated voltage: 250V/400V Wiregauge: 0.14-2.5 mm ² /1.0-6 mm ²		Tech Data	Rated current(Power/ Signal/Data) : 20A/10A/1.2A Rated voltage (Power/ Signal/Data) : 600V/250V/30V Wire gauge : 0.14-4.0mm ² (26-12AWG)		Tech Data	Rated current : 1.2A Rated voltage : 30V Wire gauge : 0.03-0.34mm ²	
Hoods & Housings	For H8A series, see page 57		Hoods & Housings	For H3A series, see page 56		Pin&Socket	ETH-CP-0.6(PIN) ETH-CS-0.6(SOCKET)	T2400011002-000 T2400012002-000

TE Connectivity's Heavy Duty Connectors

Inserts

Inserts

6			12		
Screw Terminal			Screw Terminal		
					
	Type	PN		Type	PN
Male (M)	HSB-006-M	T2060062101-000	Male (M)	HSB-006-M HSB-006-M 7-12	T2060062101-000 T2060122101-000
Female (F)	HSB-006-F	T2060062201-000	Female (F)	HSB-006-F HSB-006-F 7-12	T2060062201-000 T2060122201-000
Tech Data	Rated current: 35A Rated voltage: 690V Wiregauge: 1.5-6.0mm ²		Tech Data	Rated current: 35A Rated voltage: 690V Wiregauge: 1.5-6.0mm ²	
Hoods & Housings	For H16B series, see page 63-64		Hoods & Housings	For H32B series, see page 67	

HEAV Series

HEAV SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

			10		
Spring Terminal			Spring Terminal		
					
	Type	PN		Type	PN
Male (M)	HEAV-006-MS	T2100063101-000	Male (M)	HEAV-010-MS	T2100103101-000
Female (F)	HEAV-006-FS	T2100063201-000	Female (F)	HEAV-010-FS	T2100103201-000
Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.2-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.2-2.5mm ²	
Hoods & Housings	For H6B series, see page 59		Hoods & Housings	For H10B series, see page 61-62	

16			24		
Spring Terminal			Spring Terminal		
					
	Type	PN		Type	PN
Male (M)	HEAV-016-MS	T2100163101-000	Male (M)	HEAV-024-MS	T2100243101-000
Female (F)	HEAV-016-FS	T2100163201-000	Female (F)	HEAV-024-FS	T2100243201-000
Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.2-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.2-2.5mm ²	
Hoods & Housings	For H16B series, see page 63-64		Hoods & Housings	For H24B series, see page 65-66	

TE Connectivity's Heavy Duty Connectors

Inserts

HK & HWK Series

HK SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

HWK SERIES INSERTS CAN MATCH THE HB SERIES HOODS AND HOUSINGS.

HK4/0			HK4/2			HK4/8		
Screw Terminal			Screw Terminal			Screw Terminal		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HK4/0-004-M	T2100042101-000	Male (M)	HK4/2-006-M	T2100062101-000	Male (M)	HK4/8-012-M	T2100122101-000
Female (F)	HK4/0-004-F	T2100042201-000	Female (F)	HK4/2-006-F	T2100062201-000	Female (F)	HK4/8-012-F	T2100122201-000
Tech Data	Rated current: 80A, 16A Rated voltage: 690V, 400V Wiregauge: 1.5-16.0mm ²		Tech Data	Rated current: 80A,16A Rated voltage: 690V, 400V Wiregauge: 1.5-16.0mm ² , 0.5-2.5mm ²		Tech Data	Rated current: 80A, 16A Rated voltage: 400V, 400V Wiregauge: 1.5-16mm ² , 0.5-2.5mm ²	
Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H24B series see page 65-66	

HK8/24			HK12/2			HK6/36		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HK8/24-032-M	T2100322101-000	Male (M)	HK12/2-014-M	T2120142101-000	Male (M)	HK6/36-042-M	T2120422101-000
Female (F)	HK8/24-032-F	T2100322201-000	Female (F)	HK12/2-014-F	T2120142201-000	Female (F)	HK6/36-042-F	T2120422201-000
Tech Data	Rated current: 16A, 10A Rated voltage: 400V, 250V Wiregauge: 0.14-4mm ² , 0.14-2.5mm ²		Tech Data	Rated current: 40A, 10A Rated voltage: 690V, 250V Wiregauge: 1-6mm ² , 0.14-2.5mm ²		Tech Data	Rated current: 40A, 10A Rated voltage: 690V, 160V Wiregauge: 1-6mm ² , 0.14-2.5mm ²	
Hoods & Housings	For H10B series see page 61-62		Hoods & Housings	For H16B series see page 63-64		Hoods & Housings	For H16B series see page 63-64	

HWK3/3/6			HK-HDW3/1/1-23/16/47		
Screw Terminal			Crimp Terminal (Order crimp contacts separately)		
					
	Type	PN		Type	PN
Male (M)	HWK3/3/6-012-M	T2093362101-000	Male (M)	HK-HDW3/1/1-23/16/47-M	T2120865101-000
Female (F)	HWK3/3/6-012-F	T2093362201-000	Female (F)	HK-HDW3/1/1-23/16/47-F	T2120865201-000
Tech Data	Rated current: 100A, 40A, 16A Rated voltage: 690V, 400V, 250V Wiregauge: 16-35mm ² , 2.5-6mm ² , 0.5-2.5mm ² ,		Tech Data	Rated current: 11A, 3.7A, 2.2A Rated voltage: 400V, 300V, 32V Wiregauge: 0.08-2.2mm ² , 0.05-0.87mm ² , 0.05-0.37mm ²	
Hoods & Housings	For H24B series, see page 65-66		Hoods & Housings	H10B(short rib/one rib), PNs see below	

TCPN	Type
T1410100000-001	H10B-AG-SL, ONE RIB
T1220102025-000	H10B-TG-M20/M25 SHORT RIB
T1230100132-002	H10B-TSH-M32, SHORT RIB
T1240100132-002	H10B-TGH-M32, SHORT RIB
T1750101132-002	H10B-TBFHS-PG/M, SHORT RIB

TE Connectivity's Heavy Duty Connectors

Inserts

Special Inserts

HCC-010



	Type	PN
Male (M)	HCC-010-M	T2100102101-000
Female (F)	HCC-010-F	T2100102201-000
Tech Data	Rated current : 30A Rated voltage : 500V Wire gauge : 0.5-4.0mm ²	
Hood & Housings	NA	

H1A Series - 12+


Crimp Terminal(order crimp contacts separately)



	Type	PN
Male (M)	H1A-012-M	T2010124101-000
Female (F)	H1A-012-F	T2010124201-000
Tech Data	Rated current : 6.5A Rated voltage : 50V Wire gauge : 0.08-0.52mm ² (28-20 AWG)	
Hood & Housings	T2010124301-000-H1A CABLE ADAPTER * 2pcs	

BPSC-12/2/4

Screw Terminal



	Type	PN
Male (M)	BPSC-12/2/4-M	T2100182101-000
Female (F)	BPSC-12/2/4-F	T2100182201-000
Tech Data	Rated current/ voltage: Power : 70A/ 1000V * 4 Pins Power : 20A/ 400V * 2 Pins Signal : 5A/ 25V * 12 Pins Wire gauge : 10-12mm ² /2.5-4mm ² /0.5-0.75mm ²	
Contact & Screw	PNs See below	

HK2/4-006



	Type	PN
Male (M)	HK2/4-006-M	T2120062101-001
Female (F)	HK2/4-006-F	T2120062201-001
Tech Data	Rated current : 80A,10A Rated voltage : 250V,60V , 32V Wire gauge : 10-16mm ² (8-6 AWG), 0.14-2.5mm ² (26-14 AWG)	
Hoods & Housings	NA	


TCPN	Type
T0931000408-000	M4 STAINLESS STEEL SCREW
T2410001160-000	MCSM10-12
T2031001040-000	MCEM-4.0
T3020001005-000	MDAM-0.5
T2240002120-000(4000PCS/BOX)	SCSF10-12
T2240002120-001(1000PCS/BOX)	
T2220002040-000(10000PCS/BOX)	SCEF2.5-4.0
T2220002040-001(2500PCS/BOX)	
T2210002010-000(20000PCS/BOX)	SDAF0.5-0.75
T2210002010-001(5000PCS/BOX)	

TE Connectivity's Heavy Duty Connectors


Modular Inserts

HMN MODULAR CONNECTORS OVERVIEW

Modular units, install and remove without special tools!



HMN module fixing frame



Distance for electrical contacts max.21mm
20.5mm/For pneumatic contacts max.20.5mm
Each frame is composed of an upper and a lower bracket.


Hood/ Housing Type	No. of Modules	a	b	Product	P/N
H24B	6	104	111	H24BN-T6-M	T2070244101-000
				H24BN-T6-F	T2070244201-000
H16B	4	77.5	84.5	H16BN-T4-M	T2070164101-000
				H16BN-T4-F	T2070164201-000
H10B	3	57	64.1	H10BN-T3-M	T2070104101-000
				H10BN-T3-F	T2070104201-000
H6B	2	44	51	H6BN-T2-M	T2070064101-000
				H6BN-T2-F	T2070064201-000
H10A	1	49.5	56.5	H10A-T1-M	T2079104101-000
				H10A-T1-F	T2079104201-000

TE Connectivity's Heavy Duty Connectors


Modular Inserts

HMN DOCKING FRAME OVERVIEW

Modular units, install and remove without special tools!



Space of two Panels at close status



Panel cut out

Hood/Housing Type	No. of Modules	a	b	Product	P/N
H24BP	6	107.4	97.4	H24BP-T6-M docking frame,floating	T2071244101-000
				H24BP-T6-F docking frame,fixed	T2071244201-000
H16BP	4	78	68	H16BP-T4-M docking frame,floating	T2071164101-000
				H16BP-T4-F docking frame,fixed	T2071164201-000
H10BP	3	63.3	53.3	H10BP-T3-M docking frame,floating	T2071104101-000
				H10BP-T3-F docking frame,fixed	T2071104201-000
H6BP	2	48.6	38.6	H6BP-T2-M docking frame,floating	T2071064101-000
				H6BP-T2-F docking frame,fixed	T2071064201-000
-	-	-	-	Floating washer	T0930050457-001




TE Connectivity's Heavy Duty Connectors



Modular Inserts




HMN Series




HMN SERIES INSERTS CAN MATCH THE HA SERIES HOODS AND HOUSINGS.

Inserts

1-pole			2-poles			2-poles		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HMN-001-MC	T2111013101-000	Male (M)	HMN-D2-MC	T2111028101-000	Male (M)	HMN-002-MC	T2111020101-000
Female (F)	HMN-001-FC	T2111013201-000	Female (F)	HMN-D2-FC	T2111028201-000	Female (F)	HMN-002-FC	T2111020201-000
Tech Data	Rated current: 200A, 250A Rated voltage: 1000V Wiregauge: 25-85mm ²		Tech Data	Rated current: 100A Rated voltage: 1000V Wiregauge: 10-35mm ²		Tech Data	Rated current: 70A, 85A Rated voltage: 1000V Wiregauge: 6-25mm ²	

2-poles			2-poles		
Axial Terminal			Axial Terminal		
					
	Type	PN		Type	PN
Male (M)	HMN-S2-M 2.5-8	S2111023101-000	Male (M)	HMN-S2-MD 6-10	S2111025101-000
Female (F)	HMN-S2-F 2.5-8	S2111023201-000	Female (F)	HMN-S2-FD 6-10	S2111025201-000
Tech Data	Rated current: 40A Rated voltage: 1000V Wiregauge: 2.5-8 mm ²		Tech Data	Rated current: 40A Rated voltage: 1000V Wiregauge: 6-10mm ²	

3-poles			4-poles			5-poles		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Spring Terminal		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HMN-003-M	T2111032101-000	Male (M)	HMN-004-M	T2111042101-000	Male (M)	HMN-005-MS	T2110052101-000
Female (F)	HMN-003-F	T2111032201-000	Female (F)	HMN-004-F	T2111042201-000	Female (F)	HMN-005-FS	T2110052201-000
Tech Data	Rated current: 40A Rated voltage: 690V Wiregauge: 1-6mm ²		Tech Data	Rated current: 40A Rated voltage: 830V Wiregauge: 1-10mm ²		Tech Data	Rated current: 16A Rated voltage: 400V Wiregauge: 0.5-2.5mm ²	




6-poles			6-poles			8-poles		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HMN-006-M	T2111062101-000	Male (M)	HMN-006-PM	T2111063101-000	Male (M)	HMN-008-MC	T2111082101-000
Female (F)	HMN-006-F	T2111062201-000	Female (F)	HMN-006-PF	T2111063201-000	Female (F)	HMN-008-FC	T2111082201-000
Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 830V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 16A Rated voltage: 400V Wire gauge: 0.14-4.0mm ²	

TE Connectivity's Heavy Duty Connectors

Modular Inserts

HMN Series

HMN SERIES INSERTS CAN MATCH THE HA SERIES HOODS AND HOUSINGS.

12-poles			17-poles			20-poles		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
								
	Type	PN		Type	PN		Type	PN
Male (M)	HMN-012-M	T2111122101-000	Male (M)	HMN-017-M	T2111172101-000	Male (M)	HMN-020-M	T2111202101-000
Female (F)	HMN-012-F	T2111122201-000	Female (F)	HMN-017-F	T2111172201-000	Female (F)	HMN-020-F	T2111202201-000
Tech Data	Rated current: 10A Rated voltage: 250V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 10A Rated voltage: 160V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 16A Rated voltage: 500V Wiregauge: 0.14-4.0mm ²	

Inserts

TE Connectivity's Heavy Duty Connectors

Modular Inserts

HMN Series

HMN SERIES INSERTS CAN MATCH THE HA SERIES HOODS AND HOUSINGS.

2 & 3-poles			Pneu-c Ø1.6		Pneu-c Ø3.0		Pneu-c Ø4.0		Pneu-c Ø6.0	
Crimp Terminal (Order crimp contacts separately)										
	Type HMN-PA2	Type HMN-PA3	Type	PN	Type	PN	Type	PN	Type	PN
Male (M)	T211022301-000	T211032301-000	Pneu-c M1.6	T2090002101-001	Pneu-c M3.0	T2090002101-002	Pneu-c M4.0	T2090002101-003	Pneu-c M6.0	T2090002101-004
Female(F)	T211022301-000	T211032301-000	Pneu-c F1.6	T2090002201-001	Pneu-c F3.0	T2090002201-002	Pneu-c F4.0	T2090002201-003	Pneu-c F6.0	T2090002201-004

Quintax 1 2-poles			Quintax 4 2-poles			Quintax 8 2-poles		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
	Type	PN		Type	PN		Type	PN
Male (M)	HMN-Q1-M	T211027101-000	Male (M)	HMN-Q2 -M	T211027101-001	Male (M)	HMN-Q3 -M	T211027101-002
Female(F)	HMN-Q1-F	T211027201-000	Female(F)	HMN-Q2-F	T211027201-001	Female (F)	HMN-Q3-F	T211027201-002
Tech Data	Rated current: 16A Rated voltage: 50V Wiregauge: 0.14-4mm ²		Tech Data	Rated current: 10A Rated voltage: 50V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 5A Rated voltage: 50V Wiregauge: 0.08-0.52mm ²	

Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)		
	Type	PN		Type	PN		Type	PN
Male (M)	QUINTAX 1-POLE-M	T258001154-000	Male (M)	QUINTAX 4-POLES-M	T258003154-000	Male (M)	QUINTAX 8-POLES-M	T258008154-000
Female (F)	QUINTAX 1-POLE-F	T2580012154-000	Female (F)	QUINTAX 4-POLES-F	T2580032154-000	Female (F)	QUINTAX 8-POLES-F	T2580082154-000
Tech Data	Rated current: 16A Rated voltage: 50V Wiregauge: 0.14-4.0mm ²		Tech Data	Rated current: 10A Rated voltage: 50V Wiregauge: 0.14-2.5mm ²		Tech Data	Rated current: 5A Rated voltage: 50V Wiregauge: 0.08-0.52mm ²	

25-poles			D-Sub			RJ45			Dummy Module Insert		
Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)			Crimp Terminal (Order crimp contacts separately)					
	Type	PN		Type	PN		Type	PN		Type	PN
Male (M)	HMN-O25-M	T2111252101-000	Male (M)	HMN-009-M	T2111092101-000	Male (M)	HMN-RJ45-MC	T2113000101-100		HMN-DM	T3110009902-000
Female(F)	HMN-O25-F	T2111252201-000	Female (F)	HMN-009-F	T2111092201-000	Female (F)	HMN-RJ45-F	T2113000201-000			
Tech Data	Rated current: 5A Rated voltage: 50V Wiregauge: 0.08-0.52mm ²		Tech Data	Rated current: 5A Rated voltage: 50V Wiregauge: 0.08-0.52mm ²		Tech Data	Rated current: 1A Rated voltage: 50V		Tech Data		

RJ45 Cat 6A			Power 3 poles + Signal 4 poles			HMN-D3-2/6			HMN-HD1-32 EMC Shielding		
	Type	PN		Type	PN		Type	PN		Type	PN
Male (M)	HMN-RJ45-M	T2113000101-200	Male (M)	HMN-3/4-M	T2111342101-000	Male (M)	HMN-D3-2/6-M	T2115032101-000	Male (M)	HMN-HD1-32-M(8.45) HMN-HD1-32-M(12.2)	T2111322101-000 T2111322101-001
Female (F)	HMN-RJ45-F CAT6A	T2113000201-200	Female (F)	HMN-3/4-F	T2111342201-000	Female (F)	HMN-D3-2/6-F	T2115032201-000	Female (F)	HMN-HD1-32-F(8.45) HMN-HD1-32-F(12.2)	T2111322201-000 T2111322201-001
Tech Data	Rated current: 1A Rated voltage: 50V Cat 6/10Gbit		Tech Data	Rated current: 40A/10A Rated voltage: 830V Wiregauge: Power 1-6mm ² Signal 0.14-2.5mm ²		Tech Data	Rated current: 1.2A Rated voltage: 30V Wiregauge: FOR 210 DATE: 0.14-1.0 mm ² FOR 606 DATE: 0.08-0.34 mm ²		Tech Data	Rated current: 2.2A Rated voltage: 32V Wiregauge: AWG28-22 0.08-0.375Qmm AWG30-28 0.05-0.10SQmm	


Inserts

TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

FEATURES

Inserts



BENEFITS

- Designed for harsh (industrial) environments
- Improved operational efficiency using automated
- Reliable and high density contact, up to 288 positions
- Extended portfolio that offers integration with existing HDC products
- Increased flexibility and reduced size for space-saving


TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

PRODUCT SPECIFICATIONS

	Electrical		Mechanical	Materials	Standards & Specifications		Environmental		Product Compliance/ Approvals
	Current	Voltage	Housing Locking Strength	Mold Material	Product Specification	Application Specification	Heat Aging	Thermal Shock	
HMN-HD1-48	2.2A MAX	32V	100 N Min	PBT GF	108-140152	114-78022	125°C 168 hr	-40°C/1h, 125°C/1h. 100 cycles	UL1977
HMN-HD1-24	3.7A MAX	300V	100 N Min	PBT GF	108-140157	114-78025	125°C 168 hr	-40°C/1h, 125°C/1h. 100 cycles	UL1977
HMN-HD3-10	11A MAX	400V	100 N Min	PBT GF	108-140158	114-78026	125°C 168 hr	-40°C/1h, 125°C/1h. 100 cycles	UL1977
HMN-HD4-6	16A MAX	500V	100 N Min	PBT GF	108-140159	114-78027	125°C 168 hr	-40°C/1h, 125°C/1h. 100 cycles	UL1977
HMN-HD5-3	40A MAX	300V	100 N Min	PBT GF	108-140160	114-78028	125°C 168 hr	-40°C/1h, 125°C/1h. 100 cycles	UL1977

Inserts



HMN FRAME

Hood/Housing Type	No. of Modules	A	B	Product	P/N
H24B	6	104	111	H24BN-T6-M-HD	T2070244101-002
				H24BN-T6-F-HD	T2070244201-002
H16B	4	77.5	84.5	H16BN-T4-M-HD	T2070164101-002
				H16BN-T4-F-HD	T2070164201-002
H10B	3	57	64.1	H10BN-T3-M-HD	T2070104101-002
				H10BN-T3-F-HD	T2070104201-002
H6B	2	44	51	H6BN-T2-M-HD	T2070064101-002
				H6BN-T2-F-HD	T2070064201-002
H10A	1	49.5	56.5	H10A-T1-M-HD	T2079104101-002
				H10A-T1-F-HD	T2079104201-002

Note:



1)Distance for electrical contacts: max. 21mm



TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

PRODUCT OFFERINGS

HMN-HD1 MODULE

Male Housing	Product	P/N
	HMN-HD1-48-M	2312729-2
	HMN-HD1-24-M	2316315-2

Female Housing	Product	P/N
	HMN-HD1-48-F	2312730-2
	HMN-HD1-24-F	2316316-2

Male Housing assembly with Tab Contacts



Female Housing assembly with Receptacle Contacts



Inserts

Wire Size		Insulation Diameter (mm)	Size	Plating (μm)	Tab Contact P/N		Receptacle Contact P/N		Applicable Crimping Tool	
AWG	mm ²				Strip	L/P	Strip	L/P	Applicator	Hand Tool
30	0.05 - 0.10	0.6 - 1.2	S	Au 0.38	2316663-1	2316669-1	2316670-1	2316671-1	2151110-1	2119144-1 + 2305680-1**
28										
28	0.08 - 0.37	1.08 - 1.6	M	Au 0.38	2316663-2	2316669-2	2316670-2	2316671-2	2151082-1	2119141-1 + 2305680-1**
26										2305681-1***
24										
22										
28	0.08-0.37	1.08 - 1.9	L*	Au 0.38	2316663-3	2316669-3	2316670-3	2316671-3	2151111-1	2119143-1 + 2305680-1**
26										2305683-1***
24										
22										
22	0.34-0.87	1.4 - 2.2	2L*	Au 0.38	2316663-4	2316669-4	2316670-4	2316671-4	2151083-1	2119142-1 + 2305680-1**
20										2305682-1***
18										

TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

PRODUCT SPECIFICATIONS

HMN-HD3 MODULE

Male Housing	Product	P/N
	HMN-HD3-10-M	2312733-2

Female Housing	Product	P/N
	HMN-HD3-10-F	2312734-2

Male Housing assembly with Tab Contacts



Female Housing assembly with Receptacle Contacts



Inserts


Wire Size		Insulation Diameter (mm)	Size	Plating (m)	Tab Contact P/N		Receptacle Contact P/N		Applicable Crimping Tool	
AWG	mm ²				Strip	L/P	Strip	L/P	Applicator	Hand Tool
28	0.08 - 0.20	0.8 - 1.4	S	Au 0.38	2316815-1	2316817-1	2298107-1	2311162-1	2836130-1	91565-1
26										
24										
24	0.20 - 0.50	1.2-2.6	M	Au 0.38	2316815-2	2316817-2	2298107-2	2311162-2	2151080-1	91559-1
24										
22										
20	0.50 - 1.42	1.8-2.8	L	Au 0.38	2316815-3	2316817-3	2298107-3	2311162-3	2151018-1	91558-1
18										
18										
16	1.25 - 2.20	2.2-2.8	2L	Au 0.38	2316815-4	2316817-4	2298107-4	2311162-4	2151119-1	91560-1
14										
14										
16	1.25 - 2.20	3.1-3.4	3L	Au 0.38	2316815-5	2316817-5	2298107-5	2311162-5	2151073-1	91561-1
14										


TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

PRODUCT SPECIFICATIONS


HMN-HD4 MODULE

Male Housing	Product	P/N
	HMN-HD4-6-M	2312735-2

Female Housing	Product	P/N
	HMN-HD4-6-F	2312736-2

Male Housing assembly with Tab Contacts

Female Housing assembly with Receptacle Contacts



Inserts


Wire Size		Insulation Diameter (mm)	Size	Plating (μm)	Tab Contact P/N		Receptacle Contact P/N		Applicable Crimping Tool	
AWG	mm ²				Strip	L/P	Strip	L/P	Applicator	Hand Tool
22	0.30 - 0.50	1.58-2.56	SS	Au 0.76	1-2287732-2	1-2288019-1	2287721-2	2288020-1	-	2255300-1
20										
20	0.50 - 1.42	1.8-3.23	S	Au 0.38	1-2040016-2	1-2040586-1	2040015-2	2040587-1	2266289-X	2047670-1
18										
16										
16	1.25 - 2.20	2.0-3.75	M	Au 0.38	1-1747419-2	1-1747501-2	1747418-2	1747499-2	1762120-2	1762130-1
14										
14	2.20 - 3.50	2.9-4.1	L	Au 0.38	1-1747416-2	1-1747500-2	1747415-2	1747498-2	1762119-2	1762129-1
12										


TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

PRODUCT SPECIFICATIONS

HMN-HD5 MODULE

Male Housing	Product	P/N
	HMN-HD5-3-M	2312737-2

Female Housing	Product	P/N
	HMN-HD5-3-F	2312738-2

Male Housing assembly with Tab Contacts



Female Housing assembly with Receptacle Contacts



Inserts


Wire Size		Insulation Diameter (mm)	Size	Plating (μm)	Tab Contact P/N		Receptacle Contact P/N		Applicable Crimping Tool	
AWG	mm ²				Strip	L/P	Strip	L/P	Applicator	Hand Tool
16	1.25 - 2.00	3-3.8	S	Au 0.2	84696-1	2013594-1	179955-2	316040-2	234030-2	234170-1
14										
12	3.50 - 5.50	4-5.2	M	Au 0.2	84695-1	2013593-1	179956-2	316041-2	234029-2	234171-1
10										
8	8.00	4.9-7.8	L	Au 0.2	2316819-1	2316820-1	1318696-2	1318697-2	1366658-4	1366044-1


TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

PRODUCT SPECIFICATIONS

HMN-HDW-5/3 MODULE

Male Housing	Product	P/N
	HMN-HDW5/3-4/4-M	2312739-2

Female Housing	Product	P/N
	HMN-HDW5/3-4/4-F	2312740-2

Male Housing assembly with Tab Contacts



Female Housing assembly with Receptacle Contacts



Inserts

Wire Size		Insulation Diameter (mm)	Size	Plating (μm)	Tab Contact P/N		Receptacle Contact P/N		Applicable Crimping Tool	
AWG	mm ²				Strip	L/P	Strip	L/P	Applicator	Hand Tool
28	0.08 - 0.20	0.8 - 1.4	S	Au 0.38	2316815-1	2316817-1	2298107-1	2311162-1	2836130-1	91565-1
26										
24										
24	0.20 - 0.50	1.2-2.6	M	Au 0.38	2316815-2	2316817-2	2298107-2	2311162-2	2151080-1	91559-1
22										
20										
20	0.50 - 1.42	1.8-2.8	L	Au 0.38	2316815-3	2316817-3	2298107-3	2311162-3	2151018-1	91558-1
18										
18										
16	1.25 - 2.20	2.2-2.8	2L	Au 0.38	2316815-4	2316817-4	2298107-4	2311162-4	2151119-1	91560-1
14										
16	1.25 - 2.20	3.1-3.4	3L	Au 0.38	2316815-5	2316817-5	2298107-5	2311162-5	2151073-1	91561-1
14										

TE Connectivity's Heavy Duty Connectors

Modular Inserts HDC Dynamic Connectors

PRODUCT SPECIFICATIONS



Wire Size		Insulation Diameter (mm)	Size	Plating (μm)	Tab Contact P/N		Receptacle Contact P/N		Applicable Crimping Tool	
AWG	mm ²				Strip	L/P	Strip	L/P	Applicator	Hand Tool
16	1.25 - 2.00	3-3.8	S	Au 0.2	84696-1	2013594-1	179955-2	316040-2	234030-2	234170-1
14										
12	3.50 - 5.50	4-5.2	M	Au 0.2	84695-1	2013593-1	179956-2	316041-2	234029-2	234171-1
10										
8	8.00	4.9-7.8	L	Au 0.2	2316819-1	2316820-1	1318696-2	1318697-2	1366658-4	1366044-1

Inserts

TE Connectivity's Heavy Duty Connectors

HCM series

HCM Series

PRODUCT OFFERING



Inserts

Solution	Series	Components	PN	Description	Comments
1 Pole	HCM250	Hoods	T1920160125-000	H16BPR-TGH-M25	Depends on cable diameter
		Housings	T1930160000-000	H16BPR-AG	
		Female Inserts	T2192503201-000	HCM250-FC	Crimp terminal
		Male Inserts	T2192503101-000	HCM250-MC	Crimp terminal
		Frame	T0924028544-000	H16BRP-2P-250-FRAME	
		Female Contacts	T2192502035-000	HCM250-FC-35	Crimp area acc. to DIN EN 46 235
			T2192502050-000	HCM250-FC-50	Crimp area acc. to DIN EN 46 235
			T2192502070-000	HCM250-FC-70	Crimp area acc. to DIN EN 46 235
		Male Contacts	T2192501035-000	HCM250-MC-35	Crimp area acc. to DIN EN 46 235
			T2192501050-000	HCM250-MC-50	Crimp area acc. to DIN EN 46 235
			T2192501070-000	HCM250-MC-70	Crimp area acc. to DIN EN 46 235
		HCM350	Hoods	T1920160125-000	H16BPR-TGH-M25
	Housings		T1930060000-000	H6BPR-AG	
	Female Inserts		T2193503201-000	HCM350-FC	Crimp terminal
	Male Inserts		T2193503101-000	HCM350-MC	Crimp terminal
	Frame		T0924015115-000	H6BPR-1P-350-FRAME	
	Female Contacts		T2193502035-000	HCM350-FC35	Crimp area acc. to DIN EN 46 235
			T2193502050-000	HCM350-FC-50	Crimp area acc. to DIN EN 46 235
			T2193502070-000	HCM350-FC-70	Crimp area acc. to DIN EN 46 235
			T2193502095-000	HCM350-FC-95	Crimp area acc. to DIN EN 46 235
			T2193502120-000	HCM350-FC-120	Crimp area acc. to DIN EN 46 235
	Male Contacts		T2193501035-000	HCM350-MC-35	Crimp area acc. to DIN EN 46 235
			T2193501050-000	HCM350-MC-50	Crimp area acc. to DIN EN 46 235
		T2193501070-000	HCM350-MC-70	Crimp area acc. to DIN EN 46 235	
T2193501095-000		HCM350-MC-95	Crimp area acc. to DIN EN 46 235		
T2193501120-000		HCM350-MC-120	Crimp area acc. to DIN EN 46 235		

TE Connectivity's Heavy Duty Connectors

HCM series

HCM Series

PRODUCT OFFERING

Inserts

Solution	Series	Components	PN	Description	Comments	
2 Poles	HCM250	Hoods	T1920160225-000	H16BPR-TGH-2M25	Depends on cable diameter	
		Housings	T1930160000-000	H16BPR-AG		
		Female Inserts	T2192503201-000	HCM250-FC	Crimp terminal	
		Male Inserts	T2192503101-000	HCM250-MC	Crimp terminal	
		Frame	T0924028544-000	H16BRP-2P-250-FRAME		
		Female Contacts	T2192502035-000	HCM250-FC-35	Crimp area acc. to DIN EN 46 235	
			T2192502050-000	HCM250-FC-50	Crimp area acc. to DIN EN 46 235	
			T2192502070-000	HCM250-FC-70	Crimp area acc. to DIN EN 46 235	
			Male Contacts	T2192501035-000	HCM250-MC-35	Crimp area acc. to DIN EN 46 235
				T2192501050-000	HCM250-MC-50	Crimp area acc. to DIN EN 46 235
				T2192501070-000	HCM250-MC-70	Crimp area acc. to DIN EN 46 235
		HCM350	Hoods	T1920160225-000	H16BPR-TGH-2M25	Depends on cable diameter
	Housings		T1930160000-000	H16BPR-AG		
	Female Inserts		T2193503201-000	HCM350-FC	Crimp terminal	
	Male Inserts		T2193503101-000	HCM350-MC	Crimp terminal	
	Frame		T0924027845-000	H16BPR-2P-350-FRAME		
	Female Contacts		T2193502035-000	HCM350-FC-35	Crimp area acc. to DIN EN 46 235	
			T2193502050-000	HCM350-FC-50	Crimp area acc. to DIN EN 46 235	
			T2193502070-000	HCM350-FC-70	Crimp area acc. to DIN EN 46 235	
			T2193502095-000	HCM350-FC-95	Crimp area acc. to DIN EN 46 235	
			T2193502120-000	HCM350-FC-120	Crimp area acc. to DIN EN 46 235	
			Male Contacts	T2193501035-000	HCM350-MC-35	Crimp area acc. to DIN EN 46 235
	T2193501050-000			HCM350-MC-50	Crimp area acc. to DIN EN 46 235	
	T2193501070-000	HCM350-MC-70		Crimp area acc. to DIN EN 46 235		
	T2193501095-000	HCM350-MC-95		Crimp area acc. to DIN EN 46 235		
	T2193501120-000	HCM350-MC-120		Crimp area acc. to DIN EN 46 235		
	HCM650	Hoods		T1920240332-409	H24BPR-TGH-XL-3M32- EMC-C	Anti-corrosion performance, 3xM32 threads
		Housings	T1930240000-409	H24BPR-AG-EMC-C	High anticorrosion performance	
		Blind Plug	T3165320111-000	BLIND-32-M	Metal blind plug M32	
		Female Inserts	T2196503201-000	HCM650-FC	Crimp terminal	
		Male Inserts	T2196503101-000	HCM650-MC	Crimp terminal	
		Frame	T0924311125-000	H24BPR-3P-650-RRAME	3 Polesitions Frame	
		Female Contacts	T2196502070-001	HCM650-FC-70	Crimp area acc. to DIN EN 46 235	
T2196502095-001			HCM650-FC-95	Crimp area acc. to DIN EN 46 235		
T2196502120-001			HCM650-FC-120	Crimp area acc. to DIN EN 46 235		
T2196502150-001			HCM650-FC-150	Crimp area acc. to DIN EN 46 235		
T2196502185-001			HCM650-FC-185	Crimp area acc. to DIN EN 46 235		
Male Contacts			T2196501070-001	HCM650-MC-70	Crimp area acc. to DIN EN 46 235	
		T2196501095-001	FICM650-MC-95	Crimp area acc. to DIN EN 46 235		
		T2196501120-001	FICM650-MC-120	Crimp area acc. to DIN EN 46 235		
		T2196501150-001	FICM650-MC-150	Crimp area acc. to DIN EN 46 235		
		T2196501185-001	FICM650-MC-185	Crimp area acc. to DIN EN 46 235		

TE Connectivity's Heavy Duty Connectors

HCM series

HCM Series

PRODUCT OFFERING

Solution	Series	Components	PN	Description	Comments
3 Poles	HCM250	Hoods	T1920240325-000	H24BPR-TGH-3M25	Depends on cable diameter
		Housings	T1930240000-000	H24BPR-AG	
		Female Inserts	T2192503201-000	HCM250-FC	Crimp terminal
		Male Inserts	T2192503101-000	HCM250-MC	Crimp terminal
		Frame	T0924049044-100	H 24BPR-4P-250-M-FRAME	
			T0924049044-200	H24BPR-4P-250-F-FRAME	
		Female Contacts	T2192502035-000	HCM250-FC-35	Crimp area acc. to DIN EN 46 235
			T2192502050-000	HCM250-FC-50	Crimp area acc. to DIN EN 46 235
			T2192502070-000	HCM250-FC-70	Crimp area acc. to DIN EN 46 235
		Male Contacts	T2192501035-000	HCM250-MC-35	Crimp area acc. to DIN EN 46 235
			T2192501050-000	HCM250-MC-50	Crimp area acc. to DIN EN 46 235
			T2192501070-000	HCM250-MC-70	Crimp area acc. to DIN EN 46 235
	HCM350	Hoods	T1920240325-000	H24BPR-TGH-3M25	Depends on cable diameter
		Housings	T1930240000-000	H24BPR-AG	
		Female Inserts	T2193503201-000	HCM350-FC	Crimp terminal
		Male Inserts	T2193503101-000	HCM350-MC	Crimp terminal
		Frame	T0924311044-000	H24BRP-3P-350-FRAME	
		Female Contacts	T2193502035-000	HCM350-FC-35	Crimp area acc. to DIN EN 46 235
			T2193502050-000	HCM350-FC-50	Crimp area acc. to DIN EN 46 235
			T2193502070-000	HCM350-FC-70	Crimp area acc. to DIN EN 46 235
			T2193502095-000	HCM350-FC-95	Crimp area acc. to DIN EN 46 235
		Male Contacts	T2193502120-000	HCM350-FC-120	Crimp area acc. to DIN EN 46 235
			T2193501035-000	HCM350-MC-35	Crimp area acc. to DIN EN 46 235
			T2193501050-000	HCM350-MC-50	Crimp area acc. to DIN EN 46 235
	T2193501070-000		HCM350-MC-70	Crimp area acc. to DIN EN 46 235	
	Male Contacts	T2193501095-000	HCM350-MC-95	Crimp area acc. to DIN EN 46 235	
		T2193501120-000	HCM350-MC-120	Crimp area acc. to DIN EN 46 235	
	HCM650	Hoods	T1920240332-409	H24BPR-TGH-XL-3M32-EMC-C	Anti-corrosion performance. 3xM32 threads
		Housings	T1930240000-409	H24BR-AG-EMC-C	High anticorrosion performance
		Mounting frame	T1990240001-001	H24BPR-FRAME	
		Female Inserts	T2196503201-000	HCM650-FC	Crimp terminal
		Male Inserts	T2196503101-000	HCM650-MC	Crimp terminal
		Frame	T0924311125-000	H24BPR-3P-650-RRAME	3 Polesitions Frame
		Female Contacts	T2196502070-001	HCM650-FC-70	Crimp area acc. to DIN EN 46 235
			T2196502095-001	HCM650-FC-95	Crimp area acc. to DIN EN 46 235
			T2196502120-001	HCM650-FC-120	Crimp area acc. to DIN EN 46 235
T2196502150-001			HCM650-FC-150	Crimp area acc. to DIN EN 46 235	
T2196502185-001			HCM650-FC-185	Crimp area acc. to DIN EN 46 235	
Male Contacts		T2196501070-001	HCM650-MC-70	Crimp area acc. to DIN EN 46 235	
	T2196501095-001	HCM650-MC-95	Crimp area acc. to DIN EN 46 235		
	T2196501120-001	HCM650-MC-120	Crimp area acc. to DIN EN 46 235		
	T2196501150-001	HCM650-MC-150	Crimp area acc. to DIN EN 46 235		
	T2196501185-001	HCM650-MC-185	Crimp area acc. to DIN EN 46 235		

Inserts

TE Connectivity's Heavy Duty Connectors

HCM series

HCM Series

PRODUCT OFFERING












Inserts

Solution	Series	Components	PN	Description	Comments	
4 Poles	HCM250	Hoods	T1920240425-002	H24EPR-TGH-XL-4M25	Depends on cable diameter	
		Housings	T1930240000-000	H24EPR-AG		
		Female Inserts	T2192503201-000	HCM250-FC	Crimp terminal	
		Male Inserts	T2192503101-000	HCM250-MC	Crimp terminal	
		Frame	T0924049044-100	H24BPR-4P-250-M-FRAME		
			T0924049044-200	H24EPR-4P-250-F-FRAME		
		Female Contacts	T2192502035-000	HCM250-FC-35	Crimp area acc. to DIN EN 46 235	
			T2192502050-000	HCM250-FC-50	Crimp area acc. to DIN EN 46 235	
			T2192502070-000	HCM250-FC-70	Crimp area acc. to DIN EN 46 235	
		Male Contacts	T2192501035-000	HCM250-MC-35	Crimp area acc. to DIN EN 46 235	
			T2192501050-000	HCM250-MC-50	Crimp area acc. to DIN EN 46 235	
			T2192501070-000	HCM250-MC-70	Crimp area acc. to DIN EN 46 235	
		HCM350	Hoods	T1926320163-001	H32BPR-TGXH-4S-M63	
			Housings	T1936320000-000	H32BPR-AG-45	
	Female Inserts		T2193503201-000	HCM350-FC	Crimp terminal	
	Male Inserts		T2193503101-000	HCM350-MC	Crimp terminal	
	Frame		T0924048581-000	H32BRP-4P-350-FRAME		
	Female Contacts		T2193502035-000	HCM350-FC35	Crimp area acc. to DIN EN 46 235	
			T2193502050-000	HCM350-FC-50	Crimp area acc. to DIN EN 46 235	
			T2193502070-000	HCM350-FC-70	Crimp area acc. to DIN EN 46 235	
			T2193502095-000	HCM350-FC-95	Crimp area acc. to DIN EN 46 235	
			T2193502120-000	HCM350-FC-120	Crimp area acc. to DIN EN 46 235	
	Male Contacts		T2193501035-000	HCM350-MC-35	Crimp area acc. to DIN EN 46 235	
			T2193501050-000	HCM350-MC-50	Crimp area acc. to DIN EN 46 235	
		T2193501070-000	HCM350-MC-70	Crimp area acc. to DIN EN 46 235		
		T2193501095-000	HCM350-MC-95	Crimp area acc. to DIN EN 46 235		
T2193501120-000		HCM350-MC-120	Crimp area acc. to DIN EN 46 235			

TE Connectivity's Heavy Duty Connectors

Tools and Accessories

TOOLS AND ACCESSORIES







Crimping tools and remove tools			
<p>Crimp tool Wire range: 0.14-4.0mm² Used for CEM/CEF/DEM/DEF/HEM/HEF contacts</p> <p>Wire range: 1-2.5mm² Used for CMM/DMM/HMM/CMF/DMF/HMF contacts</p>		<p>Crimp tool Wire range: 4.0-10.0mm² Used for CMM/DMM/HMM/CMF/DMF/HMF contacts</p>	
Type	CRIMPBOX-0.14/4.0	Type	CRIMPBOX-4.0/10.0
Part Number	T310000001-000	Part Number	T3100001001-000
<p>Remove tools Used for HEE series remove tools</p>		<p>Remove tools Used for HEEE series remove tools</p>	
Type	REMOV-HEE	Type	REMOV-HEEE
Part Number	T310000002-000	Part Number	T3100000016-000
<p>Remove tools Used for HD/HDD series remove tools</p>		<p>Remove tools Used for CMM/CMF series remove tools</p>	
Type	REMOV-HD	Type	REMOV-MM
Part Number	T310000003-000	Part Number	T3100000013-000
Axial screw tool and crimping tool			
<p>M3 screw driver Used for HA/HE inserts</p>		<p>Tool Used for 100A inserts</p>	
Type	SCREWD-M3	Type	HEXA-D1
Part Number	T310000009-000	Part Number	T3100000010-000
<p>Tool Used for 40A inserts</p>		<p>Crimp tool Wire range: 20AWG-28AWG (0.08mm² - 0.52mm²) CAM/DAM;CAF/DAF</p>	
Type	HEXA-D2	Type	DIGITAL CRIMPING TOOL
Part Number	T3100000012-000	Part Number	CO-0324-000-000
<p>Crimp tool 12AWG-26AWG (3.33mm² - 0.128mm²) CDM/DDM; CDF/DDF; CEM/DEM; CEF/DEF; HDM/HDF; HEM/HEF</p>			
Type	RPC-M23-T-B		
Part Number	T3100000022-000		

Tools & Accessories

TE Connectivity's Heavy Duty Connectors

Tools and Accessories

TOOLS AND ACCESSORIES

<p>Remove tools Used for 5A contacts remove tools</p> 	<p>Remove tools Used for HMN-002 series remove tools</p> 
<p>Type REMOV-5A-M</p>	<p>Type REMOV-HMN-002</p>
<p>Part Number T3100000017-000</p>	<p>Part Number T3100000034-000</p>
<p>Remove tools Used for HMN-D2 series remove tools</p> 	<p>Remove tools Used for HMN-001 series remove tools</p> 
<p>Type REMOV-HMN-D2</p>	<p>Type REMOV-HMN-001</p>
<p>Part Number T3100000035-000</p>	<p>Part Number T3100000036-000</p>
<p>Remove tools Used for HK2/4-006 series remove tools</p> 	<p>Remove tools Used for HD1 DYNAMIC CONTACT series remove tools</p> 
<p>Type REMOVE TOOL-HK2/4-006</p>	<p>Type REMOVE TOOL FOR HD1 DYNAMIC CONTACT</p>
<p>Part Number T3100000037-000</p>	<p>Part Number T3100000038-000</p>

Tools & Accessories

TE Connectivity's Heavy Duty Connectors









Tools and Accessories

Tool	TE-P/N	Type	Picture	CAF/ CAM DAF/ DAM	5A	CDF/ CDM DDF/ DDM HDF/ HDM	10A	CEP/CEM DEF/DEM HEF/HEM	16A	CEP/CEM DEF/DEM HEF/HEM	4mm ²	1.5- 2.5mm ²	4.0- 10mm ²	6.0- 25mm ²	10- 16mm ²	25mm ²	35mm ²	CHF/ CHM CHM	250A	HCM250- FC HCM250- MC	250A	HCM350- FC HCM350- MC	350A	HCM650- FC HCM650- MC	650A	
				0.08- 0.52 mm ²	0.14-2.5 mm ²	0.14- 2.5 mm ²	0.14- 2.5 mm ²	10A	16A	40A	70A	100A	250A	350A	650A											
Crimping tool	CO-0324-000- 000	DIGITAL CRIMPING TOOL		✓																						
	T3100000022- 000	RPC-M23- T-B			✓			✓																		
	T3100000001- 000	CRIMP- BOX-0.14/4				✓		✓																		
	T31000001001- 000	CRIMP- BOX-4/10						✓																		
	T3100000032- 100	CRIMPBOX- E-60kN													✓											
	T3100000032- 000	CRIMPBOX- M-60kN													✓											
	T3100000032- N01	CRIMP- DIE-N-D226																								
	T3100000032- 001	CRIMP- DIE-D226																								
	T3100000032- 002	CRIMP- DIE-D2210																								
	T3100000032- 003	CRIMP- DIE-D2216																								
	T3100000032- 004	CRIMP- DIE-D2225																								
	T3100000033- 100	CRIMPBOX- E-120kN																								
	T3100000033- 000	CRIMPBOX- M-120kN																								

Tools & Accessories

TE Connectivity's Heavy Duty Connectors

Tools and Accessories



Tool	TE-P/N	Type	Picture	CAF/ CAM DAF/ DAM	10A	16A	40A		70A	100A			250A	HCM250- FC HCM250- MC	HCM350- FC HCM350- MC	HCM650- FC HCM650- MC	
				CDF/ CDM DDE/ DDM HDF/ HDM	CEP/CEM DEF/DEM HEF/HEM	CMF/CMM DMF/DMM HMF/HMM	CSF/ CSM HSF/ HSM	CNF/CNM	CHF/ CHM	10- 16mm ²	25mm ²	35mm ²	6-0- 25mm ²	1.5- 2.5mm ²	4.0- 10mm ²	√(only for 25mm ²)	10- 16mm ²
Crimping tool	T3100000033-002	CRIMP- DIE-HD1325		-	-	-	-	-	-	-	-	-	-	-	-	-	
	T3100000033-003	CRIMP- DIE-HD1335		-	-	-	-	-	-	-	-	-	-	-	-	-	-
	T3100000033-004	CRIMP- DIE-HD1350		-	-	-	-	-	-	-	-	-	-	-	-	-	-
	T3100000033-005	CRIMP- DIE-HD1370		-	-	-	-	-	-	-	-	-	-	-	-	-	-
	T3100000033-006	CRIMP- DIE-HD1395		-	-	-	-	-	-	-	-	-	-	-	-	-	-
	T3100000033-007	CRIMP- DIE-HD13120		-	-	-	-	-	-	-	-	-	-	-	-	-	-
	T3100000033-008	CRIMP- DIE-HD13150		-	-	-	-	-	-	-	-	-	-	-	-	-	-
	T3100000033-009	CRIMP- DIE-HD13185		-	-	-	-	-	-	-	-	-	-	-	-	-	-
	T3100000017-000	REMOV-5A-M		√	-	-	-	-	-	-	-	-	-	-	-	-	-
Extraction tool	T3100000003-000	REMOV-HD		-	-	-	-	-	-	-	-	-	-	-	-	-	
	T3100000002-000	REMOV-HE/ HEE		-	√	-	-	-	-	-	-	-	-	-	-	-	
	T3100000016-000	REMOV-HEEE		-	√	-	-	-	-	-	-	-	-	-	-	-	
	T3100000013-000	REMOV-MM		-	-	√	-	-	-	-	-	-	-	-	-	-	
	T3100000034-000	RE- MOV-HMN-002		-	-	-	-	-	√	-	-	-	-	-	-	-	
	T3100000035-000	RE- MOV-HMN-D2		-	-	-	-	-	-	√	-	-	-	-	-	-	
	T3100000036-000	RE- MOV-HMN-001		-	-	-	-	-	-	-	-	-	√	-	-	-	

Tools & Accessories



TE Connectivity's Heavy Duty Connectors

Contacts

Contacts - 5A Series

	Tech Data	Product Image	Wire Gauge		Ø	Stripping Length	Crimp Contacts, Silver-Plated		Crimp Contacts, Gold-Plated	
							Type	PN	Type	PN
5A Contact	Material: Copper Contact resistance: ≤7.5mΩ Terminal: Crimp Connection		0.08-0.21mm ²	AWG 28-24	0.7	4.0mm	CAM-08	T2070001008-000	DAM-08	T2070011008-000
			0.13-0.33mm ²	AWG 26-22	0.9	4.0mm	CAM-13	T2070001013-000	DAM-13	T2070011013-000
			0.33-0.52mm ²	AWG 22-20	1.12	4.0mm	CAM-33	T2070001033-000	DAM-33	T2070011033-000
	Material: Copper Contact resistance: ≤7.5mΩ Terminal: Crimp Connection		0.08-0.21mm ²	AWG 28-24	0.7	4.0mm	CAF-08	T2070002008-000	DAF-08	T2070012008-000
			0.13-0.33mm ²	AWG 26-22	0.9	4.0mm	CAF-13	T2070002013-000	DAF-13	T2070012013-000
			0.33-0.52mm ²	AWG 22-20	1.12	4.0mm	CAF-33	T2070002033-000	DAF-33	T2070012033-000

Contacts - 10A/16A Series



Current (A)	Tech Data	Product Image	Wire Gauge		Stripping Length	Crimp Contacts, Silver-Plated		Crimp Contacts, Gold-Plated	
						Type	PN	Type	PN
10A Contact	Material: copper Contact resistance: ≤5mΩ Terminal: crimp connection		0.14-0.37mm ²	AWG26-22	8mm	CDM-0.3	T2020001002-000	DDM-0.3	T2020011002-000
			0.5mm ²	AWG 20	8mm	CDM-0.5	T2020001005-000	DDM-0.5	T2020011005-000
			0.75mm ²	AWG 18	8mm	CDM-0.75	T2020001008-000	DDM-0.75	T2020011008-000
			1.0mm ²	AWG 18	8mm	CDM-1.0	T2020001010-000	DDM-1.0	T2020011010-000
			1.5mm ²	AWG 16	8mm	CDM-1.5	T2020001015-000	DDM-1.5	T2020011015-000
			2.5mm ²	AWG 14	6.2mm	CDM-2.5	T2020001025-000	DDM-2.5	T2020011025-000
	Material: copper Contact resistance: ≤5mΩ Terminal: crimp connection		0.14-0.37mm ²	AWG26-22	8mm	CDF-0.3	T2020002002-000	DDF-0.3	T2020012002-000
			0.5mm ²	AWG 20	8mm	CDF-0.5	T2020002005-000	DDF-0.5	T2020012005-000
			0.75mm ²	AWG 18	8mm	CDF-0.75	T2020002008-000	DDF-0.75	T2020012008-000
			1.0mm ²	AWG 18	8mm	CDF-1.0	T2020002010-000	DDF-1.0	T2020012010-000
			1.5mm ²	AWG 16	8mm	CDF-1.5	T2020002015-000	DDF-1.5	T2020012015-000
			2.5mm ²	AWG 14	6.2mm	CDF-2.5	T2020002025-000	DDF-2.5	T2020012025-000
16A Contact	Material: Copper Contact resistance: ≤5mΩ Terminal: Crimp Connection		0.14-0.37mm ²	AWG 26-22	7.5mm	CEM-0.3	T2030001002-000	DEM-0.3	T2030011002-000
			0.5mm ²	AWG 20	7.5mm	CEM-0.5	T2030001005-000	DEM-0.5	T2030011005-000
			0.75mm ²	AWG 18	7.5mm	CEM-0.75	T2030001008-000	DEM-0.75	T2030011008-000
			1.0mm ²	AWG 18	7.5mm	CEM-1.0	T2030001010-000	DEM-1.0	T2030011010-000
			1.5mm ²	AWG 16	7.5mm	CEM-1.5	T2030001015-000	DEM-1.5	T2030011015-000
			2.5mm ²	AWG 14	7.5mm	CEM-2.5	T2030001025-000	DEM-2.5	T2030011025-000
	Material: Copper Contact resistance: ≤5mΩ Terminal: Crimp Connection		0.14-0.37mm ²	AWG 26-22	7.5mm	CEF-0.3	T2030002002-000	DEF-0.3	T2030012002-000
			0.5mm ²	AWG 20	7.5mm	CEF-0.5	T2030002005-000	DEF-0.5	T2030012005-000
			0.75mm ²	AWG 18	7.5mm	CEF-0.75	T2030002008-000	DEF-0.75	T2030012008-000
			1.0mm ²	AWG 18	7.5mm	CEF-1.0	T2030002010-000	DEF-1.0	T2030012010-000
			1.5mm ²	AWG 16	7.5mm	CEF-1.5	T2030002015-000	DEF-1.5	T2030012015-000
			2.5mm ²	AWG 14	7.5mm	CEF-2.5	T2030002025-000	DEF-2.5	T2030012025-000
			3.0mm ²	AWG 12	7.5mm	CEF-3.0	T2030002030-000	DEF-3.0	T2030012030-000
			4.0mm ²	AWG 12	7.5mm	CEF-4.0	T2030002040-000	DEF-4.0	T2030012040-000

Contact

TE Connectivity's Heavy Duty Connectors

Contacts

Contacts - 40A Series

Current (A)	Tech Data	Product Image	Wire Gauge			Stripping Length	Crimp Contacts, Silver-Plated		Crimp Contacts, Gold-Plated	
							Type	PN	Type	PN
40A Contact	Material: Copper Contact resistance: $\leq 3m\Omega$ Terminal: Crimp Connection	Male 	1.0mm ²	AWG 18	9.2mm	CMM-1.0	T2040001010-000	DMM-1.0	T2040011010-000	
			1.5mm ²	AWG 16	9.2mm	CMM-1.5	T2040001015-000	DMM-1.5	T2040011015-000	
			2.5mm ²	AWG 14	9.2mm	CMM-2.5	T2040001025-000	DMM-2.5	T2040011025-000	
			4.0mm ²	AWG 12	9.2mm	CMM-4.0	T2040001040-000	DMM-4.0	T2040011040-000	
			6.0mm ²	AWG 10	9.2mm	CMM-6.0	T2040001060-000	DMM-6.0	T2040011060-000	
			10.0mm ²	AWG 7	9.2mm	CMM-10	T2040001100-000	DMM-10.0	T2040011100-000	
		Female 	1.0mm ²	AWG 18	9.2mm	CMF-1.0	T2040002010-000	DMF-1.0	T2040012010-000	
			1.5mm ²	AWG 16	9.2mm	CMF-1.5	T2040002015-000	DMF-1.5	T2040012015-000	
			2.5mm ²	AWG 14	9.2mm	CMF-2.5	T2040002025-000	DMF-2.5	T2040012025-000	
			4.0mm ²	AWG 12	9.2mm	CMF-4.0	T2040002040-000	DMF-4.0	T2040012040-000	
			6.0mm ²	AWG 10	9.2mm	CMF-6.0	T2040002060-000	DMF-6.0	T2040012060-000	
			10.0mm ²	AWG 7	9.2mm	CMF-10	T2040002100-000	DMF-10.0	T2040012100-000	

Contacts - 70A/100A/200A Series















	Tech Data	Product Image	Wire Gauge		ϕ	Stripping Length	Crimp Contacts, Silver-Plated	
							Type	PN
70A Contact	Material: Copper Contact resistance: $\leq 1.5m\Omega$ Terminal: Crimp Connection	Male 	6mm ²	AWG 10	3.5	15mm	CSM-6.0	T2400001060-000
			10mm ²	AWG 7	4.3	15mm	CSM-10	T2400001100-000
			16mm ²	AWG 5	5.5	15mm	CSM-16	T2400001160-000
			25mm ²	AWG 3	7	15mm	CSM-25	T2400001250-000
		Female 	6mm ²	AWG 10	3.5	15mm	CSF-6.0	T2400002060-000
			10mm ²	AWG 7	4.3	15mm	CSF-10	T2400002100-000
			16mm ²	AWG 5	5.5	15mm	CSF-16	T2400002160-000
			25mm ²	AWG 3	7	15mm	CSF-25	T2400002250-000
100A Contact	Material: Copper Contact resistance: $\leq 0.5m\Omega$ Terminal: Crimp Connection	Male 	10mm ²	AWG 7	4.3	20mm	CNM-10	T2050001010-000
			16mm ²	AWG 5	5.5	20mm	CNM-16	T2050001016-000
			25mm ²	AWG 3	7	20mm	CNM-25	T2050001025-000
			35mm ²	AWG 2	8.2	20mm	CNM-35	T2050001035-000
		Female 	10mm ²	AWG 7	4.3	20mm	CNF-10	T2050002010-000
			16mm ²	AWG 5	5.5	20mm	CNF-16	T2050002016-000
			25mm ²	AWG 3	7	20mm	CNF-25	T2050002025-000
			35mm ²	AWG 2	8.2	20mm	CNF-35	T2050002035-000
200A Contact	Material: Copper Contact resistance: $\leq 0.5m\Omega$ Terminal: Crimp Connection	Male 	25mm ²	AWG 3	7	19mm	CHM-25	T2060001025-000
			35mm ²	AWG 2	8.2	20mm	CHM-35	T2060001035-000
			50mm ²	AWG 1	10	22.5mm	CHM-50	T2060001050-000
			70mm ²	AWG 2/0	11.5	22.5mm	CHM-70	T2060001070-000
			85mm ²	AWG 3/0	13.2	22.5mm	CHM-85	T2060001085-000
		Female 	25mm ²	AWG 3	7	19mm	CHF-25	T2060002025-000
			35mm ²	AWG 2	8.2	20mm	CHF-35	T2060002035-000
			50mm ²	AWG 1	10	22.5mm	CHF-50	T2060002050-000
			70mm ²	AWG 2/0	11.5	22.5mm	CHF-70	T2060002070-000
			85mm ²	AWG 3/0	13.2	22.5mm	CHF-85	T2060002085-000

Contacts

TE Connectivity's Heavy Duty Connectors

Contacts

Contacts - High Mating Cycle Series

Mating Cycle	Current(A)	Product Image	Wire Gauge		Insulation Dia. Max Ø	Stripping Length	Crimp Contacts, Silver-Plated		
							Type	PN	
3K	3		0.14-0.3mm ²	AWG 26-22	0.9mm	7.5mm	HEM-0.3	T2030331002-000	
	3		0.14-0.3mm ²	AWG 26-22	0.9mm	7.5mm	HEF-0.3	T2030332002-000	
	40		6.0mm ²	AWG 10	3.5mm	13mm	HSM-6.0	T2400331060-002	
	40		6.0mm ²	AWG 10	3.5mm	13mm	HSF-6.0	T2400332060-002	
5K	5		0.14-0.3mm ²	AWG 26-22	0.9mm	8mm	HDM-0.3	T2020051002-000	
	5		0.14-0.3mm ²	AWG 26-22	0.9mm	8mm	HDF-0.3	T2020052002-000	
	3		0.14-0.3mm ²	AWG 26-22	0.9mm	7.5mm	HEM-0.3	T2030541002-000	
	5		0.75mm ²	AWG 18	1.3mm	7.5mm	HEM-0.75	T2030541008-000	
	8		1.5mm ²	AWG 16	1.75mm	7.5mm	HEM-1.5	T2030541015-000	
	10		2.5mm ²	AWG 14	2.25mm	7.5mm	HEM-2.5	T2030541025-000	
	3		0.14-0.3mm ²	AWG 26-22	0.9mm	7.5mm	HEF-0.3	T2030532002-000	
	5		0.75mm ²	AWG 18	1.3mm	7.5mm	HEF-0.75	T2030532008-000	
	25		4.0mm ²	AWG 12	2.85mm	9.2mm	HMM-4.0,L=35	T2040051040-001	
	40		6.0mm ²	AWG 10	3.5mm	9.2mm	HMM-6.0,L=35	T2040051060-001	
	40		6.0mm ²	AWG 10	3.5mm	9.2mm	HMM-6.0,L=29	T2040051060-000	
	25		4.0mm ²	AWG 12	2.85mm	8.6mm	HMF-4.0	T2040052040-000	
	40		6.0mm ²	AWG 10	3.5mm	8.6mm	HMF-6.0	T2040052060-000	
	80		25mm ²	AWG 3	7mm	13mm	HSM-25	T2400051250-000	
	80		25mm ²	AWG 3	7mm	13mm	HSF-25	T2400052250-000	
	30K	3		0.14-0.3mm ²	AWG 26-22	0.9mm	7.5mm	HEM-0.3	T2030031002-000
		3		0.5mm ²	AWG 20	1.15mm	7.5mm	HEM-0.5	T2030031005-000
		5		0.75mm ²	AWG 18	1.3mm	7.5mm	HEM-0.75	T2030031008-000
6.5		1.0mm ²		AWG 18	1.45mm	7.5mm	HEM-1.0	T2030031010-000	
8		1.5mm ²		AWG 16	1.75mm	7.5mm	HEM-1.5	T2030031015-000	
10		2.5mm ²		AWG 14	2.25mm	7.5mm	HEM-2.5	T2030031025-000	
12		3.0mm ²		AWG 12	2.55mm	7.5mm	HEM-3.0	T2030031030-000	
16		4.0mm ²		AWG 12	2.85mm	7.5mm	HEM-4.0	T2030031040-000	
3			0.14-0.3mm ²	AWG 26-22	0.9mm	7.5mm	HEF-0.3	T2030032002-000	
3			0.5mm ²	AWG 20	1.15mm	7.5mm	HEF-0.5	T2030032005-000	
5			0.75mm ²	AWG 18	1.3mm	7.5mm	HEF-0.75	T2030032008-000	
6.5			1.0mm ²	AWG 18	1.45mm	7.5mm	HEF-1.0	T2030032010-000	
8			1.5mm ²	AWG 16	1.75mm	7.5mm	HEF-1.5	T2030032015-000	
10			2.5mm ²	AWG 14	2.25mm	7.5mm	HEF-2.5	T2030032025-000	
12			3.0mm ²	AWG 12	2.55mm	7.5mm	HEF-3.0	T2030032030-000	
16			4.0mm ²	AWG 12	2.85mm	7.5mm	HEF-4.0	T2030032040-000	

Contacts

TE Connectivity's Heavy Duty Connectors

Contacts

Mating Cycle	Current(A)	Product Image	Wire Gauge		Insulation Dia. Max Ø	Stripping Length	Crimp Contacts, Silver-Plated	
							Type	PN
30K	3		0.14-0.3mm ²	AWG 26-22	0.9mm	7.5mm	HEM-0.3	T2030041002-000
	3		0.5mm ²	AWG 20	1.15mm	7.5mm	HEM-0.5	T2030041005-000
	5		0.75mm ²	AWG 18	1.3mm	7.5mm	HEM-0.75	T2030041008-000
	6.5		1.0mm ²	AWG 18	1.45mm	7.5mm	HEM-1.0	T2030041010-000
	8		1.5mm ²	AWG 16	1.75mm	7.5mm	HEM-1.5	T2030041015-000
	10		2.5mm ²	AWG 14	2.25mm	7.5mm	HEM-2.5	T2030041025-000
	12		3.0mm ²	AWG 12	2.55mm	7.5mm	HEM-3.0	T2030041030-000
	16		4.0mm ²	AWG 12	2.85mm	7.5mm	HEM-4.0	T2030041040-000
	6.5		1.0mm ²	AWG 18	1.45mm	9.2mm	HMM-1.0	T2040021010-000
	8		1.5mm ²	AWG 16	1.75mm	9.2mm	HMM-1.5	T2040021015-000
	10		2.5mm ²	AWG 14	2.25mm	9.2mm	HMM-2.5	T2040021025-000
	25		4.0mm ²	AWG 12	2.85mm	9.2mm	HMM-4.0	T2040021040-000
	40		6.0mm ²	AWG 10	3.5mm	9.2mm	HMM-6.0	T2040021060-000
	50		10.0mm ²	AWG 7	4.3mm	9.2mm	HMM-10.0	T2040021100-000
	6.5		1.0mm ²	AWG 18	1.45mm	8.6mm	HMF-1.0	T2040022010-000
	8		1.5mm ²	AWG 16	1.75mm	8.6mm	HMF-1.5	T2040022015-000
	10		2.5mm ²	AWG 14	2.25mm	8.6mm	HMF-2.5	T2040022025-000
	25		4.0mm ²	AWG 12	2.85mm	8.6mm	HMF-4.0	T2040022040-000
	40		6.0mm ²	AWG 10	3.5mm	8.6mm	HMF-6.0	T2040022060-000
	50		10.0mm ²	AWG 7	4.3mm	8.6mm	HMF-10.0	T2040022100-000
55		10.0mm ²	AWG8	4.3mm	13mm	HSM-10	T2400031100-002	
80		16.0mm ²	AWG6	5.8mm	13mm	HSM-16	T2400031160-002	
55		10.0mm ²	AWG8	4.3mm	13mm	HSF-10	T2400032100-002	
80		16.0mm ²	AWG6	5.8mm	13mm	HSF-16	T2400032160-002	
70		16.0mm ²	AWG6	5.5mm	13mm	HSM-16	T2400031160-000	
100		25.0mm ³	AWG 3	7mm	13mm	HSM-25	T2400031250-000	
70		16.0mm ²	AWG6	5.5mm	13mm	HSF-16	T2400032160-000	
100		25.0mm ³	AWG 3	7mm	13mm	HSM-25	T2400032250-000	

TE Connectivity's Heavy Duty Connectors

Contacts

TE Connectivity's Heavy Duty Connectors HPC Series



Contacts

BENEFITS

- **Easy to plug:** Smart locking system with 180° in line unlocking
- **Reliability:** Lower temperature rise with one piece contact design, providing excellent conduction performance
- **Safety:** Temperature sensor module helps enable timely monitoring the system situation




















KEY FEATURES

- Power transfer range: 1500V/400A/350A/250A/200A
- Single pole with Black and Orange version
- Cable size: 50mm²- 120mm²
- IP67 protection & UL 4128 certification/PPP51090 B
- NTC (Negative Temperature Coefficient) temperature sensor module with 95% accuracy (optional)

TE Connectivity's Heavy Duty Connectors

Contacts












TE Connectivity's Heavy Duty Connectors HPC Series

Solution	Product Image	Wire Gauge	Part Number	Description	Type	Color
HPC 200A		50mm ²	H1111001301-000	HPC-200-050-F-P-BK-01	Female Side	Black
HPC 200A		50mm ²	H1111000301-000	HPC-200-050-F-P-OR-01	Female Side	Orange
HPC 200A/250A		50mm ² /70mm ²	H101100130A-000	HPC-250/200-M-R-BK-01	Male side	Black
HPC 200A/250A		50mm ² /70mm ²	H101100030A-000	HPC-250/200-M-R-OR-01	Male side	Orange
HPC 250A		70mm ²	H1121001401-000	HPC-250-070-F-P-BK-01	Female Side	Black
HPC 250A		70mm ²	H1121000401-000	HPC-250-070-F-P-OR-01	Female Side	Orange
HPC 350A		95mm ²	H1131000501-000	HPC-350-095-F-P-OR-01-A	Female Side	Orange
HPC 350A		95mm ²	H1131001501-000	HPC-350-095-F-P-BK-01-A	Female Side	Black
HPC 350A		95mm ²	H1131010501-000	HPC-350-095-F-P-OR-01-B	Female Side	Orange
HPC 350A		95mm ²	H1131011501-000	HPC-350-095-F-P-BK-01-B	Female Side	Black
HPC 350A		95mm ²	H103110050A-000	HPC-350-M-R-OR-01-A-W	Male side	Orange
HPC 350A		95mm ²	H103110150A-000	HPC-350-M-R-BK-01-A-W	Male side	Black
HPC 350A		95mm ²	H103111050A-000	HPC-350-M-R-OR-01-B-W	Male side	Orange
HPC 350A		95mm ²	H103111150A-000	HPC-350-M-R-BK-01-B-W	Male side	Black
HPC 350A		95mm ²	H103110050C-000	HPC-350-M-R-OR-01-A-S	Male side	Orange
HPC 350A		95mm ²	H103110150C-000	HPC-350-M-R-BK-01-A-S	Male side	Black
HPC 350A		95mm ²	H103111050C-000	HPC-350-M-R-OR-01-B-S	Male side	Orange
HPC 350A		95mm ²	H103111150C-000	HPC-350-M-R-BK-01-B-S	Male side	Black
Temperature sensor		-	20026452-00	High power connector NTC temp sensor	NTC sensor	-


TE Connectivity's Heavy Duty Connectors

Insert Mounting Elements

Insert Mounting Elements

INSERT MOUNTING ELEMENT	Product Image	Set Order	Type	PN
<p>Set Insert mounting with carrier element Set include: Top and base frame</p>		H6B Set	H6B-RAIL-SET	T1870062000-000
		H10B Set	H10B-RAIL-SET	T1870102000-000
		H16B Set	H16B-RAIL-SET	T1870162000-000
		H24B Set	H24B-RAIL-SET	T1870242000-000
		Top	H6B-RAIL-TOP	T1870062101-000
			H10B-RAIL-TOP	T1870102101-000
			H16B-RAIL-TOP	T1870162101-000
			H24B-RAIL-TOP	T1870242101-000
		Base	HB-RAIL-BASE	T1870002201-000
		HB Top	HB-LM-TOP	T1871002101-000
		HB Base	HB-PLM-PM-BASE	T1871002201-000



Insert Mounting Elements




TE Connectivity's Heavy Duty Connectors

Coding Pin

Coding Pin

Product Image	Materials	Type	PN
	Ordinary	CODING-PIN-M3	T0931003003-000
	Stainless Steel	CODING-PIN-M3-S	T0931103003-000
	Ordinary	CODING-PIN-M3-TM	T0931000423-000
	Ordinary	CODING-PIN-M3-TF	T0931006524-000
	Stainless Steel	CODING-PIN-M3-STM	T0932000423-000
	Stainless Steel	CODING-PIN-M3-STF	T0932006524-000



Coding Pin

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H3A Hoods and Housings

H3A INCLUDE METAL AND PLASTIC SHELLS.
LEVERS INCLUDE METAL, PLASTIC AND STAINLESS STEEL.

H3A metal Hoods & Housings	Product Image	Metr.	PG	Type	PN	H3A Thermo-plastic Hoods & Housings	Product Image	Metr.	PG	Type	PN
Top Entry			PG11	H3A-MTG-PG11	T1329030111-000 T1329032111-000	Top Entry			PG11	H3A-TG-PG11	T1329031111-000
		M20		H3A-MTG-M20	T1329030120-000 T1329032120-000			M20		H3A-TG-M20	T1329031120-000
		M25			T1329030125-000						
Side Entry			PG11	H3A-MTG-PG11	T1319030111-000	Side Entry			PG11	H3A-TS-PG11	T1319031111-000
		M20		H3A-MTG-M20	T1319030120-000			M20		H3A-TS-M20	T1319031120-000
Bulkhead Mounting-Bottom Entry		-		H3A-MAG	T1509030000-000	Bulkhead Mounting-Bottom Entry		-		H3A-AG	T1509031100-000
Bulkhead Mounting - Bottom Entry			TIC-LOQ LOCKING		T1509034600-000	Bulkhead Mounting - Side Entry				H3A-AGS	T1509031111-000
				T1509034500-000							
Bulkhead Mounting-Side Entry				H3A-MAG	T1549030000-000	Surface Mounting-Side Entry			PG11	H3A-AGSV-PG11	T1619031111-000
			M16					H3A-AGSV-M16	T1619031116-000		
			M20					H3A-AGSV-M20	T1619031120-000		
Surface Mounting-Side Entry			PG11	H3A-MTG-PG11	T1619030111-000	Cable-to-Cable Hood			PG11	H3A-TGVB-PG11	T1739032111-000 T1739032111-300
			M16	H3A-MAGSV-M16	T1619030116-000			M20		H3A-TGVB-M20	T1739032120-000 T1739032120-300 T1739032120-200
			M20	H3A-MTGVB-M20	T1619030120-000						
Cable-to-Cable Hoods			PG11	H3A-MTG-PG11	T1739030111-000	Protection covers for Housings		Note: For mounted male insert and hood		H3A-KDBP (THERMOPLASTIC)	T1010034100-000
			M20	H3A-MTGVB-M20	T1739030120-000						
			M25		T1736030125-000						
Protection covers for hoods (Thermoplastic)		Note: For mounted male insert and hood		H3A-KDTP-G	T1010034100-000						

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H8A Thermoplastic and H10A & H16A Metal Hoods and Housings

H10A metal Hoods & Housings	Product Image	Metr.	PG	Type	PN	H16A metal Hoods & Housings	Product Image	Metr.	PG	Type	PN	
Hoods: Side Entry			PG16	H10A-TS-PG16	T1319100116-000	Hoods: Side Entry			PG11	H16A-TS-PG11	T1319160111-000	
		M20		H10A-TS-M20	T1319100120-000				PG16	H16A-TS-PG16	T1319160116-000	
			PG21	H10A-TS-PG21	T1319100121-000			M20		H16A-TS-M20	T1319160120-000	
		M25		H10A-TS-M25	T1319100125-000				PG21	H16A-TS-PG21	T1319160121-000	
Hood: Top Entry			PG13.5	H10A-TG-PG13.5	T1329100113-000			M25		H16A-TS-M25	T1319160125-000	
		M16		H10A-TG-M16	T1329100116-100				PG11	H16A-TSH-PG11	T1339160111-000	
			PG16	H10A-TG-PG16	T1329100116-000				PG16	H16A-TSH-PG16	T1339160116-000	
		M20		H10A-TG-M20	T1329100120-000			M20		H16A-TSH-M20	T1339160120-000	
			PG21	H10A-TG-PG21	T1329100121-000				PG21	H16A-TSH-PG21	T1339160121-000	
	M25		H10A-TG-M25	T1329100125-000			M25		H16A-TSH-M25	T1339160125-000		
BULK-HEAD MOUNTED				H10A-AGS	T1509101000-000	Hoods: Top Entry			PG16	H16A-TG-PG16	T1329160116-000	
				H10A-ADMS	T1519101000-000			M20		H16A-TG-M20	T1329160120-000	
Surface Mounted-Side Entry			PG16	H10A-SGRS-PG16	T1619101116-000				PG21	H16A-TG-PG21	T1329160121-000	
		M20		H10A-SGRS-M20	T1619101120-000			M25		H16A-TG-M25	T1329160125-000	
			PG21	H10A-SGRS-PG21	T1619101121-000				PG16	H16A-TGH-PG16	T1349160116-000	
		M25		H10A-SGRS-M25	T1619101125-000			M20		H16A-TGH-M20	T1349160120-000	
			PG16	H10A-SDRMS-PG16	T1629101116-000				PG21	H16A-TGH-PG21	T1349160121-000	
		M20		H10A-SDRMS-M20	T1629101120-000			M25		H16A-TGH-M25	T1349160125-000	
Cable-to-Cable Hoods			PG16	H10A-TBFS-PG16	T1739101116-000		BULK-HEAD MOUNTED				H16A-AGS	T1509161000-000
		M20		H10A-TBFS-M20	T1739101120-000						H16A-ADMS	T1519161000-000
		M25		H10A-TBFS-M25	T1739101125-000					H16A-ADS	T1519162000-000	
									PG16	H16A-SGRS-PG16	T1619161116-000	
									M20	H16A-SGRS-M20	T1619161120-000	
									PG21	H16A-SGRS-PG21	T1619161121-000	
									M25	H16A-SGRS-M25	T1619161125-000	
										PG16	H16A-SDRMS-PG16	T1629161116-000
									M20	H16A-SDRMS-M20	T1629161120-000	
										PG21	H16A-SDRMS-PG21	T1629161121-000
								M25	H16A-SDRMS-M25	T1629161125-000		
						Surface Mounted-Side Entry			PG16	H16A-SDRS-PG16	T1629163116-000	
								M20		H16A-SDRS-M20	T1629163120-000	
									PG21	H16A-SDRS-PG21	T1629163121-000	
								M25		H16A-SDRS-M25	T1629163125-000	
							Cable-to-Cable Hoods			PG16	H16A-TBFS-PG16	T1739161116-000
										PG21	H16A-TBFS-PG21	T1739161121-000
						M20				H16A-TBFS-M20	T1739161120-000	
								M25		H16A-TBFS-M25	T1739161125-000	
									PG16	H16A-TBFHS-PG16	T1779161116-000	
									PG21	H16A-TBFHS-PG21	T1779161121-000	
								M20	H16A-TBFHS-M20	T1779161120-000		
								M25	H16A-TBFHS-M25	T1779161125-000		
H8A Thermo-plastic Hoods & Housings	Product Image	Metr.	PG	Type	PN							
Hoods: Side Entry		M25		H8A-TG-M25	T1329081125-000	Surface Mounted-Side Entry			PG16	H8A-TS-PG16	T1359090116-000	
				H8A-TG-M25-L	T1329081125-006							
Hoods: Top Entry		M25		H8A-TG-M25-L	T1329081125-006							
Hoods: Top Entry		M32		H8A-TG-M32	T1329081132-000							
Bulkhead Mounted				H8A-AG	T1509081100-000		Cable-to-Cable Hoods			PG16	H16A-TBFS-PG16	T1739161116-000
											PG21	H16A-TBFS-PG21
Housing plasti protection cover				H8A-KDBP	T1009084100-001					M20	H16A-TBFS-M20	T1739161120-000
										M25	H16A-TBFS-M25	T1739161125-000

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65












H32A Metal Hoods and Housings

H32A metal Hoods & Housings	Product Image	Metr.	PG	Type	PN
Hoods: Side Entry			PG16	H32A-TS-PG16	T1319320116-000
		M20		H32A-TS-M20	T1319320120-000
			PG21	H32A-TS-PG21	T1319320121-000
		M25		H32A-TS-M25	T1319320125-000
			PG29	H32A-TS-PG29	T1319320129-000
		M32		H32A-TS-M32	T1319320132-000
Hoods: Top Entry			PG21	H32A-TG-PG21	T1329320121-000
		M25		H32A-TG-M25	T1329320125-000
			PG29	H32A-TG-PG29	T1329320129-000
		M32		H32A-TG-M32	T1329320132-000
		M40		H32A-TG-M40	T1329320140-000
		M50		H32A-TG-M50	T1329320150-000
BULKHEAD MOUNTED		-		H32A-AG	T1419320000-000
Surface Mounted-Side Entry			PG21	H32A-SGR-PG21	T1449320121-000
		M25		H32A-SGR-M25	T1449320125-000
			PG29	H32A-SGR-PG29	T1449320129-000
		M32		H32A-SGR-M32	T1449320132-000
			PG21	H32A-SGR-2PG21	T1449320221-000
		M25		H32A-SGR-2M25	T1449320225-000
			PG29	H32A-SGR-2PG29	T1449320229-000
		M32		H32A-SGR-2M32	T1449320232-000

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H6B Metal Hoods and Housings

H6B metal Hoods	Product Image	Metr.	PG	Type	PN	H6B metal Housings	Product Image	Metr.	PG	Type	PN		
Hoods: Side Entry			PG11	H6B-TS-PG11	T1310060111-000	Bulkhead Mounted				H6B-AG	T1500063000-000		
			PG13.5	H6B-TS-PG13.5	T1310060113-000					H6B-ADMS	T1510062000-000		
			PG16	H6B-TS-PG16	T1310060116-000					H6B-ADS	T1510062100-000		
			PG21	H6B-TS-PG21	T1310060121-000					H6B-AD	T1510063000-000		
										H6B-ADM	T1510063100-000		
		M16	H6B-TS-M16	T131061116-000	Bulkhead Mounted without Seal and Gasket				H6B-AG-RO	T1520060000-001			
		M20	H6B-TS-M20	T1310060120-000									
		M25	H6B-TS-M25	T1310060125-000									
	Hoods: Top Entry			PG13.5	H6B-TSH-PG13.5	T1330060113-000	Bulkhead Mounted Plastic Single Locking				H6B-AG-SL-LB	T1500064000-000	
				M16	H6B-TSH-M16	T1330060106-000							
			PG16	H6B-TSH-PG16	T1330060116-000	Surface Mounted-Side Entry							
			PG21	H6B-TSH-PG21	T1330060121-000								
			PG29	H6B-TSH-PG29	T1330060129-000								
			M20	H6B-TSH-M20	T1330060120-000								
			M25	H6B-TSH-M25	T1330060125-000								
		M32	H6B-TSH-M32	T1330060132-000									
	M40	H6B-TSH-M40	T1330060140-000										
Hoods: Top Entry			PG13.5	H6B-TG-PG13.5	T1320060113-000	Surface Mounted-Side Entry			PG13.5	H6B-SGR-PG13.5	T1610063113-000		
			PG16	H6B-TG-PG16	T1320060116-000				PG16	H6B-SGR-PG16	T1610063116-000		
			PG21	H6B-TG-PG21	T1320060121-000				M20	H6B-SGR-M20	T1610063120-000		
			M20	H6B-TG-M20	T1320060120-000				PG21	H6B-SGR-PG21	T1610063121-000		
			M25	H6B-TG-M25	T1320060125-000				M25	H6B-SGR-M25	T1610063125-000		
			M32	H6B-TG-M32	T1320060132-000				PG13.5	H6B-SGRS-PG13.5	T1610062113-000		
									PG16	H6B-SGRS-PG16	T1610062116-000		
								M20	H6B-SGRS-M20	T1610062120-000			
								M25	H6B-SGRS-M25	T1610062125-000			
			PG21	H6B-TGH-PG21	T1340060121-000				PG13.5	H6B-SDR-PG13.5	T1620063113-000		
			PG29	H6B-TGH-PG29	T1340060129-000				PG16	H6B-SDR-PG16	T1620063116-000		
			M20	H6B-TGH-M20	T1340060120-000				M20	H6B-SDR-M20	T1620063120-000		
			M25	H6B-TGH-M25	T1340060125-000				PG21	H6B-SDR-PG21	T1620063121-000		
			M30	H6B-TGH-M30	T1340060130-000				M25	H6B-SDR-M25	T1620063125-000		
		M32	H6B-TGH-M32	T1340060132-000		PG16	H6B-SDRM-PG16	T1620064116-000					
		M40	H6B-TGH-M40	T1340060140-000		M20	H6B-SDRM-M20	T1620064120-000					
					M20	H6B-SDRS-M20	T1620062120-000						
Cable-to-Cable Hood			PG13.5	H6B-TBF-PG13.5	T1730063113-000	Surface Mounted-Side Entry			PG16	H6B-TBF-PG16	T1730063116-000		
			M20	H6B-TBF-M20	T1730062120-000				PG21	H6B-TBF-PG21	T1730063121-000		
			M25	H6B-TBF-M25	T1730062125-000				PG29	H6B-TBF-PG29	T1730063129-000		
			M32	H6B-TBF-M32	T1730062132-000				M32	H6B-TBF-M32	T1730063132-000		
			PG16	H6B-TBF-PG16	T1730063116-000				PG16	H6B-TBFHS-PG16	T1770062116-000		
			M20	H6B-TBF-M20	T1730063120-000				M20	H6B-TBFHS-M20	T1770062120-000		
			M25	H6B-TBF-M25	T1730063125-000				M25	H6B-TBFHS-M25	T1770062125-000		
			M32	H6B-TBF-M32	T1730063132-000				PG21	H6B-TBFHS-PG21	T1770062121-000		
			M20	H6B-TBFHS-M20	T1770062120-000				M25	H6B-TBFHS-M25	T1770062125-000		
			PG21	H6B-TBFHS-PG21	T1770062121-000				PG29	H6B-TBFHS-PG29	T1770062129-000		
			M32	H6B-TBFHS-M32	T1770062132-000				M32	H6B-TBFHS-M32	T1770062132-000		
			M20	H6B-TBFH-M20	T1770063120-000				PG21	H6B-TBFH-PG21	T1770063121-000		
			PG21	H6B-TBFH-PG21	T1770063121-000				M25	H6B-TBFH-M25	T1770063125-000		
			M25	H6B-TBFH-M25	T1770063125-000				PG29	H6B-TBFH-PG29	T1770063129-000		
			M32	H6B-TBFH-M32	T1770063132-000				M32	H6B-TBFH-M32	T1770063132-000		
			PG16	H6B-SGRH-PG16	T1770063116-000								

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H6BE Thermo-plastic Hoods and Housings	Product Image	Metr.	PG	Type	PN
Cable-to-Cable Hood (Frame included)		M32		H6BEP-TG-TBF-M32	T122E061132-001
Cable-to-Cable Housing (Frame included)		M32		H6BEP-TBF-M32	T181E061132-000
Hood:Side Entry (Frame included)		M40		H6BEP-TS-M40	T121E061140-000
Cable-to-Cable Housing (Frame included)		2M32		H6BEP-TBF-2M32	T181E061232-000
Bulkhead Mounting housing with 4 Bolts (Frame included)		-		H6BEP-AG-BO	T142E061000-000
Bulkhead mounted housing (Frame included)		-		H6BEP-AG	T141E061000-000
Hood plastic protection cover		-		H6BE-KDP-WLS	T101E066000-000
		-		H6BE-KDP-WLS-NY	T102E066000-000
Housing plastic protection cover		-		H6BE-KDP	T100E066000-000

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H10B Metal Hoods and Housings

H10B metal Hoods	Product Image	Metr.	PG	Type	PN	H10B metal Housings	Product Image	Metr.	PG	Type	PN	
Hoods: Side Entry			PG13.5	H10B-TS-PG13.5	T1210100113-000	Bulkhead Mounted				H10B-AGS	T1410101000-000	
			PG16	H10B-TS-PG16	T1210100116-000					H10B-AG	T1410102000-000	
		M20		H10B-TS-M20	T1210100120-000	Bulkhead Mounting with 4 Bolts				H10B-AG-BO	T1420100000-000	
			PG21	H10B-TS-PG21	T1210100121-000					H10B-AD-BO	T1430100000-000	
		M25		H10B-TS-M25	T1210100125-000					H10B-ADM-BO	T1430101000-000	
		M32		H10B-TS-M32	T1210100132-000	Bulkhead Mounted without Seal and Gasket				H10B-AG-RO	T1430101000-000	
		PG16	H10B-TSH-PG16	T1230100116-000					H10B-AG-SL H10B-AG-SL, ONE RIB	T1410100000-000		
		M20		H10B-TSH-M20	T1230100120-000	Bulkhead Mounted Plastic Double Locking					T1410100000-001	
		PG21	H10B-TSH-PG21	T1230100121-000								
		M25		H10B-TSH-M25	T1230100125-000							
	PG29	H10B-TSH-PG29	T1230100129-000									
	M32		H10B-TSH-M32	T1230100132-000								
Hoods: Top Entry			PG13.5	H10B-TG-PG13.5	T1220100113-000	Surface Mounted-Side Entry			PG16	H10B-SGRS-PG16	T1440101116-000	
			PG16	H10B-TG-PG16	T1220100116-000				M20	H10B-SGRS-M20	T1440101120-000	
		M20		H10B-TG-M20	T1220100120-000				PG21	H10B-SGRS-PG21	T1440101121-000	
			PG21	H10B-TG-PG21	T1220100121-000				M25	H10B-SGRS-M25	T1440101125-000	
		M25		H10B-TG-M25	T1220100125-000				PG16	H10B-SGR-PG16	T1440102116-000	
		M32		H10B-TG-M32	T1220100132-000		M20	H10B-SGR-M20	T1440102120-000			
		M36		H10B-TG-M36	T1220100136-000		PG21	H10B-SGR-PG21	T1440102121-000			
							M25	H10B-SGR-M25	T1440102125-000			
							M25	H10B-SGR-BO-M25	T1450100125-000			
							PG16	H10B-SDR-BO-PG16	T1460100116-000			
Side Entry Housings with Levers			PG16	H10B-TGH-PG16	T1240100116-000	Bulkhead Mounting with 4 Bolts			M20	H10B-SDR-BO-M20	T1460100120-000	
		M20		H10B-TGH-M20	T1240100120-000				PG21	H10B-SDR-BO-PG21	T1460100121-000	
			PG21	H10B-TGH-PG21	T1240100121-000				M25	H10B-SDR-BO-M25	T1460100125-000	
		M25		H10B-TGH-M25	T1240100125-000				PG16	H10B-SDRM-BO-PG16	T1460101116-000	
			PG29	H10B-TGH-PG29	T1240100129-000				M20	H10B-SDRM-BO-M20	T1460101120-000	
		M30		H10B-TGH-M30	T1240100130-000		PG21	H10B-SDRM-BO-PG21	T1460101121-000			
		M32		H10B-TGH-M32	T1240100132-000		M25	H10B-SDRM-BO-M25	T1460101125-000			
		M40		H10B-TGH-M40	T1240100140-000							
Side Entry Housings with Levers			PG16	H10B-TSB-PG16	T1250102116-000	Surface Mounted-Side Entry			PG21	H10B-SGRHS-PG21	T1470101121-000	
		M20		H10B-TSB-M20	T1250102120-000				PG29	H10B-SGRHS-PG29	T1470101129-000	
		M25		H10B-TSB-M25	T1250102125-000				M32	H10B-SGRHS-M32	T1470101132-000	
			PG16	H10B-TGB-PG16	T1260102116-000				PG16	H10B-SGRH-PG16	T1470102116-000	
		M20		H10B-TGB-M20	T1260102120-000				PG21	H10B-SGRH-PG21	T1470102121-000	
		PG21	H10B-TGB-PG21	T1260102121-000		M25	H10B-SGRH-M25	T1470102125-000				
		M25		H10B-TGB-M25	T1260102125-000		PG29	H10B-SGRH-PG29	T1470102129-000			
Side Entry Housings with Levers			PG21	H10B-TSBH-PG21	T1270102121-000	Bulkhead Mounting with 4 Bolts			PG21	H10B-SDRH-BO-PG21	T1490100121-000	
		M25		H10B-TSBH-M25	T1270102125-000				M25	H10B-SDRH-BO-M25	T1490100125-000	
		M32		H10B-TSBH-M32	T1270102132-000				PG29	H10B-SDRH-BO-PG29	T1490100129-000	
		M40		H10B-TSBH-M40	T1270102140-000				M32	H10B-SDRH-BO-M32	T1490100132-000	
			PG21	H10B-TGBH-PG21	T1280102121-000					PG21	H10B-SDRHM-BO-PG21	T1490101121-000
		M25		H10B-TGBH-M25	T1280102125-000		PG29	H10B-SDRHM-BO-PG29	T1490101129-000			
		PG29	H10B-TGBH-PG29	T1280102129-000		M32	H10B-SDRHM-BO-M32	T1490101132-000				
	Side Entry Housings with Levers			PG16	H10B-TSBS-PG16	T1250103116-000	Cable-to-Cable Hood			M20	H10B-TBFS-PG16	T1710101116-000
			PG21	H10B-TSBS-PG21	T1250103121-000				M25	H10B-TBFS-M25	T1710101125-000	
M20				H10B-TSBS-M20	T1250103120-000				PG16	H10B-TBF-PG16	T1710102116-000	
M25				H10B-TSBS-M25	T1250103125-000				M20	H10B-TBF-M20	T1710102120-000	
			PG16	H10B-TGBS-PG16	T1260103116-000				M25	H10B-TBF-M25	T1710102125-000	
		M20		H10B-TGBS-M20	T1260103120-000		PG16	H10B-TBF-LB-PG16	T1730103116-000			
		M25		H10B-TGBS-M25	T1260103125-000		M20	H10B-TBF-LB-M20	T1730103120-000			
Side Entry Housings with Levers			PG21	H10B-TSBS-PG21	T1250103121-000	Cable-to-Cable Hood			M25	H10B-TBFH-PG16	T1750101125-000	
		M25		H10B-TSBS-M25	T1250103125-000				M25	H10B-TBFH-M25	T1750101125-000	
			PG29	H10B-TSBS-PG29	T1270103129-000					PG21	H10B-TBFHS-PG21	T1750101121-000
		M32		H10B-TSBS-M32	T1270103132-000				PG29	H10B-TBFHS-PG29	T1750101129-000	
			PG21	H10B-TGBHS-PG21	T1280103121-000				M32	H10B-TBFHS-M32	T1750101132-000	
		M25		H10B-TGBHS-M25	T1280103125-000			PG16	H10B-TBFH-PG16	T1750102116-000		
		PG29	H10B-TGBHS-PG29	T1280103129-000			PG21	H10B-TBFH-PG21	T1750102121-000			

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H10B Metal Hoods and Housings

H10B metal Hoods	Product Image	Metr.	PG	Type	PN	H10B metal Housings	Product Image	Metr.	PG	Type	PN		
Hoods: Side Entry			PG13.5	H10B-TS-RO-PG13.5	T1310100113-000	Bulkhead Mounted				H10B-AG-LB	T1500103000-000		
			PG16	H10B-TS-RO-PG16	T1310100116-000					H10B-AD-LB	T1510103000-000		
			PG21	H10B-TS-RO-PG21	T1310100121-000					H10B-ADM-LB	T1510103001-000		
		M16		H10B-TS-RO-M16	T1310100016-000				PG16	H10B-SGR-LB-PG16	T1610103116-000		
		M20		H10B-TS-RO-M20	T1310100120-000			M20		H10B-SGR-LB-M20	T1610103120-000		
		M25		H10B-TS-RO-M25	T1310100125-000		PG21	H10B-SGR-LB-PG21	T1610103121-000				
		M20		H10B-TSH-RO-M20	T1330100120-000		M25		H10B-SGR-LB-M25	T1610103125-000			
		M25		H10B-TSH-RO-M25	T1330100125-000			PG21	H10B-SGRH-LB-PG21	T1650103121-000			
		M32		H10B-TSH-RO-M32	T1330100132-000			PG29	H10B-SGRH-LB-PG29	T1650103129-000			
				PG21	H10B-TSH-RO-PG21	T1330100121-000		M32		H10B-SGRH-LB-M32	T1650103132-000		
Hoods: Top Entry			PG21	H10B-TG-RO-PG21	T1320100121-000	Surface Mounted-Side Entry				H10B-SGRS-LB-PG16	T1610102116-000		
			PG16	H10B-TG-RO-PG16	T1320100116-000				M20		H10B-SGRS-LB-M20	T1610102120-000	
		M20		H10B-TG-RO-M20	T1320100120-000				PG21	H10B-SGRS-LB-PG21	T1610102121-000		
		M25		H10B-TG-RO-M25	T1320100125-000				M25		H10B-SGRS-LB-M25	T1610102125-000	
		M32		H10B-TG-RO-M32	T1320100132-000				PG16	H10B-SDR-LB-PG16	T1620103116-000		
				PG21	H10B-TGH-RO-PG21			T1340100121-000		M20		H10B-SDR-LB-M20	T1620103120-000
				PG29	H10B-TGH-RO-PG29			T1340100129-000			PG21	H10B-SDR-LB-PG21	T1620103121-000
		M25		H10B-TGH-RO-M25	T1340100125-000				M25		H10B-SDR-LB-M25	T1620103125-000	
		M32		H10B-TGH-RO-M32	T1340100132-000					PG16	H10B-SDRM-LB-1PG16	T1620103416-000	
										PG21	H10B-SDRM-LB-PG21	T1620103421-000	
Housings: Top Entry			PG21	H10B-TSBH-LB-PG21	T1370102121-000		M20		H10B-SDRM-LB-M20	T1620103420-000			
			PG29	H10B-TSBH-LB-PG29	T1370102129-000		M25		H10B-SDRM-LB-1M25	T1620103425-000			
			PG21	H10B-TBFH-LB-PG21	T1770103121-000			PG21	H10B-SDRH-LB-PG21	T1660103121-000			
		M25		H10B-TBFH-LB-M25	T1770103125-000		M25		H10B-SDRH-LB-M25	T1660103125-000			
			PG29	H10B-TBFH-LB-PG29	T1770103129-000			PG29	H10B-SDRH-LB-PG29	T1660103129-000			
		M32		H10B-TBFH-LB-M32	T1770103132-000		M32		H10B-SDRH-LB-M32	T1660103132-000			
							PG21	H10B-SDRHM-LB-PG21	T1660103321-000				
							PG29	H10B-SDRHM-LB-PG29	T1660103329-000				
						M32		H10B-SDRHM-LB-M32	T1660103332-000				
						M25		H10B-SDRHS-LB-M25	T1660102125-000				
						M25		H10B-SDRS-LB-M25	T1620102125-000				

H10BEP Thermo-plastic Hoods and Housings	Product Image	Metr.	PG	Type	PN
Hood: TOP Entry (Frame included)-high construction		M32		H10BEP-TGH-M32	T124E101132-000
Hood: TOP Entry (Frame included)-low construction		M32		H10BEP-TG-M32	T122E101132-000
Bulkhead mounted housing (Frame included)		-		H10BEP-AG	T141E101000-000

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H16B Metal Hoods and Housings













H16B metal Hoods	Product Image	Metr.	PG	Type	PN	H16B metal Housings	Product Image	Metr.	PG	Type	PN	
Hoods: Side Entry			PG16	H16B-TS-PG16	T1210160116-000	Bulkhead Mounted				H16B-AGS	T1410161000-000	
		M20		H16B-TS-M20	T1210160120-000					H16B-AG	T1410162000-000	
			PG21	H16B-TS-PG21	T1210160121-000	Bulkhead Mounting with 4 Bolts				H16B-AD-BO	T1430160000-000	
		M25		H16B-TS-M25	T1210160125-000					H16B-ADM-BO	T1430161000-000	
			M32		H16B-TS-M32	T1210160132-000	Bulkhead Mounted without Seal and Gasket				H16B-AG-RO	T1420160000-001
		M25		H16B-TSH-M25	T1230160125-000							
	High Construction			M32	H16B-TSH-M32	T1230160132-000	Bulkhead Mounted Plastic Double Locking				H16B-AG-SL	T1410160000-000
				M40	H16B-TSH-M40	T1230160140-000						
				PG21	H16B-TSH-PG21	T1230160121-000	Surface Mounted-Side Entry			PG21	H16B-SGRS-PG21	T1440161121-000
				PG29	H16B-TSH-PG29	T1230160129-000				M25	H16B-SGRS-M25	T1440161125-000
			M25	H16B-TG-PG16	T1220160116-000				PG21	H16B-SGR-PG21	T1440162121-000	
Hoods: Top Entry	Low Construction		M20	H16B-TG-M20	T1220160120-000	Bulkhead Mounting with 4 Bolts			M25	H16B-SGR-M25	T1440162125-000	
			PG21	H16B-TG-PG21	T1220160121-000				PG21	H16B-SGR-BO-PG21	T1450160121-000	
			M25	H16B-TG-M25	T1220160125-000				M25	H16B-SGR-BO-M25	T1450160125-000	
			PG29	H16B-TG-PG29	T1220160129-000				PG21	H16B-SDR-BO-PG21	T1460160121-000	
			M32	H16B-TG-M32	T1220160132-000				M25	H16B-SDR-BO-M25	T1460160125-000	
	High Construction			M36	H16B-TG-M36	T1220160136-000	Surface Mounted-Side Entry			PG21	H16B-SDRM-BO-PG21	T1460161121-000
				PG21	H16B-TGH-PG21	T1240160121-000				M25	H16B-SDRM-BO-M25	T1460161125-000
				M25	H16B-TGH-M25	T1240160125-000				PG21	H16B-SGRH-PG21	T1470162121-000
				PG29	H16B-TGH-PG29	T1240160129-000				M25	H16B-SGRH-M25	T1470162125-000
				M32	H16B-TGH-M32	T1240160132-000				PG29	H16B-SGRH-PG29	T1470162129-000
Cable-to-Cable Hoods			M40	H16B-TGH-M40	T1240160140-000	Side Entry Housings with Two Levers			M32	H16B-SGRH-M32	T1470162132-000	
			PG16	H16B-TBFS-PG16	T1710161116-000				PG21	H16B-SGRHS-PG21	T1470161121-000	
			M20	H16B-TBFS-M20	T1710161120-000				PG29	H16B-SGRHS-PG29	T1470161129-000	
			PG21	H16B-TBFS-PG21	T1710161121-000				M32	H16B-SGRHS-M32	T1470161132-000	
			M25	H16B-TBFS-M25	T1710161125-000				M40	H16B-SGRHS-M40	T1470161140-000	
			PG13.5	H16B-TBF-PG13.5	T1710162113-000				M20	H16B-TSB-M20	T1250162120-000	
			PG21	H16B-TBF-PG21	T1710162121-000				PG21	H16B-TSB-PG21	T1250162121-000	
			M25	H16B-TBF-M25	T1710162125-000				M25	H16B-TSB-M25	T1250162125-000	
			PG29	H16B-TBF-PG29	T1710162129-000				M32	H16B-TSB-M32	T1250162132-000	
			M32	H16B-TBF-M32	T1710162132-000				PG21	H16B-TSBS-PG21	T1250163121-000	
			PG21	H16B-TBFHS-PG21	T1750161121-000				M25	H16B-TSBS-M25	T1250163125-000	
			PG29	H16B-TBFHS-PG29	T1750161129-000				M32	H16B-TSBS-M32	T1250163132-000	
			M32	H16B-TBFH-M32	T1750161132-000				PG21	H16B-TSBH-PG21	T1270162121-000	
			PG21	H16B-TBFH-PG21	T1750162121-000				M25	H16B-TSBH-M25	T1270162125-000	
			M25	H16B-TBFH-M25	T1750162125-000				PG29	H16B-TSBH-PG29	T1270162129-000	
			PG29	H16B-TBFH-PG29	T1750162129-000				M32	H16B-TSBH-M32	T1270162132-000	
			M32	H16B-TBFH-M32	T1750162132-000				M40	H16B-TSBH-M40	T1270162140-000	
			M40	H16B-TBFH-M40	T1750162140-000				PG21	H16B-TSBHS-PG21	T1270163121-000	
									M25	H16B-TSBHS-M25	T1270163125-000	
									PG29	H16B-TSBHS-PG29	T1270163129-000	
					M32	H16B-TSBHS-M32	T1270163132-000					
					M40	H16B-TSBHS-M40	T1270163140-000					

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H16B Metal Hoods and Housings

H16B metal Hoods	Product Image	Metr.	PG	Type	PN	H16B metal Housings	Product Image	Metr.	PG	Type	PN		
Hoods: Side Entry		M20		H16B-TS-RO-M20	T1310160120-000	Bulkhead Mounted				H16B-AGS-LB	T1500162000-000		
			PG21	H16B-TS-RO-PG21	T1310160121-000					H16B-AG-LB	T1500163000-000		
		M25		H16B-TS-RO-M25	T1310160125-000					H16B-ADS-LB	T1510162000-000		
		M32		H16B-TS-RO-M32	T1310160132-000					H16B-ADMS-LB	T1510162001-000		
			PG21	H16B-TSH-RO-PG21	T1330160121-000						H16B-AD-LB	T1510163000-000	
		M25		H16B-TSH-RO-M25	T1330160125-000					H16B-ADM-LB	T1510163001-000		
			PG29	H16B-TSH-RO-PG29	T1330160129-000					H16B-ADM-LB	T1510163002-000		
		M32		H16B-TSH-RO-M32	T1330160132-000								
		M40		H16B-TSH-RO-M40	T1330160140-000								
Hoods: Top Entry			PG13.5	H16B-TG-RO-PG13	T1320160113-000	Surface Mounted-Side Entry				H16B-SGR-LB-PG21	T1610163121-000		
			PG21	H16B-TG-RO-PG21	T1320160121-000					H16B-SGR-LB-M25	T1610163125-000		
		M25		H16B-TG-RO-M25	T1320160125-000								
	M32		H16B-TG-RO-M32	T1320160132-000									
			PG21	H16B-TGH-RO-PG21	T1340160121-000								
		M25		H16B-TGH-RO-M25	T1340160125-000								
		PG29	H16B-TGH-RO-PG29	T1340160129-000									
Cable-to-Cable Hood			PG21	H16B-TBF-LB-PG21	T1730163121-000					H16B-SDR-LB-PG21	T1620163121-000		
		M25		H16B-TBF-LB-M25	T1730163125-000					H16B-SDR-LB-M20	T1620163120-000		
		M32		H16B-TBF-LB-M32	T1730163132-000					H16B-SDR-LB-M25	T1620163125-000		
			PG21	H16B-TBFH-LB-PG21	T1770162121-000					H16B-SDRH-LB-PG21	T1660163121-000		
		PG29	H16B-TBFH-LB-PG29	T1770162129-000					H16B-SDRH-LB-PG29	T1660163129-000			
	M32		H16B-TBFH-LB-M32	T1770162132-000									
	Protection covers for Hoods		-		H16B-KDTP-LB			T1010161500-000					
			-		H16B-KDBP			T1010162100-000					
Top Entry Housings with Two Levers										PG21	H16B-TGB-PG21	T1260162121-000	
										M25	H16B-TGB-M25	T1260162125-000	
											M32	H16B-TGB-M32	T1260162132-000
										PG16	H16B-TGBS-PG16	T1260163116-000	
										PG21	H16B-TGBS-PG21	T1260163121-000	
										M25	H16B-TGBS-M25	T1260163125-000	
										PG21	H16B-TGBH-PG21	T1280162121-000	
										M25	H16B-TGBH-M25	T1280162125-000	
										PG29	H16B-TGBH-PG29	T1280162129-000	
										M32	H16B-TGBH-M32	T1280162132-000	
										M40	H16B-TGBH-M40	T1280162140-000	
										PG21	H16B-TGBHS-PG21	T1280163121-000	
										PG29	H16B-TGBHS-PG29	T1280163129-000	
										M25	H16B-TGBHS-M25	T1280163125-000	
										M32	H16B-TGBHS-M32	T1280163132-000	
										M40	H16B-TGBHS-M40	T1280163140-000	
		Bulkhead Mounting with 4 Bolts									PG21	H16B-SDRH-BO-PG21	T1490160121-000
											PG29	H16B-SDRH-BO-PG29	T1490160129-000
										M25	H16B-SDRH-BO-M25	T1490160125-000	
										M32	H16B-SDRH-BO-M32	T1490160132-000	
										PG21	H16B-SDRHM-BO-PG21	T1490161121-000	
										PG29	H16B-SDRHM-BO-PG29	T1490161129-000	
										M32	H16B-SDRHM-BO-M32	T1490161132-000	
										PG21	H16B-SDRHM-BO-PG21	T1490161221-000	
								PG29	H16B-SDRHM-BO-PG29	T1490161229-000			
								M32	H16B-SDRHM-BO-M32	T1490161232-000			

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H24B Metal Hoods and Housings

H24B metal Hoods	Product Image	Metr.	PG	Type	PN	H24B metal Housings	Product Image	Metr.	PG	Type	PN			
Hoods: Side Entry		M20	PG16	H24B-TS-PG16	T1210240116-000	Bulkhead Mounted		-	-	H24B-AG	T1410242000-000			
			-	-	H24B-AGS			T1410241000-000						
		PG21	H24B-TS-PG21	T1210240121-000	Bulkhead Mounted without Seal and Gasket			-	-	H24B-AG-RO	T1420240000-001			
			M25	H24B-TS-M25				T1210240125-000	Bulkhead Mounted Plastic Double Locking	-	-	H24B-AG-SL	T1410240000-000	
				M32				H24B-TS-M32		T1210240132-000	-	-	-	-
								PG21	H24B-TSH-PG21	T1230240121-000	Surface Mounted-Side Entry		-	PG21
	M25	H24B-TSH-M25		T1230240125-000	M25	H24B-SGRS-M25	T1440241125-000							
		PG29		H24B-TSH-PG29	T1230240129-000	-	PG21	H24B-SGR-PG21	T1440242121-000					
	M25			H24B-TSH-M25	T1230240125-000	M25	H24B-SGR-M25	T1440242125-000						
		M32		H24B-TSH-M32	T1230240132-000	PG21	H24B-SGRHS-PG21	T1470241121-000						
				M40	H24B-TSH-M40	T1230240140-000	PG29	H24B-SGRHS-PG29	T1470241129-000					
		Hoods: Top Entry			PG16	H24B-TG-PG16	T1220240116-000	Side Entry Housings with Two Levers		M32		H24B-SGRHS-M32	T1470241132-000	
PG21	H24B-TG-PG21			T1220240121-000	PG21	H24B-SGRH-PG21	T1470242121-000							
M25	H24B-TG-M25			T1220240125-000	M25	H24B-SGRH-M25	T1470242125-000							
	PG29			H24B-TG-PG29	T1220240129-000	PG29	H24B-SGRH-PG29			T1470242129-000				
				M32	H24B-TG-M32	T1220240132-000	M32			H24B-SGRH-M32		T1470242132-000		
	M40				H24B-TG-M40	T1220240140-000	PG21			H24B-TSB-PG21		T1250242121-000		
			PG21	H24B-TGH-PG21	T1240240121-000	M25	H24B-TSB-M25		T1250242125-000					
				M25	H24B-TGH-M25	T1240240125-000	M32		H24B-TSB-M32	T1250242132-000				
					PG29	H24B-TGH-PG29	T1240240129-000		-	PG16	H24B-TSBH-PG16	T12X0240116-000		
	M32			H24B-TGH-M32		T1240240132-000	PG21		H24B-TSBH-PG21	T1270242121-000				
M36				H24B-TGH-M36	T1240240136-000	PG29	H24B-TSBH-PG29		T1270242129-000					
	M40			H24B-TGH-M40	T1240240140-000	M32	H24B-TSBH-M32		T1270242132-000					
Cable-to-Cable Hoods				PG21	H24B-TBFS-PG21	T1710241121-000	Top Entry Housings with Two Levers		M40	H24B-TSBH-M40	T1270242140-000			
	M25			H24B-TBFS-M25	T1710241125-000	PG21			H24B-TSBS-PG21	T1250243121-000				
	M32		H24B-TBFS-M32	T1710241132-000	M25	H24B-TSBS-M25			T1250243125-000					
	PG21		H24B-TBF-PG21	T1710242121-000	M32	H24B-TSBS-M32			T1250243132-000					
	M25		H24B-TBF-M25	T1710242125-000	M25	H24B-TSBHS-M25			T1270243125-000					
			PG29	H24B-TBF-PG29	T1710242129-000	PG21			H24B-TSBHS-PG21	T1270243121-000				
		M32	H24B-TBF-M32	T1710242132-000	PG29	H24B-TSBHS-PG29		T1270243129-000						
			PG21	H24B-TBFHS-PG21	T1750241121-000	M32		H24B-TSBHS-M32	T1270243132-000					
		M25	H24B-TBFHS-M25	T1750241125-000	M40	H24B-TSBHS-M40		T1270243140-000						
			PG29	H24B-TBFHS-PG29	T1750241129-000	PG21		H24B-TGB-PG21	T1260242121-000					
		M32	H24B-TBFHS-M32	T1750241132-000	M25	H24B-TGB-M25		T1260242125-000						
			PG21	H24B-TBFH-PG21	T1750242121-000	PG29		H24B-TGB-PG29	T1260242129-000					
Hoods: Side Entry		PG21	H24B-TS-RO-PG21	T1310240121-000	Bulkhead Mounted		-	-	H24B-AG-LB	T1500243000-000				
			M25	H24B-TS-RO-M25					T1310240125-000	-	-	H24B-AD-LB	T1510243000-000	
		M32		H24B-TS-RO-M32			T1310240132-000	-	-			H24B-ADM-LB	T1510243100-000	
			PG21	H24B-TSH-RO-PG21			T1330240121-000			Surface Mounted-Side Entry		-	-	PG21
		M25		H24B-TSH-RO-M25			T1330240125-000	M25	H24B-SGR-LB-M25					T1610243125-000
				PG29			H24B-TSH-RO-PG29	T1330240129-000	PG21					H24B-SGRH-LB-PG21
		M32			H24B-TSH-RO-M32	T1330240132-000	PG29	H24B-SGRH-LB-PG29	T1650243129-000					
			M40	H24B-TSH-RO-M40	T1330240140-000	M25	H24B-SGRH-LB-M25	T1650243125-000						
		M25		H24B-TSH-RO-M25	T1330240125-000	M32	H24B-SGRH-LB-M32	T1650243132-000						
			PG29	H24B-TSH-RO-PG29	T1330240129-000	-	-	-	-					

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65












H24B Metal Hoods and Housings

H24B metal Hoods	Product Image	Metr.	PG	Type	PN	H24B metal Housings	Product Image	Metr.	PG	Type	PN	
Hoods: Side Entry			PG21	H24B-TS-RO-PG21	T1310240121-000	Surface Mounting with protection cover			PG21	H24B-SDR-LB-PG21	T1620243121-000	
		M25		H24B-TS-RO-M25	T1310240125-000			M25		H24B-SDR-LB-M25	T1620243125-000	
		M32		H24B-TS-RO-M32	T1310240132-000				PG21	H24B-SDRM-LB-PG21	T1620243421-000	
								M25		H24B-SDRM-LB-M25	T1620243425-000	
			PG21	H24B-TSH-RO-PG21	T1330240121-000				PG21	H24B-SDRH-LB-PG21	T1660243121-000	
		M25		H24B-TSH-RO-M25	T1330240125-000				PG29	H24B-SDRH-LB-PG29	T1660243129-000	
			PG29	H24B-TSH-RO-PG29	T1330240129-000			M32		H24B-SDRH-LB-M32	T1660243132-000	
		M32		H24B-TSH-RO-M32	T1330240132-000				PG21	H24B-SDRHM-LB-PG21	T1660243121-100	
	M40		H24B-TSH-RO-M40	T1330240140-000		PG29	H24B-SDRHM-LB-PG29	T1660243129-100				
						M32		H24B-SDRHM-LB-M32	T1660243132-100			
Hoods: Top Entry			PG21	H24B-TG-RO-PG21	T1320240121-000	Top Entry Housings with Two Levers			PG21	H24B-TGBS-PG21	T1260243121-000	
		M25		H24B-TG-RO-M25	T1320240125-000			M25		H24B-TGBS-M25	T1260243125-000	
			PG29	H24B-TG-RO-PG29	T1320240129-000				PG29	H24B-TGBS-PG29	T1260243129-000	
			PG21	H24B-TGH-RO-PG21	T1340240121-000				M32		H24B-TGBS-M32	T1260243132-000
		M25		H24B-TGH-RO-M25	T1340240125-000				PG21		H24B-TGBHS-PG21	T1280243121-000
			PG29	H24B-TGH-RO-PG29	T1340240129-000				PG29		H24B-TGBHS-PG29	T1280243129-000
		M32		H24B-TGH-RO-M32	T1340240132-000				M25		H24B-TGBHS-M25	T1280243125-000
		M40		H24B-TGH-RO-M40	T1340240140-000				M32		H24B-TGBHS-M32	T1280243132-000
Cable-to-Cable Hoods			PG21	H24B-TBF-LB-PG21	T1730242121-000	Bulkhead Mounting with 4 Bolts				H24B-AD-BO	T1430240000-000	
		M25		H24B-TBF-LB-M25	T1730242125-000					H24B-ADM-BO	T1430241000-000	
		M32		H24B-TBF-LB-M32	T1730242132-000							
			PG21	H24B-TBFH-LB-PG21	T1770243121-000							
			PG29	H24B-TBFH-LB-PG29	T1770243129-000							
Protection Covers for Hoods				H24B-KDTP-LB	T1010241500-000	Surface Mounting protection cover with			PG21	H24B-SDR-BO-PG21	T1460240121-000	
				H24B-KDTP	T1010241200-000			M25		H24B-SDR-BO-M25	T1460240125-000	
								PG21	H24B-SGRM-BO-PG21	T1460241121-000		
								M25		H24B-SGRM-BO-M25	T1460241125-000	
								PG21		H24B-SDRH-BO-PG21	T1490240121-000	
								M25		H24B-SDRH-BO-M25	T1490240125-000	
								PG29		H24B-SDRH-BO-PG29	T1490240129-000	
								M32		H24B-SDRH-BO-M32	T1490240132-000	
									PG21	H24B-SDRHM-BO-PG21	T1490241121-000	
									PG29	H24B-SDRHM-BO-PG29	T1490241129-000	
								M32		H24B-SDRHM-BO-M32	T1490241132-000	

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

H32B Metal Hoods and Housings






H32B with 2 levers on the Hoods & Housings	Product Image	Metr.	PG	Type	PN	H32B with 1 levers on the Hoods & Housings	Product Image	Metr.	PG	Type	PN		
Hoods: Side Entry		M20		H32B-TS-M20	T1210320120-000	Hoods: Side Entry			PG21	H32B-TS-RO-PG21	T1310320121-000		
			PG21	H32B-TS-PG21	T1210320121-000				PG29	H32B-TS-RO-PG29	T1310320129-000		
		M25		H32B-TS-M25	T1210320125-000				M32	H32B-TS-RO-M32	T1310320132-000		
			PG29	H32B-TS-PG29	T1210320129-000				PG36	H32B-TS-RO-PG36	T1310320136-000		
		M32		H32B-TS-M32	T1210320132-000				M40	H32B-TS-RO-M40	T1310320140-000		
			PG36	H32B-TS-PG36	T1210320136-000				M50	H32B-TS-RO-M50	T1310320150-000		
Hoods: Top Entry			PG21	H32B-TG-PG21	T1220320121-000	Hoods: Top Entry			PG21	H32B-TG-RO-PG21	T1320320121-000		
			M25	H32B-TG-M25	T1220320125-000				M25	H32B-TG-RO-M25	T1320320125-000		
			PG29	H32B-TG-PG29	T1220320129-000				PG29	H32B-TG-RO-PG29	T1320320129-000		
		M32		H32B-TG-M32	T1220320132-000				M32	H32B-TG-RO-M32	T1320320132-000		
			PG36	H32B-TG-PG36	T1220320136-000				PG36	H32B-TG-RO-PG36	T1320320136-000		
		M40		H32B-TG-M40	T1220320140-000				M40	H32B-TG-RO-M40	T1320320140-000		
			PG42	H32B-TG-PG42	T1220320142-000				PG42	H32B-TG-RO-PG42	T1320320142-000		
			PG48	H32B-TG-PG48	T1220320148-000				M50	H32B-TG-RO-M50	T1320320150-000		
		M50		H32B-TG-M50	T1220320150-000			Bulkhead Mounted		-	-	H32B-AG-LB	T1500322000-000
		M63		H32B-TG-M63	T1220320163-000					-	-	H32B-AD-LB	T1510322000-000
Hoods: Side Entry with levers			PG21	H32B-TSB-PG21	T1250322121-000	Surface Mounted-Side Entry			PG29	H32B-SGR-LB-PG29	T1610322129-000		
			PG29	H32B-TSB-PG29	T1250322129-000				M32	H32B-SGR-LB-M32	T1610322132-000		
		M32		H32B-TSB-M32	T1250322132-000				PG36	H32B-SGR-LB-PG36	T1610322136-000		
Hoods: Top Entry with levers			PG36	H32B-TGB-PG36	T1260320136-000				M40	H32B-SGR-LB-M40	T1610322140-000		
		M40		H32B-TGB-M40	T1260320140-000				PG42	H32B-SGR-LB-PG42	T1610322142-000		
			PG21	H32B-TGB-PG21	T1260322121-000				M50	H32B-SGR-LB-M50	T1610322150-000		
			PG29	H32B-TGB-PG29	T1260322129-000				PG29	H32B-SDR-LB-PG29	T1620320129-000		
Bulkhead Mounted		-	-	H32B-AG	T1410322000-000				M32	H32B-SDR-LB-M32	T1620322132-000		
		-	-	H32B-AG-BO	T1420320000-000				PG36	H32B-SDR-LB-PG36	T1620320136-000		
		-	-	H32B-AD-BO	T1430320000-000				M40	H32B-SDR-LB-M40	T1620320140-000		
Surface Mounted - Side Entry			PG29	H32B-SGR-PG29	T1440322129-000		PG42	H32B-SDR-LB-PG42	T1620320142-000				
			M32	H32B-SGR-M32	T1440322132-000		M50	H32B-SDR-LB-M50	T1620320150-000				
			PG36	H32B-SGR-PG36	T1440322136-000								
			M40	H32B-SGR-M40	T1440322140-000								
			PG42	H32B-SGR-PG42	T1440322142-000								
Cable-to-Cable Hood			PG21	H32B-TBF-PG21	T1710322121-000								
			PG29	H32B-TBF-PG29	T1710322129-000								
		M32		H32B-TBF-M32	T1710322132-000								
			PG36	H32B-TBF-PG36	T1710322136-000								
	M40		H32B-TBF-M40	T1710322140-000									

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65




H48B Metal Hoods and Housings

H48B metal Hoods and Housings	Product Image	Metr.	PG	Type	PN
Hoods: Side Entry		M25		H48B-TS-RO-M25	T1310480125-000
			PG29	H48B-TS-RO-PG29	T1310480129-000
		M32		H48B-TS-RO-M32	T1310480132-000
			PG36	H48B-TS-RO-PG36	T1310480136-000
		M40		H48B-TS-RO-M40	T1310480140-000
			PG42	H48B-TS-RO-PG42	T1310480142-000
Hoods: Top Entry			PG29	H48B-TG-RO-PG29	T1320480129-000
		M32		H48B-TG-RO-M32	T1320480132-000
			PG36	H48B-TG-RO-PG36	T1320480136-000
		M40		H48B-TG-RO-M40	T1320480140-000
			PG42	H48B-TG-RO-PG42	T1320480142-000
		M50		H48B-TG-RO-M50	T1320480150-000
Bulkhead Mounted		-	-	H48B-AG-LB	T1500482000-000
		-	-	H48B-AD-LB	T1510482000-000
Surface Mounted - Side Entry			PG29	H48B-SGR-LB-PG29	T1610482129-000
		M32		H48B-SGR-LB-M32	T1610482132-000
			PG36	H48B-SGR-LB-PG36	T1610482136-000
		M40		H48B-SGR-LB-M40	T1610482140-000
			PG42	H48B-SGR-LB-PG42	T1610482142-000
Surface Mounted with Cover			PG29	H48B-SDR-LB-PG29	T1620480129-000
		M32		H48B-SDR-LB-M32	T1620480132-000
			PG36	H48B-SDR-LB-PG36	T1620480136-000
		M40		H48B-SDR-LB-M40	T1620480140-000
			PG42	H48B-SDR-LB-PG42	T1620480142-000
	M50		H48B-SDR-LB-M50	T1620480150-000	

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65

EMC Hoods and Housings



EMC Hoods and Housings	Product Image	Metr.	PG	Type	PN	EMC Hoods and Housings	Product Image	Metr.	PG	Type	PN	
Hoods: Side Entry		M20		H6B-TS-M20-EMC	T1310065120-000	Hoods: Top Entry		M20		H10B-TG-RO-EMC-M20	T1325100120-000	
		M16		H10B-TS-RO-EMC-M16	T1315100016-000			M25		H10B-TG-RO-EMC-M25	T1325100125-000	
		M20		H10B-TS-RO-EMC-M20	T1315100120-000				PG16	H10B-TGH-EMC-PG16	T1240105116-000	
		M25		H10B-TS-RO-EMC-M25	T1315100125-000				PG21	H10B-TGH-EMC-PG21	T1240105121-000	
			PG13.5	H10B-TS-RO-EMC-PG13.5	T1315100113-000				PG29	H10B-TGH-EMC-PG29	T1240105129-000	
			PG16	H10B-TS-RO-EMC-PG16	T1315100116-000			M20		H10B-TGH-EMC-M20	T1240105120-000	
			PG21	H10B-TS-RO-EMC-PG21	T1315100121-000			M25		H10B-TGH-EMC-M25	T1240105125-000	
		M20		H10B-TSH-RO-EMC-M20	T1335100120-000			M32		H10B-TGH-EMC-M32	T1240105132-000	
		M25		H10B-TSH-RO-EMC-M25	T1335100125-000			M40		H10B-TGH-EMC-M40	T1240105140-000	
		M32		H10B-TSH-RO-EMC-M32	T1335100132-000				PG21	H10B-TGH-RO-EMC-PG21	T1345100121-000	
			PG21	H10B-TSH-RO-EMC-PG21	T1335100121-000				PG29	H10B-TGH-RO-EMC-PG29	T1345100129-000	
			PG29	H10B-TSH-RO-EMC-PG29	T1335100129-000			M25		H10B-TGH-RO-EMC-M25	T1345100125-000	
			PG16	H10B-TSH-EMC-PG16	T1230105116-000			M32		H10B-TGH-RO-EMC-M32	T1345100132-000	
			PG21	H10B-TSH-EMC-PG21	T1230105121-000				PG21	H16B-TGH-EMCS-PG21	T1130165121-000	
			PG29	H10B-TSH-EMC-PG29	T1230105129-000				PG29	H16B-TGH-EMCS-PG29	T1130165129-000	
		M20		H10B-TSH-EMC-M20	T1230105120-000			M25		H16B-TGH-EMCS-M25	T1130165125-000	
		M25		H10B-TSH-EMC-M25	T1230105125-000			M32		H16B-TGH-EMCS-M32	T1130165132-000	
		M32		H10B-TSH-EMC-M32	T1230105132-000			M40		H16B-TSH-EMCS-M40	T1120165140-000	
		M40		H10B-TSH-EMC-M40	T1230105140-000					H10B-AGS-LB-EMC	T1505102000-000	
			PG21	H16B-TSH-EMC-PG21	T1230165121-000					H10B-AGS-EMC	T1415103000-000	
			PG29	H16B-TSH-EMC-PG29	T1230165129-000					H10B-AG-EMC	T1415102000-000	
		M25		H16B-TSH-EMC-M25	T1230165125-000					H10B-AG-EMCS	T1695100000-000	
		M32		H16B-TSH-EMC-M32	T1230165132-000					H10B-AG-SL-EMC	T1415104000-000	
		M40		H16B-TSH-EMC-M40	T1230165140-000					H6B-AG-EMC	T1505063000-000	
			PG21	H16B-TSBHS-EMC-PG21	T1270165121-000					H6B-AG-SL-EMC	T1505064000-000	
			PG29	H16B-TSBHS-EMC-PG29	T1270165129-000					H16B-AG-EMCS	T1695160000-000	
		M25		H16B-TSBHS-EMC-M25	T1270165125-000					H16B-AG-EMC	T1415162000-000	
		M32		H16B-TSBHS-EMC-M32	T1270165132-000					H16B-AG-SL-EMC	T1415164000-000	
		M40		H16B-TSBHS-EMC-M40	T1270165140-000					H16B-AGS-EMC	T1415163000-000	
			PG21	H24B-TSBHS-EMC-PG21	T1270245121-000					H16B-AG-BO-EMC	T1425160000-000	
			PG29	H24B-TSBHS-EMC-PG29	T1270245129-000					H24B-AG-BO-EMC	T1425240000-000	
		M25		H24B-TSBHS-EMC-M25	T1270245125-000					H24B-AG-EMC	T1415242000-000	
						H24B-AG-SL-EMC	T1415244000-000					
M32		H24B-TSBHS-EMC-M32	T1270245132-000									
M40		H24B-TSBHS-EMC-M40	T1270245140-000									
Bulkhead Mounted								M20		H3A-MTS-EMC-M20	T1319035120-100	
									PG11	H3A-MTG-EMC-PG11	T1329035111-100	
									M20		H3A-MTG-EMC-M20	T1329035120-100
									-	-	H3A-MAG-EMC	T1506033000-000
										-	H3A-MAG-EMC	T1506033000-001
										-	H3A-MAGS-EMC	T1546033000-000
										-	H3A-MAG-S-EMC	T1506032000-000
										-	H3A-MTGVB-M20-EMC	T1739035120-000
									M25		H3A-MTGVB-M25-EMC	T1736033125-000
									M25		H3A-MTG-EMC- M25	T1329035125-000
									M25		H10A-TS-EMC-M25	T1317105125-000
									-	-	H10A-ADMS-EMC	T1516101000-000

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP65





HB (IP65) Series Central lever locking

HB (IP65) Series Central lever locking	Product Image	Standard	Metr.	PG	Type	PN		
Hoods: Side Entry		H16B		PG21	H16B-TSH-RC-PG21	T1390160121-001		
				PG29	H16B-TSH-RC-PG29	T1390160129-001		
			M25		H16B-TSH-RC-M25	T1390160125-001		
			M32		H16B-TSH-RC-M32	T1390160132-001		
			M40		H16B-TSH-RC-M40	T1390160140-001		
		H24B				PG29	H24B-TSH-RCH-PG29	T1230246029-000
						PG29	H24B-TSH-RC-PG29	T1390240129-000
				M32			H24B-TSH-RC-M32	T1390240132-000
				M40			H24B-TSH-RC-M40	T1390240140-000
						PG21	H24B-TSH-RC-PG21	T1390240121-002
						PG29	H24B-TSH-RC-PG29	T1390240129-002
				M25			H24B-TSH-RC-M25	T1390240125-002
				M32			H24B-TSH-RC-M32	T1390240132-002
			M40			H24B-TSH-RC-M40	T1390240140-002	
Bulkhead Mounted		H16B			H16B-AG-RC	T1550160000-001		
		H24B			H24B-AG-RC	T1550240000-000		

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP68

H3APR (IP68) Hoods and Housings

H3APR (IP68) Series	Product Image	Metr.	PG	Type	PN
Hoods: Top entry			PG13.5	H3APR-MTGSW-PG13.5	T1927030113-000
		M20		H3APR-MTGSW-M20	T1927030120-000
Bulkhead Mounted				H3APR-MAGSW	T1937030000-000
				H3APR-MAGS	T1946030000-000
Hoods: Top entry		M16		H3APR-TGC-M16	T1926030116-000
		M20		H3APR-TGC-M20	T1926030120-000
		M25		H3APR-TGC-M25	T1926030125-000
Bulkhead Mounted				H3APR-AGC	T1936030000-000

Note: Please go to te.com for specific drawings and product size

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP68

HBPR (IP68) Hoods and Housings

HBPR (IP68) Series	Product Image	Standard	Metr.	PG	Type	PN
Hoods: Side Entry		H6BPR	M16		H6BPR-TSH-M16	T1910060106-000
				PG16	H6BPR-TSH-PG16	T1910060116-000
			M20		H6BPR-TSH-M20	T1910060120-000
				PG21	H6BPR-TSH-PG21	T1910060121-000
			M25		H6BPR-TSH-M25	T1910060125-000
				PG29	H6BPR-TSH-PG29	T1910060129-000
		H10BPR	M20	PG16	H10BPR-TSH-PG16	T1910100116-000
				PG21	H10BPR-TSH-PG21	T1910100121-000
			M25		H10BPR-TSH-M25	T1910100125-000
				PG29	H10BPR-TSH-PG29	T1910100129-000
		H16BPR	M25	PG21	H16BPR-TSH-PG21	T1910160121-000
				PG29	H16BPR-TSH-PG29	T1910160129-000
			M32		H16BPR-TSH-M32	T1910160132-000
				PG36	H16BPR-TSH-PG36	T1910160136-000
		H24BPR	M40		H16BPR-TSH-M40	T1910160140-000
			M25	PG21	H24BPR-TSH-PG21	T1910240121-000
				PG29	H24BPR-TSH-PG29	T1910240129-000
			M32		H24BPR-TSH-M32	T1910240132-000
				PG36	H24BPR-TSH-PG36	T1910240136-000
			M40		H24BPR-TSH-M40	T1910240140-000
			M50		H24BPR-TSH-M50	T1910240150-000
			M32		H24BPR-TSH-XL-M32	T1910240132-002
			M40		H24BPR-TSH-XL-M40	T1910240140-002
			M50		H24BPR-TSH-XL-M50	T1910240150-002
			M63		H24BPR-TSH-XL-M63	T1910240163-002
				PG29	H24BPR-TSH-XL-PG29	T1910240129-002
				PG36	H24BPR-TSH-XL-PG36	T1910240136-002
				PG42	H24BPR-TSH-XL-PG42	T1910240142-002
	PG48	H24BPR-TSH-XL-PG48	T1910240148-002			
Hoods: Top Entry		H6BPR	M20		H6BPR-TGH-M20	T1920060120-000
				PG21	H6BPR-TGH-PG21	T1920060121-000
			M25		H6BPR-TGH-M25	T1920060125-000
				PG29	H6BPR-TGH-PG29	T1920060129-000
		H10BPR	M32		H6BPR-TGH-M32	T1920060132-000
			M20	PG16	H10BPR-TGH-PG16	T1920100116-000
				PG21	H10BPR-TGH-PG21	T1920100121-000
			M25		H10BPR-TGH-M25	T1920100125-000
		H16BPR		PG29	H10BPR-TGH-PG29	T1920100129-000
			M32		H10BPR-TGH-M32	T1920100132-000
			M40		H10BPR-TGH-M40	T1920100140-000
			M25	PG21	H16BPR-TGH-PG21	T1920160121-000
				PG29	H16BPR-TGH-PG29	T1920160129-000
			M32		H16BPR-TGH-M32	T1920160132-000
		H24BPR		PG36	H16BPR-TGH-PG36	T1920160136-000
			M40		H16BPR-TGH-M40	T1920160140-000
			M50		H16BPR-TGXH-M50	T1920160150-001
			M63		H16BPR-TGXH-M63	T1920160163-001
			M25	PG21	H24BPR-TGH-PG21	T1920240121-000
				PG29	H24BPR-TGH-PG29	T1920240129-000
			M32		H24BPR-TGH-M32	T1920240132-000
				PG36	H24BPR-TGH-PG36	T1920240136-000
			M40		H24BPR-TGH-M40	T1920240140-000
			M50		H24BPR-TGXH-M50	T1920240150-001
			M63		H24BPR-TGXH-M63	T1920240163-001
			M32		H24BPR-TGH-XL-M32	T1920240132-002
			M40		H24BPR-TGH-XL-M40	T1920240140-002
			M50		H24BPR-TGH-XL-M50	T1920240150-002
		M63		H24BPR-TGH-XL-M63	T1920240163-002	
		H32BPR		PG29	H24BPR-TGH-XL-PG29	T1920240129-002
	PG36		H24BPR-TGH-XL-PG36	T1920240136-002		
	PG42		H24BPR-TGH-XL-PG42	T1920240142-002		
	PG48		H24BPR-TGH-XL-PG48	T1920240148-002		
M63			H32BPR-TGXH-4S-M63	T1926320163-001		
M50			H32BPR-TGXH-4S-M50	T1926320150-001		

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP68

HBPR (IP68) Hoods and Housings

HBPR (IP68) Series	Product Image	Standard	Metr.	PG	Type	PN
Bulkhead Mounted		H6BPR	-		H6BPR-AG	T1930060000-000
		H10BPR			H10BPR-AG	T1930100000-000
		H16BPR			H16BPR-AG	T1930160000-000
		H24BPR			H24BPR-AG	T1930240000-000
		H32BPR			H32BPR-AG-4S	T1936320000-000
		H32BPR			H32BPR-AG-4S	T1936322000-000
Straight Surface Mount		H10BPR		PG21	H10BPR-SGRH-PG21	T1950100121-000
			M25		H10BPR-SGRH-M25	T1950100125-000
				PG29	H10BPR-SGRH-PG29	T1950100129-000
			M32		H10BPR-SGRH-M32	T1950100132-000
		H16BPR		PG21	H16BPR-SGRH-PG21	T1950160121-000
				PG29	H16BPR-SGRH-PG29	T1950160129-000
				PG36	H16BPR-SGRH-PG36	T1950160136-000
			M25		H16BPR-SGRH-M25	T1950160125-000
			M32		H16BPR-SGRH-M32	T1950160132-000
			M40		H16BPR-SGRH-M40	T1950160140-000
		H24BPR	M50		H24BPR-SGRH-TM50	T1950240150-000
			M25		H24BPR-SGRH-2TM25	T1950240225-000
			M32		H24BPR-SGRH-2TM32	T1950240232-000
			M40		H24BPR-SGRH-2TM40	T1950240240-000
			M25		H24BPR-SGRH-3TM25	T1950240325-000
M32			H24BPR-SGRH-3TM32	T1950240332-000		
Cover		H6BPR	-		H6BPR-KDBM	T1990060000-000
		H10BPR			H10BPR-KDBM	T1990100000-000
		H16BPR			H16BPR-KDBM	T1990160000-000
		H24BPR			H24BPR-KDBM	T1990240000-000

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP68

HBPR (IP68) Series Central locking





HBPR (IP68) Series Central locking	Product Image	Standard	Metr.	PG	Type	PN	
Hoods: Side Entry		H6BPR		PG16	H6BPR-TSHC-PG16	T1912060116-000	
			M20		H6BPR-TSHC-M20	T1912060120-000	
				PG21	H6BPR-TSHC-PG21	T1912060121-000	
			M25		H6BPR-TSHC-M25	T1912060125-000	
		H10BPR		PG16		H10BPR-TSHC-PG16	T1912100116-000
			M20			H10BPR-TSHC-M20	T1912100120-000
				PG21		H10BPR-TSHC-PG21	T1912100121-000
			M25			H10BPR-TSHC-M25	T1912100125-000
				PG29		H10BPR-TSHC-PG29	T1912100129-000
			M32			H10BPR-TSHC-M32	T1912100132-000
		H16BPR		PG21		H16BPR-TSHC-PG21	T1912160121-000
			M25			H16BPR-TSHC-M25	T1912160125-000
				PG29		H16BPR-TSHC-PG29	T1912160129-000
			M32			H16BPR-TSHC-M32	T1912160132-000
			M40			H16BPR-TSHC-M40	T1912160140-000
		H24BPR		PG21		H24BPR-TSHC-PG21	T1912240121-000
			M25			H24BPR-TSHC-M25	T1912240125-000
				PG29		H24BPR-TSHC-PG29	T1912240129-000
			M32			H24BPR-TSHC-M32	T1912240132-000
			M40		PG36	H24BPR-TSHC-PG36	T1912240136-000
				H24BPR-TSHC-M40	T1912240140-000		
Hoods: Top Entry		H6BPR		PG16	H6BPR-TGHC-PG16	T1922060116-000	
			M20		H6BPR-TGHC-M20	T1922060120-000	
				PG21	H6BPR-TGHC-PG21	T1922060121-000	
			M25		H6BPR-TGHC-M25	T1922060125-000	
				PG29	H6BPR-TGHC-PG29	T1922060129-000	
			M32		H6BPR-TGHC-M32	T1922060132-000	
		H10BPR	M40			H6BPR-TGHC-M40	T1922060140-000
			M16			H6BPR-THC-2M16	T1942060216-000
				PG16		H10BPR-TGHC-PG16	T1922100116-000
			M20			H10BPR-TGHC-M20	T1922100120-000
				PG21		H10BPR-TGHC-PG21	T1922100121-000
			M25			H10BPR-TGHC-M25	T1922100125-000
			PG29			H10BPR-TGHC-PG29	T1922100129-000
			M32			H10BPR-TGHC-M32	T1922100132-000
			M20			H10BPR-TGHC-2M20	T1922100220-000
		H16BPR		PG21		H16BPR-TGHC-PG21	T1922160121-000
			M25			H16BPR-TGHC-M25	T1922160125-000
				PG29		H16BPR-TGHC-PG29	T1922160129-000
			M32			H16BPR-TGHC-M32	T1922160132-000
				PG36		H16BPR-TGHC-PG36	T1922160136-000
			M40			H16BPR-TGHC-M40	T1922160140-000
			M25			H16BPR-TGHC-2M25	T1922160225-000
		H24BPR		PG21		H24BPR-TGHC-PG21	T1922240121-000
			M25			H24BPR-TGHC-M25	T1922240125-000
				PG29		H24BPR-TGHC-PG29	T1922240129-000
M32				H24BPR-TGHC-M32	T1922240132-000		
	PG36			H24BPR-TGHC-PG36	T1922240136-000		
	M40			H24BPR-TGHC-M40	T1922240140-000		
		PG29		H24BPR-TGHC-2PG29	T1922240129-001		
Bulkhead Mounted		H6BPR			H6BPR-AGC	T1932060000-000	
		H10BPR			H10BPR-AGC	T1932100000-000	
		H16BPR			H16BPR-AGC	T1932160000-000	
		H24BPR			H24BPR-AGC	T1932240000-000	
Cover		H24BPR			H24BPRC-KDBP	T1990240010-000	

Hoods & Housings

TE Connectivity's Heavy Duty Connectors

Hoods and Housings IP68

HBPR (IP68) Series Panel Installing

HBPR (IP68) Series Panel Installing	Product Image	Standard	Metr.	PG	Type	PN
Hoods: Side Entry		H24BPR	M40		H24BPR-TSA-M40	T1160242140-000
Hoods: Top Entry		H6BPR		PG16	H6BPR-TGMA-GR-PG16	T1170062116-000
			M20		H6BPR-TGMA-GR-M20	T1170062120-000
			M25	PG21	H6BPR-TGMA-GR-PG21	T1170062121-000
			M32		H6BPR-TGMA-GR-M32	T1170062132-000
		H16BPR		PG21	H16BPR-TGMA-GR-PG21	T1170162121-000
			M25		H16BPR-TGMA-GR-M25	T1170162125-000
			M32	PG29	H16BPR-TGMA-GR-PG29	T1170162129-000
			M40		H16BPR-TGMA-GR-M40	T1170162140-000
Hoods: Side Entry & Top Entry		H16BPR	2M40		H16BPR-TG/SMA-GR-2M40	T1A40162240-000
		H24BPR	2M40		H24BPR-TG/SA-2M40	T1A40242240-000
			2M50		H24BPR-TG/SA-2M50	T1A40242250-000
Panel mounted adapter					APT-B	T3403121001-000

TE Connectivity's Heavy Duty Connectors

Cable Glands

Metal Cable Glands - Brass Nicked-plated



Metal cable glands - brass nicked-plated	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN		
Material: Nickel plated brass Press seal material: PA Seal material: NBR Temperature range: -40°C- + 100°C Protection: IP68			PG7	3-6.5	DLX-7-MS	T3609070101-000		
				2-5	DLX-7-MTS	T3609070111-000		
				3-6.5	DLX-7-MES	T3609070121-000		
			PG9	4-8	DLX-9-MS	T3609090101-000		
				2-6	DLX-9-MTS	T3609090111-000		
			PG11	5-10	DLX-11-MS	T3609110101-000		
				3-7	DLX-11-MTS	T3609110111-000		
					DLX-11-MSN	T3609110121-000		
			PG13	6-12	DLX-13-MS	T3609130101-000		
				5-9	DLX-13-MTS	T3609130111-000		
			PG16	10-14	DLX-16-MS	T3609160101-000		
				7-12	DLX-16-MTS	T3609160111-000		
			PG21	13-18	DLX-21-MS	T3609210101-000		
				9-16	DLX-21-MTS	T3609210111-000		
			PG29	18-25	DLX-29-MS	T3609290101-000		
				13-20	DLX-29-MTS	T3609290111-000		
			PG36	22-32	DLX-36-MS	T3609360101-000		
				20-26	DLX-36-MTS	T3609360111-000		
				22-32	DLX-36-LMS	T3609360201-000		
			PG42	32-38	DLX-42-MS	T3609420101-000		
				25-31	DLX-42-MTS	T3609420111-000		
			M12 * 1.5			3-6.5	DLX-12-M	T3609120102-000
						2-5	DLX-12-MT	T3609120112-000
			M16 * 1.5			4-8	DLX-16-M	T3609160102-000
						2-6	DLX-16-MT	T3609160112-000
						5-10	DLX-16-MB	T3609160122-000
			M20 * 1.5			6-12	DLX-20-M	T3609200102-000
						5-9	DLX-20-MT	T3609200112-000
						10-14	DLX-20-MB	T3609200122-000
			M25 * 1.5			13-18	DLX-25-M	T3609250102-000
						9-16	DLX-25-MT	T3609250112-000
			M32 * 1.5			18-25	DLX-32-M	T3609320102-000
						13-20	DLX-32-MT	T3609320112-000
			M40 * 1.5			22-32	DLX-40-M	T3609400102-000
						20-26	DLX-40-MT	T3609400112-000
			M50 * 1.5			32-38	DLX-50-M	T3609500102-000
							DLX-50-M	T3609500102-001
						22-32	DLX-50-MT	T3609500112-000
						29-36	DLX-50-M	T3609500122-000
			M63 * 1.5			37-44	DLX-63-M	T3609630102-000

Cable Gland

TE Connectivity's Heavy Duty Connectors

Cable Glands


Nylon Cable Glands - Nylon Sealing Insert

Nylon cable glands - nylon sealing insert	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN	
<p>Material: PA(GREY) Press seal material: PA Seal material: EPDM Temperature range: -40°C + 100°C Protection: IP68</p> 		PG7	PG7	3-6.5	HSK-P07G	T3209071201-000	
			PG9	2.5-6	HSK-P09G-H	T3209091211-000	
				4-8	HSK-P09G	T3209091201-000	
			PG11	5-10	HSK-P11G	T3209111201-000	
			PG13.5	5-9	HSK-P13.5G-H	T3209131211-000	
				6-12	HSK-P13.5G	T3209131201-000	
			PG16	6-12	HSK-P16G-H	T3209161211-000	
				8-14	HSK-P16G	T3209161201-000	
			PG21	11-16	HSK-P21G-H	T3209211211-000	
				13-18	HSK-P21G	T3209211201-000	
			PG29	14-21	HSK-P29G-H	T3209291211-000	
				18-25	HSK-P29G	T3209291201-000	
			PG36	22-32	HSK-P36G	T3209361201-000	
		PG42	30-38	HSK-P42G	T3209421201-000		
		PG48	37-44	HSK-P48G	T3209481201-000		
		M12*1.5		M12*1.5	3-6.5	HSK-M12G	T3209121222-001
		2.5-6			HSK-M16G-H	T3209161212-001	
		M16*1.5		4-8	HSK-M16G	T3209161222-001	
				5-10	HSK-M16G-D	T3209161202-001	
		M18*1.5		5-10	HSK-M18G	T3209181222-001	
		M20*1.5		5-9	HSK-M20G-H	T3209201212-001	
				6-12	HSK-M20G	T3209201222-001	
		M22*1.5		8-14	HSK-M20G-D	T3209201202-001	
				6-12	HSK-M22G-H	T3209221212-001	
		M24*1.5		8-14	HSK-M22G	T3209221222-001	
				6-12	HSK-M24G-H	T3209241212-001	
		M25*1.5		8-14	HSK-M24G	T3209241222-001	
				11-16	HSK-M25G-H	T3209251212-001	
		M27*2.0		13-18	HSK-M25G	T3209251222-001	
				11-16	HSK-M27G-H	T3209271212-001	
		M30*2.0		13-18	HSK-M27G	T3209271222-001	
				11-16	HSK-M30G-H	T3209301212-001	
		M32*1.5		13-18	HSK-M30G	T3209301222-001	
				14-21	HSK-M32G-H	T3209321212-001	
		M33*2.0		18-25	HSK-M32G	T3209321222-001	
				18-25	HSK-M33G	T3209331222-001	
		M36*2.0		14-21	HSK-M36G-H	T3209361212-001	
				18-25	HSK-M36G	T3209361222-001	
		M40*1.5		22-32	HSK-M40G	T3209401222-001	
		M42*2.0		22-32	HSK-M42G	T3209421222-001	
		M48*2.0		22-32	HSK-M48G	T3209481222-001	
		M50*1.5		30-38	HSK-M50G	T3209501222-001	
				31-41	HSK-M50G-D	T3209501202-001	
		M56*2.0		30-38	HSK-M56G	T3209561222-001	
		M60*2.0		37-44	HSK-M60G	T3209601222-001	
		M63*1.5		37-44	HSK-M63G	T3209631222-001	
		M64*2.0		37-44	HSK-M64G	T3209641222-001	
M72*2.0	43-53	HSK-M72G-H		T3209721212-001			
	51-57	HSK-M72G		T3209721222-001			

Cable Gland

TE Connectivity's Heavy Duty Connectors

Cable Glands

Nylon cable glands - nylon sealing insert	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN	
<p>Material: PA(black) Press seal material: PA Seal material: EPDM Temperature range: -40°C- + 100°C Protection: IP68</p> 		PG	PG7	3-6.5	HSK-P07B	T3209071101-000	
			PG9	2.5-6	HSK-P09B-H	T3209091111-000	
				4-8	HSK-P09B	T3209091101-000	
			PG11	5-10	HSK-P11B	T3209111101-000	
			PG13.5	5-9	HSK-P13.5B-H	T3209131111-000	
				6-12	HSK-P13.5B	T3209131101-000	
			PG16	6-12	HSK-P16B-H	T3209161111-000	
				8-14	HSK-P16B	T3209161101-000	
			PG21	11-16	HSK-P21B-H	T3209211111-000	
				13-18	HSK-P21B	T3209211101-000	
			PG29	14-21	HSK-P29B-H	T3209291111-000	
				18-25	HSK-P29B	T3209291101-000	
			PG36	22-32	HSK-P36B	T3209361101-000	
		PG42	30-38	HSK-P42B	T3209421101-000		
		PG48	37-44	HSK-P48B	T3209481101-000		
		M12*1.5			3-6.5	HSK-M12B	T3209121122-001
		M16*1.5			2.5-6	HSK-M16B-H	T3209161112-001
					4-8	HSK-M16B	T3209161122-001
		M18			5-10	HSK-M16B-D	T3209161102-001
					5-10	HSK-M18B	T3209181122-001
		M20*1.5			5-9	HSK-M20B-H	T3209201112-001
					6-12	HSK-M20B	T3209201122-001
		M22*1.5			8-14	HSK-M20B-D	T3209201102-001
					6-12	HSK-M22B-H	T3209221112-001
		M24*1.5			8-14	HSK-M22B	T3209221122-001
					6-12	HSK-M24B-H	T3209241112-001
		M25*1.5			8-14	HSK-M24B	T3209241122-001
					11-16	HSK-M25B-H	T3209251112-001
		M27*2.0			13-18	HSK-M25B	T3209251122-001
					11-16	HSK-M27B-H	T3209271112-001
		M30*2.0			13-18	HSK-M27B	T3209271122-001
					11-16	HSK-M30B-H	T3209301112-001
		M32*1.5			13-18	HSK-M30B	T3209301122-001
					14-21	HSK-M32B-H	T3209321112-001
		M33*2.0			18-25	HSK-M32B	T3209321122-001
					18-25	HSK-M33B	T3209331122-001
		M36*2.0			14-21	HSK-M36B-H	T3209361112-001
					18-25	HSK-M36B	T3209361122-001
		M40*1.5			22-32	HSK-M40B	T3209401122-001
		M42*2.0			22-32	HSK-M42B	T3209421122-001
		M48*2.0			22-32	HSK-M48B	T3209481122-001
		M50*1.5			30-38	HSK-M50B	T3209501122-001
					31-41	HSK-M50B-D	T3209501102-001
		M56*2.0			30-38	HSK-M56B	T3209561122-001
		M60*2.0			37-44	HSK-M60B	T3209601122-001
		M63*1.5			37-44	HSK-M63B	T3209631122-001
		M64*2.0			37-44	HSK-M64B	T3209641122-001
M72*2.0	43-53	HSK-M72B-H			T3209721112-001		
	51-57	HSK-M72B			T3209721122-001		

Cable Gland

TE Connectivity's Heavy Duty Connectors

Cable Glands


Cable Glands - Multiple Sealing Insert

Multiple sealing insert metal cable gland	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN
Material: Nickel plated brass Seal material: TPE/EPDM Temperature range: -40°C + 100°C Protection: IP65 Seal material colors: White (other colors need consulting)			PG29	4*9	DLX-29-MS 4*9	T3729290201-000
			PG29	3*10	DLX-29-MS 3*10	T3729290401-000
		M20		3*4	DLX-20-KM	T3729200102-000
		M25		4*6	DLX-25-1KM	T3729250102-000
		M25		2*8	DLX-25-4KM	T3729250402-000
M32	6*6.5	DLX-32-1KM	T3729320102-000			
Multiple sealing insert nylon cable gland Material: PA Seal material: EPDM Temperature range: -40°C + 100°C Protection: IP65 Seal material colors: White (other colors need consulting)			PG16	2*6	DLX-16-KPMS	T3229160201-000
			PG21	2*8	DLX-21-4KPMS	T3229210401-000
			PG29	4*9	DLX-29-2KPMS	T3229290201-000
			PG36	5*9	DLX-36-1KPMS	T3229360101-000
		M16		2*3	DLX-16-KPM	T3229160102-000
		M20		2*5	DLX-20-KPM	T3229200202-000
		M25		4*6	DLX-25-1KPM	T3229250102-000
		M25		2*6	DLX-25-3KPM	T3229250302-000
		M25		2*8	DLX-25-4KPM	T3229250402-000
		M32		4*9	DLX-32-2KPM	T3229320202-000

TE Connectivity's Heavy Duty Connectors

Cable Glands

Special Sealing Insert Glands



Special sealing insert glands	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN
Sealing with Different Color Material: Nickel plated brass Seal material: TPE/EPDM Temperature range: -40°C + 100°C Protection: IP65 Seal material colors: Black (other colors need consulting)			PG9	6.5-9	DLX-9-MSE	T3709090101-000
			PG9	3.5-6	DLX-9-MSET	T3709090111-000
			PG11	6-8.5	DLX-11-MSET	T3709110111-000
			PG11	8.5-11	DLX-11-MSEZ	T3709110121-000
			PG13.5	13.5-15	DLX-13-MSE	T3709130101-000
			PG13.5	8.5-11	DLX-13-MSET	T3709130111-000
			PG13.5	11-13.5	DLX-13-MSEZ	T3709130121-000
			PG16	14-16	DLX-16-MSE	T3709160101-000
			PG16	9-12	DLX-16-MSET	T3709160111-000
			PG16	12-14	DLX-16-MSEZ	T3709160121-000
			PG21	17.5-19	DLX-21-MSE	T3709210101-000
			PG21	13.5-16	DLX-21-MSET	T3709210111-000
			PG21	16-17.5	DLX-21-MSEZ	T3709210121-000
			PG29	22.5-25	DLX-29-MSE	T3709290101-000
			PG29	17.5-21	DLX-29-MSET	T3709290111-000
			PG29	21-22.5	DLX-29-MSEZ	T3709290121-000
			M16*1.5	9.5-10.5	DLX-16-ME	T3709160102-000
			M16*1.5	6.5-8	DLX-16-MET	T3709160112-000
			M16*1.5	8-9.5	DLX-16-MEZ	T3709160122-000
			M20*1.5	13.5-15	DLX-20-ME	T3709200102-000
	M20*1.5	8.5-11	DLX-20-MET	T3709200112-000		
	M20*1.5	11-13.5	DLX-20-MEZ	T3709200122-000		
	M24*1.5	10-14	DLX-24-MET	T3709240112-000		
	M25*1.5	17.5-19	DLX-25-ME	T3709250102-000		
	M25*1.5	13.5-16	DLX-25-MET	T3709250112-000		
	M25*1.5	16-17.5	DLX-25-MEZ	T3709250122-000		
	M25*1.5	19-21	DLX-25-MEC	T3709250142-000		
	M32*1.5	22.5-25	DLX-32-ME	T3709320102-000		
	M32*1.5	17-21	DLX-32-MET	T3709320112-000		
	M32*1.5	21-22.5	DLX-32-MEZ	T3709320122-000		
EMC cable glands Material: Nickel plated brass Press Seal Material: PA Temperature range: -40°C + 100°C Protection: IP68			PG11	5-10	DLX-11-MS	T3706110203-000
			PG21	13-18	DLX-21-MS	T3707210101-000
			PG29	17-24	DLX-29-MS	T3707290101-000
		M16	4-8	DLX-16-MC	T3707160103-000	
		M20	7-12	DLX-20-MC	T3706200103-000	
		M25	11-16	DLX-25-MTC	T3707250113-000	
		M25	13-18	DLX-25-MC	T3609250103-000	
		M32	15-21	DLX-32-MTC	T3707320113-000	
		M32	18-25	DLX-32-MC	T3707320103-000	
		M40	22-30	DLX-40-MTC	T3707400113-000	
		M40	22-32	DLX-40-MC	T3706400103-000	
		M50	30-38	DLX-50-MC	T3707500103-000	
		M63	37-44	DLX-63-MC	T3707630103-000	

Cable Gland

TE Connectivity's Heavy Duty Connectors

Cable Glands

Metal Glands with Multiple Seal

Metal glands with multiple seal	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN
Material: Nickel plated brass Seal Material: NBR Temperature range: -40°C + 100°C Protection: IP65			PG9	5-10	DSM-9	T3201090101-000
			PG16	7-15	DSM-16	T3201160101-000
			PG21	10-19	DSM-21	T3201210101-000
			PG29	18-27	DSM-29	T3201290101-000
		M25	13-20	DSM-25-M	T3201250102-000	
		M32	19-28	DSM-32-M	T3201320102-000	
Material: Nickel plated brass Seal Material: NBR Temperature range: -40°C + 100°C Protection: IP54			PG21	17-19	DSM-21-S	T3211210101-000
			PG29	23-25	DSM-29-S	T3211290101-000
		M25	15-17	DSM-25-SM	T3211250102-000	
		M32	24-26	DSM-32-SM	T3211320102-000	

TE Connectivity's Heavy Duty Connectors

Cable Glands

Metal Clamp Glands with Multiple Seal

Metal clamp glands with multiple seal	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN
Material: Nickel plated brass Seal Material: NBR Temperature range: -40°C + 100°C Protection: IP65			PG9	6.5-10	ZSM-9	T3135090101-000
			PG11	7.5-12	ZSM-11	T3135110101-000
			PG13.5	8.5-13.5	ZSM-13	T3135130101-000
			PG16	10.5-16	ZSM-16	T3135160101-000
			PG21	13-20	ZSM-21	T3135210101-000
			PG29	19-28	ZSM-29	T3135290101-000
			PG36	24-34	ZSM-36	T3135360101-000
		M16		6.5-10	ZSM-16-M	T3135160121-000
		M20		7.5-12	ZSM-20-M	T3135200121-000
		M25		13-20	ZSM-25-M	T3135250121-000
		M32		19-28	ZSM-32-M	T3135320121-000
		M40		24-34	ZSM-40-M	T3135400121-000

Metal Clamp Glands

Metal clamp glands	Product Image	Metr.	PG	Clamp Range Ø (mm)	Type	PN
Material: Nickel plated brass Temperature range: -40°C + 100°C			PG9	6.5-10	KSM-9-MS	T3105090101-000
			PG11	7.5-12	KSM-11-MS	T3105110101-000
			PG13.5	8.5-14	KSM-13-MS	T3105130101-000
			PG16	9.5-16	KSM-16-MS	T3105160101-000
			PG21	12-21	KSM-21-MS	T3105210101-000
			PG29	19-30	KSM-29-MS	T3105290101-000
			PG36	25-37	KSM-36-MS	T3105360101-000
		M32		16-27	KSM-32-M	T3105320121-000
		M40		23-33	KSM-40-M	T3105400121-000

TE Connectivity's Heavy Duty Connectors

Cable Glands

Metal Lock Nuts

Metal lock nuts	Product Image	Metr.	PG	Type	PN
Material: Nickel plated brass Temperature range: -40°C + 100°C			PG7	LN-7-MS	T3161070001-000
			PG9	LN-9-MS	T3161090001-000
			PG11	LN-11-MS	T3161110001-000
			PG13	LN-13-MS	T3161130001-000
			PG16	LN-16-MS	T3161160001-000
			PG21	LN-21-MS	T3161210001-000
			PG29	LN-29-MS	T3161290001-000
			PG36	LN-36-MS	T3161360001-000
			PG42	LN-42-MS	T3161420001-000
		M12		LN-12-M	T3161120050-000
		M16		LN-16-M	T3161160050-000
		M20		LN-20-M	T3161200050-000
		M25		LN-25-M	T3161250050-000
		M27		LN-27-M	T3161270051-000
		M28		LN-28-M	T3161280001-000
		M32		LN-32-M	T3161320050-000
		M40		LN-40-M	T3161400050-000
		M50		LN-50-M	T3161500050-000
		M63		LN-63-M	T3161630050-000
Nylon lock nuts Material: PA Temperature range: -40°C + 100°C			PG7	LN-7-P	T3262070001-000
			PG9	LN-9-P	T3162090001-000
			PG11	LN-11-P	T3262110001-100
			PG13.5	LN-13-P	T3262130001-100
			PG16	LN-16-P	T3262160001-100
			PG21	LN-21-P	T3262210001-100
			PG29	LN-29-P	T3262290001-100
			PG36	LN-36-P	T3262360001-000
			PG42	LN-42-P	T3262420001-000
			PG48	LN-48-P	T3262480001-000
		M12		LN-12-PM	T3262120050-000
		M16		LN-16-PM	T3262160050-000
		M20		LN-20-PM	T3262200050-100
		M25		LN-25-PM	T3262250050-000
		M32		LN-32-PM	T3262320050-100
		M40		LN-40-PM	T3262400050-000
		M50		LN-50-PM	T3262500050-000
		M60		LN-60-PM	T3262600050-000
		M63		LN-63-PM	T3262630050-000
			PG16	LN-16-BP	T3262160001-200
			PG21	LN-21-BP	T3262210001-200
			PG29	LN-29-BP	T3262290001-200
		M16		LN-16-BPM	T3262160050-200
		M20		LN-20-BPM	T3262200050-200
		M25		LN-25-BPM	T3262250050-200
		M32		LN-32-BPM	T3262320050-200

TE Connectivity's Heavy Duty Connectors

Cable Glands

Metal Increasesers


Metal increasers	Product Image	Metr.	PG	Clamp Range	Type	PN		
			PG9-PG11	-	INCR-9/11-PG	T3033091101-000		
			PG16-PG21		INCR-16/21-PG	T3033162102-000		
			PG21-PG29		INCR-21/29-PG	T3033212902-000		
			PG29-PG36		INCR-29/36-PG	T3033293601-000		
		M16-M20			INCR-16/20-M	T3033162050-000		
		M16-PG11			INCR-M16-PG11	T3033161150-000		
		M16-PG16			INCR-M16-PG16	T3168161612-000		
		M20-M25			INCR-20/25-M	T3033202550-000		
		M20-PG16			INCR-M20-PG16	T3168201612-000		
		M25-M32			INCR-25/32-M	T3033253250-000		
		M32-PG29			INCR-M32-PG29	T3033322950-000		
		M32-M40			INCR-32/40-M	T3033324050-000		
		M40-M50			INCR-40/50-M	T3033405050-000		
		M50-M63			INCR-50/63-M	T3033506350-000		
						PG11-PG7	REDU-11/7-PG	T3071110701-000
						PG11-PG9	REDU-11/9-PG	T3071110901-000
						PG13.5-PG11	REDU-13/11-PG	T3071131101-000
					M6-M12		REDU-16/12-M	T3071161250-000
					M20-PG11		REDU-M20-PG11	T3071201101-000
					M20-M12		REDU-20/12-M	T3071201250-000
					M20-M16		REDU-20/16-M	T3071201650-000
	PG21-PG16			REDU-21/16-PG	T3071211602-000			
	PG21-M25			REDU-PG21-M25	T3071212502-000			
M25-M20				REDU-25/20-M	T3071252050-000			
	PG29-PG21			REDU-29/21-PG	T3071292101-000			
	PG29-M32			REDU-PG29-M32	T3071293202-000			
M32-M25				REDU-32/25-M	T3071322550-000			
	PG36-PG29			REDU-36/29-PG	T3071362902-000			
				PG42-PG36	REDU-40/32-M	T3071403250-000		
M40-M32					REDU-42/36-PG	T3071423601-000		
				PG21-PG9	REDU-50/40-M	T3071504050-000		
				PG21-PG11	REDU-21/9-PG	T3167210901-000		
					PG21-PG13.5	REDU-21/11-PG	T3167211101-000	
					PG21-PG13.5	REDU-21/13-PG	T3167211301-000	
M32-PG21				REDU-32/21	T3167322111-000			
M50-M32		REDU-50/32-M	T3167503211-000					
Product Image			Dimensions	Type	PN			
				10	AD10	T3310010000-000		
				13	AD13	T3310013000-000		
				15.8	AD15.8	T3310015000-000		
				21.2	AD21.2	T3310022000-000		
				34.5	AD34.5	T3310034000-000		
				42.5	AD42.5	T3310040000-000		
54.5	AD54.5	T3310054000-000						

Material: PA
 Temperature range:
 -40°C + 100°C



TE Connectivity's Heavy Duty Connectors

Cable Glands

Inside and Outside Thread Adapter

Inside and outside thread adapter	Product Image	Metr.	PG	Type	PN
Material: Nickel plated brass Temperature range: -40°C + 100°C		M16		STUD-16-M	T3265161611-000
		M20		STUD-20-M	T3265202011-000
			PG21	STUD-PG21	T3333212112-000
			PG29	STUD-PG29	T3333292912-000
		M25		STUD-M25	T3333252511-000
		M32		STUD-M32	T3333323211-000
		M40		STUD-M40	T3333404011-000
	M32		STUD-M32	T3333323201-000	

Blind Plug

BLIND PLUG	Product Image	Metr.	PG	Type	PN
Body material: BLIND-32-M-BX & BLIND-25-M-BX: STAINLESS STEEL; Others Nickel plated brass Temperature range: -40°C- + 100°C Protection: IP65			PG7	BLIND-7-MS	T3165070101-000
			PG9	BLIND-9-MS	T3165090101-000
			PG11	BLIND-11-MS	T3165110101-000
			PG13	BLIND-13-MS	T3165130101-000
			PG16	BLIND-16-MS	T3165160101-000
			PG21	BLIND-21-MS	T3165210101-000
			PG29	BLIND-29-MS	T3165290101-000
			PG36	BLIND-36-MS	T3165360101-000
			PG42	BLIND-42-MS	T3165420101-000
			PG48	BLIND-48-MS	T3165480101-000
		M12*1.5		BLIND-12-M	T3165120111-000
		M16*1.5		BLIND-16-M	T3165160111-000
		M20*1.5		BLIND-20-M	T3165200111-000
		M25*1.5		BLIND-25-M	T3165250111-000
		M25*1.5,stainless steel		BLIND-25-M-BX	T3165250111-100
		M32*1.5		BLIND-32-M	T3165320111-000
		M32*1.5,stainless steel		BLIND-32-M-BX	T3165320111-100
		M40*1.5		BLIND-40-M	T3165400111-000
		M50*1.5		BLIND-50-M	T3165500111-000
Body material: PA(grey) Temperature range: -40°C- + 100°C Protection: IP65			PG9	BLIND-9-P	T3166090101-000
			PG11	BLIND-11-P	T3166110101-000
			PG13.5	BLIND-13-P	T3166130101-000
			PG16	BLIND-16-P	T3166160101-000
			PG21	BLIND-21-P	T3166210101-000
			PG29	BLIND-29-P	T3166290101-000
			PG36	BLIND-36-P	T3166360101-000
			PG42	BLIND-42-P	T3166420101-000
			PG48	BLIND-48-P	T3166480101-000
		M12*1.5		BLIND-12-PM	T3166120111-000
		M16*1.5		BLIND-16-PM	T3166160111-000
		M20*1.5		BLIND-20-PM	T3166200111-000
		M25*1.5 (with TE LOGO)		BLIND-25-PM	T3166250111-000
		M32*1.5		BLIND-32-PM	T3166320111-000
		M40*1.5		BLIND-40-PM	T3166400111-000
		M50*1.5		BLIND-50-PM	T3166500111-000
		M63*1.5		BLIND-63-PM	T3166630111-000

Cable Gland

TE Connectivity's Heavy Duty Connectors

te.com

©2024 TE Connectivity. All Rights Reserved.

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

1-1773869-8 12/24 BA

INDUSTRIAL / HEAVY DUTY CONNECTORS

