
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT – TE Connectivity ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REV PER ECO 18-016054	10-22-18	CT	PR


COMPONENT	MATERIAL	FINISH
FERRULE ASSY JACK SHELL NUT	BRASS PER ASTM-B-16	SILVER PER ASTM-B-700
DIELECTRIC	TEFLON PER ASTM-D-1710	--
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196	GOLD PLATED PER ASTM-B-488
LOCKWASHER	PHOS BRONZE PER ASTM-B-103	SILVER PER ASTM-B-700
O-RING	SILICONE PER ZZ-R-765	--




AS SHIPPED TO CUSTOMER



ASSEMBLED VIEW



RECOMMENDED STRIP LENGTH
SCALE 2:1



RECOMMENDED
PANEL CUTOUT
SCALE 2:1

RAYCHEM 5012H3012	90740-1	1996332-1
CABLE SIZE	CRIMP TOOL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –
FINISH –

DWN C.C.THOMAS 11-16-07
CHK W.MOYER 11-16-07
APVD W.MOYER 11-16-07
PRODUCT SPEC –
APPLICATION SPEC I.S. 2028-3
WEIGHT 0

TE Connectivity

NAME JACK,BULKHEAD,WEATHERPROOF,SERIES N
–
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-1996332	–

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV C

4805 (1/15)