



EC No.

Battery Disconnector 2x200A









Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MOhm
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	to 32VDC
Duty Rating	2x200A
Overload	2x500A-180sec.
	2x1000A-30sec.
Sealing	IP 67/ IEC 529
Vibration	4G / 50-2000Hz
Shock G-Level	6G / 11ms
Weight	~330g / 0.72 Pound
Temperature Range	-40°C to +85°C
Wire Section (at nominal Load)	min. 70mm2
Switch Lever	removeable
Max. Torque (Main Contacts)	12-13Nm

	Date	Name	mm	Scale	Drawing No:
Drawn	23.05.2014	Mielk		1:2	35-221-040-R
Check	06.08.2018	Grind	General Tolerances DIN ISO 2768 cL		NSN.: