

4

3


2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION —, — .
© COPYRIGHT — By —	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECO-11-022043	07NOV11	KH	PO

2	0.4VA-20VAC/DC, ROUND BUTTON (0.188”) DIAMETER BUSHING, DPST-OFF/(ON), B TERMINALS	TPB21MG004	1-1825097-7
2	0.4VA-20VAC/DC, ROUND BUTTON (0.188”) DIAMETER BUSHING, SPDT-(ON)/(ON), B TERMINALS	TPB11FG004	1825097-9
2	0.4VA-20VAC/DC, ROUND BUTTON (0.188”) DIAMETER BUSHING, SPST-OFF/(ON), B TERMINALS	TPB11CG004	1825097-1
2	0.4VA-20VAC/DC, ROUND BUTTON NO BUSHING, SPDT-(ON)/(ON), B TERMINALS RIGHT ANGLE	TPA11FGRA004	1-1825096-0
2	0.4VA-20VAC/DC, ROUND BUTTON NO BUSHING, SPDT-(ON)/(ON), B TERMINALS	TPA11FG004	1825096-7
2	0.4VA-20VAC/DC, ROUND BUTTON NO BUSHING, SPST-OFF/(ON), B TERMINALS	TPA11CG004	1825096-1
QTY	DESCRIPTION	ALCOSWITCH PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm 		DWN KIRAN HOLAL 07NOV2011		 TE Connectivity						
		CHK OTT, PETER		NAME SINGLE AND DOUBLE POLE AND THROW, VERTICAL AND RIGHT ANGLE PRINTED CIRCUIT BOARD TERMINALS TP KIT						
		APVD OTT, PETER								
		PRODUCT SPEC —		APPLICATION SPEC —		SIZE A3	CAGE CODE 00779	DRAWING NO C-2110843-2	RESTRICTED TO —	
MATERIAL —		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		WEIGHT —		CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	REV A
FINISH —										