

PART AFTER UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS:

1	H DIA		J DIA		Р	R	S	T	10	W	U
Ì	MIN	MAX	MIN	MAX	± 10%	± 10%	± 10%	± 10%	± 10%	± 20%	土10%
	α	b	a	b	b	b	ь	b	b	b	b
	1,85	.82	1.85	.33	3.15	1.63	.12	.04	.82	.08	.79

If this document is printed it becomes uncontrolled.

Check for the latest revision.

REVISIONS: DATE DESCRIPTION

If this document is printed it becomes uncontrolled. Check for the latest revision.

NOTES:

- 1. ALL DIMENSION ARE IN INCHES
- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
 - a AS SUPPLIED
 - b AFTER UNRESTRICTED RECOVERY
- 3. COATING IS OFTIONAL. AS SUPPLIED DIMENSIONS AFFEARING IN TABLE ARE UNCOATED; ENTRY DIAMETERS, AND LIPS SHOWN WILL BE REDUCED BY . 06 MAX WHEN COATING IS ADDED.

202DI53 ORDERING INFORMATION: Base part number ----Material dash number -----3 Polyolefin, semi-rigid (RT-301) -4 Polyolefin, flexible (RT-1304) Modification number -Coating slash number

	SPECIFICATION OF THE SPECIFICA	ON CON	ITROL DRA	AWING	(L	IMITED	DISTRIBU	JTION	}	
	THIS DRAWING AND THE	DRAYM	C.WALREN 12-13-02	Raychem		RAYCHEM CORPORATION 300 CONSTITUTION DRIVE				
	INFORMATION SET FORTH HEREON ARE THE PROP-	CHECKED		nayonem			MENLO PARIC, CALIFORNIA S44			
	ERTY OF RAYCHEM COR- PORATION, AND ARE TO BE	DOON APPD	6/2-02-02	BOOT, STRAIGHT						
	HELD IN TRUST AND CON- PIDENCE. PUBLICATION,	MPG APPO	But Noller							
	DUPLICATION, DISCLO- SURE, OR USE FOR ANY	OC APPO	D.Hay 12-23-92							
	PURPORE NOT EXPRESSLY AUTHORIZED IN WRITING	MICTO APPD	15-17-FZ	CODE IDENT.	7. DWG. NO. 202DI53-X-		10 /42	j,		
	BY RAYCHEM CORPORA- TION IS PROHIBITED,	TROP SERVER	X. C 12-25-46	NO. 00000						
T	DO NOT SCALE THIS DRAIMING PROJECT			. SIZE D		SCALE		SHEET /	OF	