

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | | DIST | | REVISIONS | | | |
|-----|-----|---------------------------|--|-----------|-----|------|--|
| P | LTR | DESCRIPTION | | DATE | DWN | APVD | |
| | A | REVISED PER ECO-11-022043 | | 11NOV11 | KH | PO | |

| QTY | DESCRIPTION | ALCOSWITCH PART NUMBER | PART NUMBER |
|-----|---|------------------------|-------------|
| 2 | 0.4VA-20VAC/DC, SPDT-(ON)/(ON), B TERMINALS, BLACK BUTTON | TSPD11FG004 | 1-1571990-5 |
| 2 | 0.4VA-20VAC/DC, SPST-OFF/(ON), WIRE WRAP TERMINALS, BLACK BUTTON | TSPD11CGWW004 | 1-1571990-4 |
| 2 | 0.4VA-20VAC/DC, SPST-OFF/(ON), B TERMINALS VERTICAL RIGHT ANGLE, BLACK BUTTON | TSPD11CGVRA004 | 1-1571990-3 |
| 2 | 0.4VA-20VAC/DC, SPST-OFF/(ON), B TERMINALS RIGHT ANGLE, BLACK BUTTON | TSPD11CGRA004 | 1571990-4 |
| 2 | 0.4VA-20VAC/DC, SPST-OFF/(ON), B TERMINALS WITH BRACKET, BLACK BUTTON | TSPD11CGV004 | 1571990-3 |
| 2 | 0.4VA-20VAC/DC, SPST-OFF/(ON), B TERMINALS, BLACK BUTTON | TSPD11CG004 | 1571990-1 |

| | | | | | | | |
|--|--|---------------------------------|--|-----------|-------------|---------------|-----|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN KIRAN HOLAL 07NOV2011 | STE TE Connectivity | | | | |
| DIMENSIONS: mm | | CHK OTT, PETER | | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD OTT, PETER | NAME SINGLE POLE, SINGLE AND DOUBLE THROW, PRINTED CIRCUIT BOARD AND WIRE LUG TERMINALS TSP KIT | | | | |
| 0 PLC ± - | | PRODUCT SPEC | | | | | |
| 1 PLC ± - | | APPLICATION SPEC | SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO | |
| 2 PLC ± - | | — | A3 | 00779 | C-2110843-1 | — | |
| 3 PLC ± - | | — | CUSTOMER DRAWING | | SCALE | SHEET | REV |
| 4 PLC ± - | | — | — | | 1:1 | 1 OF 1 | A |
| ANGLES ± - | | WEIGHT | — | | | | |
| MATERIAL | | | | | | | |
| FINISH | | | | | | | |