THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| — | — |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | 1 | - | 2/28/08 | SS | CR |

MATERIAL:
HOUSING: PA6-6, COLOR: GREEN, UL94V-0.
SCREW: M3, NICKEL PLATED, COPPER ALLOY.
TERMINAL: TIN PLATED, COPPER ALLOY.
CLAMP: NICKEL PLATED, COPPER ALLOY.

ELECTRICAL:
VOLTAGE RATING: 300V, 15A.
WIRE SIZE RANGE: 12-30 AWG.

ENVIRONMENTAL:
OPERATING TEMP.: -40°C TO +110°C

2 THRU 5 POSN PARTS ARE MOLDED TO SIZE. ALL OTHER SIZES ARE ACHIEVED BY INTERLOCKING COMPONENTS.




THIS PRINT IS
PRELIMINARY
PRIOR TO CUSTOMER ORDER
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

| DIM B | DIM A | NO OF POS | PART NUMBER |
|---|---|---|---|
| 62.66 | 61.04 | 12 | 1-1986361-2 |
| 57.58 | 55.96 | 11 | 1-1986361-1 |
| 52.50 | 50.88 | 10 | 1-1986361-0 |
| 47.42 | 45.80 | 9 | 1986361-9 |
| 42.34 | 40.72 | 8 | 1986361-8 |
| 37.26 | 35.64 | 7 | 1986361-7 |
| 32.18 | 30.56 | 6 | 1986361-6 |
| 27.10 | 25.48 | 5 | 1986361-5 |
| 22.02 | 20.40 | 4 | 1986361-4 |
| 16.92 | 15.32 | 3 | 1986361-3 |
| 11.84 | 10.24 | 2 | 1986361-2 |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

| | |
|---|---|
| 0 PLC | ± - |
| 1 PLC | ± 0.3 |
| 2 PLC | ± 0.25 |
| 3 PLC | ± - |
| 4 PLC | ± - |
| ANGLES | ± 2° |

MATERIAL -
FINISH -

DWN S SCHLEGEL 28FEB2008
CHK C RICHARD 2/28/08
APVD C RICHARD 2/28/08
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

Tyco Electronics
Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
INVERTED HEADER, CLOSED ENDS
5.08mm PITCH
—

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | 00779 | C-1986361 | — |

CUSTOMER DRAWING

| SCALE | SHEET | REV |
|---|---|---|
| NTS | 1 OF 1 | 1 |