

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
ESDIST
-

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
| B | | REVISED PER ECR-10-011717 | 30MAY2010 | S.W | S.Y |

RECOMMENDED P.C. BOARD LAYOUT
P.C. BOARD THK 0.8~1.2
(VIEW FROM CONNECTOR MOUNTING SIDE)

SECT. "A"- "A"

SECT. "B"- "B"

SECT. "C"- "C"

SECT. "D"- "D"

NOTES

△ MATERIAL HOUSING : THERMOPLASTIC RESIN, UL94V-0
COLOR ; BLACK
CONTACT : COPPER ALLOY
RETENTION LEG : COPPER ALLOY

△ FINISH CONTACT : Ni ALL OVER UNDER PL
Pd-Ni PL. AT CONTACT AREA
Au FLASH PL. AT CONTACT AREA
TIN-LEAD PL. AT LEAD AREA
RETENTION LEG : TIN-LEAD PL.

1612413-1 ; AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

| | | |
|------|------------|------------|
| DWN | Y.WATANABE | 21-JUN-'99 |
| CHK | K.ASAKAWA | 21-JUN-'99 |
| APVD | I.ENOMOTO | 22-JUN-'99 |

Tyco Electronics
Shanghai, P.R.China, 200233

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:

| | | | |
|--------|---|-----|-----------|
| 0-PLG | ± | 10 | ±0.2 |
| 1-PLG | ± | 30 | >10 ±0.25 |
| 2-PLG | ± | 100 | >30 ±0.3 |
| 3-PLG | ± | | |
| 4-PLG | ± | | |
| ANGLES | | | ±3° |

MATERIAL

△

FINISH

△

PRODUCT SPEC
108-5599
APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
PLUG ASSEMBLY
2.5mm PITCH BATTERY CONNECTOR
5POS. OFFSET DIP TYPE

| | | | |
|------|-----------|------------|---------------|
| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
| A3 | 00779 | ©=1318790 | - |

| | | | |
|-------|-------|----|-----|
| SCALE | SHEET | OF | REV |
| 2:1 | 1 | 1 | B |

AMP 1470-19 REV 31MAR2000