

TE P/N	TE CD	Nanonics P/N	Part Description
1589055-1	1589055	QCM007PC2DC003	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 inches.
1589055-2	1589055	QCM007PC2DC006	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches.
1589055-3	1589055	QCM007PC2DC012	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches.
1589055-6	1589055	QCM007PC2DC020	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches.
1589055-8	1589055	QCM007PC2DC040	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 40 inches.
1589055-9	1589055	QCM007PC2DC072	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 72 inches.
1-1589055-0	1589055	QCM007PC2DCC30	Quick disconnect, circular, metal, 7 position, plug, 30 awg 7 strand, color coded PTFE wire, 30 centimeters.
1-1589055-1	1589055	QCM007PC2DMC46	Quick disconnect, circular, metal, 7 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 46 centimeters.
1-1589055-3	1589055	QCM007PC2DC028	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 28 inches.
1-1589055-4	1589055	QCM007PC2DCM01	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 1 meter.
1-1589055-5	1589055	QCM007PC2DCM03	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 meters.
1-1589055-6	1589055	QCM007PC2DMC150	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 150 centimeters.
1-1589055-7	1589055	QCM007PC2DMC50	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 50 centimeters.
1-1589055-8	1589055	QCM007PC2DCM02	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 2 meters.
1-1589055-9	1589055	QCM007PC2DC024	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches.