

TE P/N	TE CD	Nanonics P/N	Part Description
1589815-1	1589815	STG051T2	Dualobe, 2 row, gold, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe.
1589815-2	1589815	STG051T2AQ	Dualobe, 2 row, gold, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1589815-3	1589815	STM009T2HN	Dualobe, 2 row, metal, 9 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589815-4	1589815	STM015T2HN	Dualobe, 2 row, metal, 15 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589815-5	1589815	STM025T2HN	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589815-6	1589815	STM037T2HN	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589815-7	1589815	STM051T2HN	Dualobe, 2 row, metal, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589815-8	1589815	STM065T2HN	Dualobe, 2 row, metal, 65 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589815-9	1589815	STG025T2HN	Dualobe, 2 row, gold, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589815-0	1589815	STG065T2HN	Dualobe, 2 row, gold, 65 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589815-1	1589815	STL015T2AQ	Dualobe, 2 row, LCP, 15 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589815-2	1589815	STL025T2AN	Dualobe, 2 row, LCP, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589815-3	1589815	STL025T2AQ	Dualobe, 2 row, LCP, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589815-4	1589815	STM025T2AQ	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589815-5	1589815	STM025T2IQ	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .200 mounting screw, thread for 1.2 jackscrews.
1-1589815-6	1589815	STM037T2AQ	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589815-7	1589815	STM065T2AQ	Dualobe, 2 row, metal, 65 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screws, thread for 1.2 jackscrews.
1-1589815-8	1589815	STM051T2IQ	Dualobe, 2 row, metal, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .200 mounting screw, thread for 1.2 jackscrews.
1-1589815-9	1589815	STM065T2IQ	Dualobe, 2 row, metal, 65 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .200 mounting screw, thread for 1.2 jackscrews.
2-1589815-0	1589815	STM009T2AQ	Dualobe, 2 row, metal, 9 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
2-1589815-1	1589815	STL015T2HQ	Dualobe, 2 row, LCP, 15 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.2 jackscrews.
2-1589815-2	1589815	STL025T2HQ	Dualobe, 2 row, LCP, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.2 jackscrews.
2-1589815-3	1589815	STM051T2AQ	Dualobe, 2 row, metal, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
2-1589815-4	1589815	STG015T2HN	Dualobe, 2 row, gold, 15 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.