THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION – ,– .
© COPYRIGHT – TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	DRAWING FORMAT UPDATE AND MATERIAL RE–DESIGN	31JUL2019	GK	KM

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: F51654-000

OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 5000.
ROLL LENGTH: 116.50 m

MATERIAL	WHITE VINYL FILM
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	–0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL: SEE TABLE

FINISH: –

DWN GOPALAKRISHNA HV 31JUL2019
CHK K. MUNZ 31JUL2019
APVD K. MUNZ 31JUL2019
PRODUCT SPEC TTDS–207
APPLICATION SPEC –
WEIGHT 0.15354 g

TE Connectivity

NAME: WV – WHITE VINYL LABELS – –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	C–WV–699191–5–9	–

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV B

WV–699191–5–9

1470–19 (1/15)