

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Jumper Bars

## General Information

<b>Extended Product Type:</b>	JB22-3
<b>Product ID:</b>	1SNK922303R0000
<b>EAN:</b>	3472599163614
<b>Catalog Description:</b>	JB22-3 Jumper Bar
<b>Long Description:</b>	Screw jumper bars

## Ordering

<b>Minimum Order Quantity:</b>	5 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160033D0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	22 mm
<b>Product Net Height:</b>	57 mm
<b>Product Net Length:</b>	20.7 mm
<b>Product Net Depth / Length:</b>	20.7 mm
<b>Product Net Weight:</b>	43.3 g

## Technical

<b>Spacing:</b>	22 mm
<b>Function:</b>	Jumper Bars
<b>Rated Current (<math>I_n</math>):</b>	Main Circuit 192 A
<b>Rated Short-time Withstand Current (<math>I_{cw}</math>):</b>	for 1 s 8400 A
<b>Rated Voltage (<math>U_r</math>):</b>	1000 V
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	8000 V
<b>Dielectric Test Voltage:</b>	2200 V
<b>Power Loss:</b>	6.1 W
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide

**Recommended Screw Driver:** 4 mm

---

**Suitable For:** D70/22  
ZS70

---

## Technical UL/CSA

**Maximum Operating Voltage  
UL/CSA:** Main Circuit 600 V

---

## Environmental

**Ambient Air Temperature:** Operation -55 ... +110 °C  
Storage -55 ... +110 °C

---

**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment

---

## Certificates and Declarations (Document Number)

**ATEX Certificate:** 1SND162004A1708

---

**CB Certificate:** 1SND161034A0202

---

**Instructions and Manuals:** 1SNK160027C0201

---

**RoHS Information:** 1SND230499F0202

---

## Classifications

**Object Classification Code:** X

---

**E-number:** 2925394

---

**ETIM 4:** EC000489 - Cross-connector for terminal block

---

**ETIM 5:** EC000489 - Cross-connector for terminal block

---

**ETIM 6:** EC000489 - Cross-connector for terminal block

---

## Container Information

**Package Level 1 Units:** 5 piece

---

**Package Level 1 Width:** 45 mm

---

**Package Level 1 Depth / Length:** 105 mm

---

**Package Level 1 Height:** 45 mm

---

**Package Level 1 Gross Weight:** 0.216 kg

---

**Package Level 1 EAN:** 3472599163614

---

**Package Level 2 Units:** 105 piece

---

**Package Level 2 Width:** 200 mm

---

**Package Level 2 Depth / Length:** 300 mm

---

**Package Level 2 Height:** 200 mm

---

**Package Level 2 Gross Weight:** 4.87 kg

---

**Package Level 3 Units:** 10080 piece

---

**Product Packing Type:** Box

---

