

THIS DRAWING IS A CONTROLLED DOCUMENT.

RING

| APPLICATOR PARTS LIST | | | | MINIATURE QUICK CHANGE APPLICATOR SIDE FEED MOD III | | | AMP INCORPORATED HARRISBURG, PENNA. | | | | |
|-----------------------|--------------------------------|------|------------|--|----------------------------|----------|--|---|--------------|---------------------------|------------|
| NO. | DESCRIPTION | REQ. | PART NO. | NO. | DESCRIPTION | REQ. | PART NO. | CRIMPING DATA | | | TERMINALS |
| 1 | WIRE CRIMPER 453804-6 | 1 | 690403-6 | 43 | WASHER-LAMINATED | 1 | 690125-1 | TO APPLY TERMINAL | | | 61006-2 |
| 2 | CRIMPER SPACER | 1 | 690407-5 | 44 | RAM | 1 | 238016-1 | Rev. Reel | | | of 61006-1 |
| 3 | INSULATION CRIMPER | 1 | 2-690404-0 | 45 | PLUG-NYLON | 1 | 690191-1 | PAD LETTER | CRIMP HEIGHT | WIRE SIZE | |
| 4 | CRIMPER SPAC. BLOCK | 1 | 1-238011-7 | 46 | BLOCK-INS. ADJ. | 1 | 690402-1 | A | .073 | 16 | |
| 5 | SHEAR DEPRESSOR-FRONT 692930-4 | 1 | 690539-3 | 47 | SCREW-SHOULDER | 1 | 22353-8 | B | .065 | 18 | |
| 6 | SHEAR DEPRESSOR-REAR | 1 | 690468-1 | 48 | CAM | 1 | 690602-2 | C | .061 | 20 | |
| 7 | DEPRESSOR SPACER-REAR | 1 | 1-240641-0 | 49 | CRIMPER BOLT | 1 | 7-21002-9 | D | NOT USED | | |
| 8 | ANVIL | 1 | 690512-7 | 50 | | | | CRIMP | SIZE | TYPE | FEED |
| 9 | FLOAT-SHEAR-FRONT 454276-1 | 1 | 690540-5 | 51 | | | | WIRE | .090 | F | |
| 10 | SHEAR HOLDER-FRONT | 1 | 690459-1 | 52 | XXXXXXXXXXXXX Feed Arm | 1 | 690544-1 | INSUL. | .110 | O | .991 |
| 11 | SHEAR STOP | 2 | 690461-1 | 53 | FEED FINGER Holder | 1 | 690541-1 | INSULATION RANGE | | WIRE RANGE | |
| 12 | SHEAR SPRING | 2 | 5-22280-0 | 54 | FEED FINGER SPRING | 1 | 691499-1 | .070 - .100 | | #20 - #16 | |
| 13 | FLOAT-SHEAR-REAR | 1 | 690463-2 | 55 | FEED FINGER PIN | 1 | 690545-1 | EXPLODED VIEW | | SET UP GAGE | |
| 14 | SHEAR HOLDER-REAR | 1 | 691314-1 | 56 | FEED PAWL | 1 | 690542-1 | A-6033-5, -6 | | 679130-1 | |
| 15 | SHEAR PLATE-REAR | 1 | 691313-1 | 57 | Cotter Pin 5/64 Dia 223460 | 1 | 690543-1 | REMARKS: | | | |
| 16 | CHIP GUARD-FRONT | 1 | 691667-3 | 58 | HOUSING 458009-1 | 1 | 690547-1 | Pre Feed | | | |
| 17 | CHIP GUARD-REAR | 1 | 691668-2 | 59 | CAP 240767-3 | 1 | 240767-1 | Amp-O-lectric | | | |
| 18 | TERMINAL HOLDER Spacer | 1 | 690753-1 | 60 | WEAR PLATE | ± | 240816-1 | | | | |
| 19 | STRIPPER 453591-1 | 1 | 690472-1 | 61 | ROD-FEED 454398-2 | 1 | 240817-1 | | | | |
| 20 | ARM, WIRE STOP | 1 | 453590-2 | 62 | ROLLER-CAM | 1 | 240658-1 | | | | |
| 21 | SPRING-FEED RETURN | 1 | 2-22288-9 | 63 | PIN-CAM ROLLER 240659-3 | 1 | 240659-1 | | | | |
| 22 | ANCHOR-SPRING | 1 | 690564-1 | 64 | SCREW-ADJ. | 1 | 240632-1 | | | | |
| 23 | FRONT STRIP GUIDE 690438-1 | 1 | 690561-1 | 65 | BLOCK-PIVOT | 1 | 690538-1 | | | | |
| 24 | REAR STRIP GUIDE | 1 | 2-690440-2 | 66 | LEVER-INTERMEDIATE | 1 | 690537-1 | | | | |
| 25 | DRAG-STOCK | 1 | 240792-1 | 67 | BUSHING | 1 | 240633-1 | | | | |
| 26 | DRAG RELEASE LEVER | 1 | 240793-1 | 68 | SHAFT-PIVOT | 1 | 240626-1 | | | | |
| 27 | DRAG SPRING | 2 | 1-22284-1 | 69 | PLATE ADJ. 240628-1 | 1 | 240628-1 | | | | |
| 28 | SHOULDER SCREW | 1 | 22353-9 | 70 | HEX NUT | 1 | 22594-8 | | | | |
| 29 | STRIP GUIDE PLATE | 1 | 692168-1 | 71 | SPACER | 1 | 690517-1 | | | | |
| 30 | BASE BLOCK | 1 | 690430-2 | 72 | Spring Assist | 2 | 690603-1 | ■ DENOTES WEARING PARTS RECOMMEND PURCHASE REPLACEMENT | | | |
| 31 | SCREW BLOCK | 1 | 690431-2 | 73 | Strip Guide Cover Plate | | | THIS APPLICATOR IS TO BE USED ON | | | |
| 32 | ADJ. SCREW | 1 | 690432-1 | 74 | Depressor SPA Front | 1 | 690407-8 | MACH. SERIAL NO. | | DIST. 66 | |
| 33 | BASE PLATE | 1 | 690429-1 | 75 | Rubber Bumper | 1 | 811242-2 | MACH. PARTS LIST 565435-5 | | DESIGNED 7-23-70 BANKS | |
| 34 | SCREW SHLD. | 1 | 456567-1 | 76 | Hex Nut | 1 | 21018-5 | APPL. SERIAL NO. | | DATE SHIPPED | |
| 35 | POST-RAM 690217-1 | 1 | 690217-1 | 77 | | | | CUSTOMER NAME AND ADDRESS | | CHARTER 7-24-70 L.L.M. | |
| 36 | SPRING WASHER 22480-5 | 1 | 690155-1 | 78 | | | | APPLICATOR NUMBER H2 | | REV 686958-3 | |
| 37 | DISC-WIRE | 1 | 3-692155-2 | 79 | Guard 455755-4 | 1 | 690511-1 | APPL. SERIAL NO. | | DATE SHIPPED | |
| 38 | DISC-INSULATION | 1 | 690142-1 | REV. REVISION RECORD | | | DATE | BY | ECN | SHEET 1 OF 2 | |
| 39 | SPRING-COMPRESSION | 2 | 690170-1 | A | REV PER ECN | 11-18-70 | BY L-7936 | | | | |
| 40 | BALL STEEL | 2 | 23241-6 | B | REV PER ECN | 12-14-70 | BY L-7975 | | | | |
| 41 | DISC SPACER | | | B1 | PER SUPP. | 12-18-70 | BY L-7975 | | | | |
| 42 | WASHER RAM | 1 | 690124-1 | C | REV PER ECN | 7-26-71 | BY L-8411 | | | | |

RELEASED FOR PUBLICATION JULY, 1986.

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 1986

H DELETE ITEMS IN R.C. 3-2-70

F REV PER ECN R1002 JAN 2-17-75
 G REV PER ECN R-2789 JUN 12/13/78
 H1 0150-6785-96
 H2 0150-9043-97 JAN 1-99
 D REV PER ECN 3-21-70 BY L-8782
 E REV PER ECN 5-21-73 BY L-8755
 For Sheet #2 See 1-687012-0

RESTRICTED TO

CUSTOMER AND ASSEMBLY DRAWING CASE CODE 00779