



NOTE:-

1. BATCH No. & PART No. BREAKDOWN.

DEUTSCH ASDD2\*\*-\*P/S\* RP654321

SERIES  
SHELL STYLE

BATCH NUMBER EXAMPLE  
KEYWAY ORIENTATION  
P=PIN OR S=SOCKET  
ARRANGEMENT

SHELL SIZE	A REF	B ±0.20	φC ±0.10	φD +0.0/-0.13	E +0.15/-0.0	F ±0.10	φG MAX	φH ±0.10	L MAX
8	16.50	21.40	3.25	12.00	17.17	15.98	11.10	14.50	27.20
10	19.50	25.90	3.25	15.00	17.17	15.98	14.27	17.40	32.00
12	24.00	29.10	3.25	19.05	17.17	15.98	17.44	21.90	35.20
14	27.00	32.50	3.25	22.22	17.17	15.98	20.60	25.00	38.40
16	30.30	34.80	3.25	25.40	17.17	15.98	23.77	28.20	41.00

AA	DUK-66990	WES	NDL	NDL	CEO	30/06/16
A	52430	NDL	JAK	IKG	KW	12/05/06
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. B.U.	DATE

MATERIAL

HEAT TREATMENT & FINISH

APP. I.E.D.

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH LTD. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH LTD.

SCALE

N.T.S.

GENERAL TOLERANCES UNLESS OTHERWISE STATED.  
±0.4mm ON WHOLE NUMBERS  
±0.2mm ON ONE PLACE DECIMALS  
±0.1mm ON TWO PLACE DECIMALS  
±1/2° ON ANGLES  
±0.05mm ON DRILLED HOLES

REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.

DIMS. IN MILLIMETRES



DEUTSCH LTD

ST LEONARDS-ON-SEA, EAST SUSSEX, TN38 9RF, TEL:(01424)852721

TITLE  
ASDD RECEIPT TYPE 2  
ENVELOPE DETAILS

DRAWING NUMBER

610285-ENV