

Single Port Modular Jacks

Product Facts


- Meets or exceeds FCC Part 68 rules and regulations: REA PE-76; and UL 1863, **Communication Circuit** Accessories
- Meets 1000 volt dielectric requirement Contact to Contact
- Available in both top and side entry (Right-Angle)
- Designed for direct mounting on pc boards
- Designed for ease of soldering and board cleaning
- Available in both shielded and unshielded versions
- Shielded jack available with two grounding paths - pc board and panel
- 20 dB shielding effectiveness from 30 MHz to 400 MHz
- Selectively gold plated contacts for lower cost
- All jacks are UL 94V-0 flame retardant polyester, standard color black, unless specified otherwise
- **■** Listed by Underwriters Laboratories Inc., File No. E81956



■ Certified by Canadian Standards Association, (\$60) File No. LR 7189A



A copy of the certificate is available upon request



Specifications

Electrical

Current Rating — 1.5 amp max. @ 25°C, derated to 0.2 amp max. @ 70°C

Voltage Rating — 150 volts AC max. Dielectric Withstanding Voltage — 1000 VAC, RMS, 60 Hz, 1 min. Contact to Contact

Mechanical

PC Board Retention - will not dislodge from pc board when subjected to 1 lb. [4.4N] pull before soldering and 10 lb. [44N] pull after soldering

Durability — 750 mating cycles

Material and Finish

Housing — Through-hole: Polyester (wave solder compatible), UL 94V-0 rated: Surface Mount: Polyphenylene Sulfide, or High Temp Nylon, UL 94V-0

Contact — .014 [0.36] thk. Phosphor bronze; plated .000050 [0.00127] gold in contact area and .000150 [0.00381] tin-lead on solder tails, over .000050 [0.00127] nickel underplate

Technical Documents

Application Specifications

114-02048 114-6040

Product Specifications

108-01163 108-01163-1

108-01163-3

108-01163-4 108-01163-7

www.tycoelectronics.com




Side Entry (RA), Thru-Hole



| | | | | | | | ~ |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
| 215875-1 | 4/4 | Without | No | Cat 3 | Without | No | Without |
| 2-215875-1 | 4/4 | Without | No | Cat 3 | Without | No | Without |
| 5520249-2 | 4/4 | Without | No | Cat 3 | With | No | Without |
| 215876-2 | 6/4 | Without | No | Cat 3 | Without | No | Without |
| 5555140-2 | 6/4 | Without | Yes | Cat 3 | With | No | Panel and PCB |
| 5555163-2 | 6/4 | Without | No | Cat 3 | With | No | Without |
| 1-215876-3 | 6/6 | Without | No | Cat 3 | Without | No | Without |
| 215876-1 | 6/6 | Without | No | Cat 3 | N/A | No | Without |
| 5520250-3 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 5555003-1 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 5555140-1 | 6/6 | Without | Yes | Cat 3 | With | No | Panel and PCB |
| 5555154-1 | 6/6 | Without | Yes | Cat 3 | With | No | PCB Ground |
| 5555163-1 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 5555165-1 | 6/6 | Without | No | Cat 3 | Without | No | Without |
| 106066-2 | 8/8 | Without | Yes | Cat 3 | Without | No | Panel and PCB |
| 1116062-2 | 8/8 | Without | Yes | Cat 5 | Without | No | Panel and PCB |
| 1116503-2 | 8/8 | Without | Yes | Cat 5 | Without | No | PCB Ground |
| 6116526-1 | 8/8 | Without | Yes | Cat 5 | Without | No | PCB Ground |
| 1-215877-3 | 8/8 | Without | No | Cat 3 | Without | No | Without |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Low Profile, Face Shield



| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 5555162-1 | 8/8 | Without | No | Cat 3 | With | No | Without |
| 5555164-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 1-5406299-1 | 8/8 | Without | Yes | Cat 5 | Without | No | Panel and PCB |
| 1-1734264-1 | 8/8 | Without | Yes | Cat 3 | Without | No | Panel and PCB |
| 1734579-1 | 8/8 | Without | Yes | Cat 3 | Without | No | PCB Ground |
| 215877-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 2-215877-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 2-215878-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 2-5338556-1 | 8/8 | Without | Yes | Cat 3 | Without | No | Panel and PCB |
| 3-5338556-1 | 8/8 | Without | Yes | Cat 3 | Without | No | Panel and PCB |
| 5406217-1 | 8/8 | Without | Yes | Cat 5 | Without | No | Panel and PCB |
| 5406296-1 | 8/8 | Without | Yes | Cat 5 | Without | No | Panel and PCB |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Note: All part numbers are RoHS compliant.



Side Entry (RA), Thru-Hole


Low Profile, Face Shield (Continued)




| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 5406299-1 | 8/8 | Without | Yes | Cat 5 | Without | No | Panel and PCB |
| 1-406525-1 | 8/8 | Without | No | Cat 5 | Without | Yes | Without |
| 1-406541-1 | 8/8 | Without | Yes | Cat 5 | Without | Yes | Panel and PCB |
| 5520243-4 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 5520251-4 | 8/8 | Without | No | Cat 3 | With | No | Without |
| 5520426-4 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 5555141-1 | 8/8 | Without | Yes | Cat 3 | Without | No | Panel and PCB |
| 5555153-1 | 8/8 | Without | Yes | Cat 3 | With | No | PCB Ground |
| 5555153-3 | 8/8 | Without | Yes | Cat 3 | With | No | PCB Ground |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Side Entry (RA), Thru-Hole





| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 5555166-1 | 8/8 | Without | No | Cat 3 | With | No | Without |
| 5555167-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 5557785-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 5557789-1 | 8/8 | Without | Yes | Cat 3 | Without | No | PCB Ground |
| 5557791-1 | 8/8 | Without | Yes | Cat 3 | Without | No | Panel and PCB |
| 5558341-1 | 8/8 | Without | No | Cat 5 | Without | No | Without |
| 5558342-1 | 8/8 | Without | Yes | Cat 5 | Without | No | PCB Ground |
| 5558344-1 | 8/8 | Without | Yes | Cat 5 | Without | No | Panel and PCB |
| 5569115-1 | 8/8 | Without | Yes | Cat 3 | With | No | Panel and PCB |
| 5569118-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 6116075-1 | 8/8 | With | Yes | Cat 5 | Without | Yes | PCB Ground |
| 6116173-1 | 8/8 | With | Yes | Cat 5 | Without | Yes | Panel and PCB |
| 6364139-5 | 8/8 | With | No | Cat 5 | Without | Yes | Without |
| 1734509-2 | 8/8 | With | Yes | Cat 3 | Without | No | PCB Ground |
| 5406533-1 | 8/8 | With | No | Cat 5 | Without | Yes | Without |
| 2-406549-1 | 8/8 | With | Yes | Cat 5 | Without | Yes | Panel and PCB |
| 2-406549-4 | 8/8 | With | Yes | Cat 5 | Without | Yes | Panel and PCB |
| 5569564-1 | 8/8 | With | Yes | Cat 3 | Without | No | Panel and PCB |
| 1734542-5 | 10/10 | Without | No | Cat 3 | Without | No | Without |
| 5558065-1 | 10/10 | Without | No | Cat 3 | Without | No | Without |
| 5558067-1 | 10/10 | Without | Yes | Cat 3 | Without | No | PCB Ground |
| 5558070-1 | 10/10 | Without | Yes | Cat 3 | Without | No | Panel and PCB |


Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)


Note: All part numbers are RoHS compliant.

www.tycoelectronics.com



Side Entry (RA), Surface Mount






1339212-1

| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 6339212-1 | 6/6 | Without | Yes | Cat 3 | Without | Yes | Panel and PCB |
| 5406514-2 | 6/6 | Without | No | Cat 3 | Without | Yes | Without |
| 5555077-1 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 6339160-1 | 8/8 | Without | Yes | Cat 3 | Without | Yes | Panel and PCB |
| 5406721-1 | 8/8 | Without | No | Cat 3 | With | Yes | Without |
| 5406721-2 | 8/8 | Without | No | Cat 3 | With | Yes | Without |
| 5558178-1 | 8/8 | Without | Yes | Cat 3 | With | No | PCB Ground |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Top Entry, Thru-Hole



Shielded 557484-1


| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 5520257-2 | 4/4 | Without | No | Cat 3 | With | No | Without |
| 5406010-2 | 6/2 | Without | No | Cat 3 | Without | No | Without |
| 5520258-2 | 6/4 | Without | No | Cat 3 | With | No | Without |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Note: All part numbers are RoHS compliant.



Top Entry, Thru-Hole




| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 5520425-2 | 6/4 | Without | No | Cat 3 | Without | No | Without |
| 216548-1 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 216564-1 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 5520258-3 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 5520425-3 | 6/6 | Without | No | Cat 3 | Without | No | Without |
| 5554990-1 | 6/6 | Without | No | Cat 3 | With | No | Without |
| 100616-1 | 8/8 | Without | Yes | Cat 3 | With | No | PCB Ground |
| 100616-2 | 8/8 | Without | Yes | Cat 3 | With | No | PCB Ground |
| 6116202-1 | 8/8 | Without | Yes | Cat 5 | Without | No | PCB Ground |
| 216550-1 | 8/8 | Without | No | Cat 3 | With | No | Without |
| 216566-1 | 8/8 | Without | No | Cat 3 | With | No | Without |
| 5520259-4 | 8/8 | Without | No | Cat 3 | With | No | Without |
| 5555799-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 5556416-1 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 5557484-1 | 8/8 | Without | Yes | Cat 3 | With | No | Panel and PCB |
| 5557730-1 | 8/8 | Without | Yes | Cat 3 | With | No | Panel and PCB |
| 5557969-1 | 8/8 | Without | Yes | Cat 3 | With | No | Panel and PCB |
| 5557969-2 | 8/8 | Without | Yes | Cat 3 | With | No | Panel and PCB |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Top Entry, Surface Mount

6-Position



Top or Bottom Entry Part Number 1-338088-3

| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 1-338084-3 | 4/4 | Without | No | Cat 3 | Without | No | Without |
| 1-338086-3 | 6/6 | Without | No | Cat 3 | Without | No | Without |
| 2-338086-3 | 6/6 | Without | No | Cat 3 | Without | No | Without |
| 1-338088-3 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 2-338088-3 | 8/8 | Without | No | Cat 3 | Without | No | Without |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Note: All part numbers are RoHS compliant.

www.tycoelectronics.com



Top Entry, Press Fit




Part Number 1116201-1

| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 6116201-1 | 8/8 | Without | No | Cat 5 | Without | No | Without |
| 6116201-2 | 8/8 | Without | No | Cat 5 | Without | No | Without |
| 6116202-1 | 8/8 | Without | Yes | Cat 5 | Without | No | PCB |
| 6116418-1 | 8/8 | Without | Yes | Cat 5 | Without | No | Panel and PCB |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Bottom Entry, Thru-Hole



Part Number 216444

| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 216444-1 | 4/4 | Without | No | Cat 3 | Without | No | Without |
| 216446-1 | 6/6 | Without | No | Cat 3 | Without | No | Without |


Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Note: All part numbers are RoHS compliant.



Bottom Entry, Surface Mount

6-Position



Top or Bottom Entry Part Number 1-338088-3


| Part Number | Positions/ Contacts | LEDs | Shielded | Performance | Panel Stops | Inverted | Ground Options |
|----------------|------------------------|---------|----------|-------------|----------------|----------|-------------------|
| 100860-1 | 6/6 | Without | No | Cat 3 | Without | No | Without |
| 1-338088-5 | 8/8 | Without | No | Cat 3 | Without | No | Without |
| 2-100860-1 | 6/6 | Without | No | Cat 3 | Without | No | Without |

Note: Consult Tyco Electronics Sales Representative for additional Part Numbers and features differences (tail length, LED color, IRR, etc.)

Shorting Unshielded



| Positions/ Contacts | Shorting | Configuration | Tray Packaging Part No. |
|------------------------|-----------|-----------------------------|----------------------------|
| 8/8 | 1-4 & 2-5 | RJ 48X | 5557788-1 |
| 8/8 | 3-5 & 4-6 | IBM Token Ring Emulation | 5569972-1 |



Short is removed by insertion of modular plug.

Shielded



IBM is a trademark of International Business Machine Corporation.

Note: All part numbers are RoHS compliant.

| Positions/ Contacts | Shorting Configuration | | Panel Grounds | Tray Packaging Part Numbers |
|------------------------|------------------------|-----------------------------|---------------|--------------------------------|
| 8/8 | 1-4 & 2-5 | RJ 48X | _ | 5557789-1 |
| 8/8 | 1-4 & 2-5 | RJ 48X | Υ | 5557791-1 |
| 8/8 | 3-5 & 4-6 | IBM Token Ring Emulation | _ | 5569972-1 |

NOTE: SHIELDED PRODUCT WITH PANEL GROUNDS ALWAYS CONTAINS PCB GROUNDS