



REVISIONS

| P | LTR | DESCRIPTION              | DATE      | DWN | APVD |
|---|-----|--------------------------|-----------|-----|------|
|   | BA  | NEW RELEASE              | 30SEP09   | MRS | St.P |
|   | BA1 | DRAWING DIMENSION UPDATE | 31MAY2025 | SY  | GT   |
|   |     |                          |           |     |      |
|   |     |                          |           |     |      |

FOR FURTHER INFORMATION SEE DATA SHEET FOR  
SERIES LR, METAL FILM FIXED RESISTORS



RoHS Compliant

|                                                                                       |  |                                        |  |                                                                                                                 |  |                  |  |                 |  |            |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------|--|-----------------------------------------------------------------------------------------------------------------|--|------------------|--|-----------------|--|------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>MAHARUDRA<br>30-SEP-09          |  | <div>TE Connectivity</div> |  |                  |  |                 |  |            |  |
| DIMENSIONS:<br><br>mm                                                                 |  | CHK<br>ALLAN.P<br>30-SEP-09            |  |                                                                                                                 |  |                  |  |                 |  |            |  |
|                                                                                       |  | APVD<br>STEPHEN.P<br>30-SEP-09         |  |                                                                                                                 |  |                  |  |                 |  |            |  |
|  |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | NAME<br>METAL FILM FIXED RESISTORS<br>TYPE LR0204 SERIES                                                        |  |                  |  |                 |  |            |  |
|                                                                                       |  | 0 PLC ±0.2                             |  |                                                                                                                 |  |                  |  |                 |  |            |  |
|                                                                                       |  | 1 PLC ±0.1                             |  |                                                                                                                 |  |                  |  |                 |  |            |  |
|                                                                                       |  | 2 PLC ±                                |  |                                                                                                                 |  |                  |  |                 |  |            |  |
|                                                                                       |  | 3 PLC ±                                |  |                                                                                                                 |  |                  |  |                 |  |            |  |
| 4 PLC ±                                                                               |  | PRODUCT SPEC                           |  | SIZE<br>CAGE CODE<br>DRAWING NO<br>RESTRICTED TO                                                                |  |                  |  |                 |  |            |  |
| ANGLES ±5°                                                                            |  | -                                      |  |                                                                                                                 |  |                  |  |                 |  |            |  |
| APPLICATION SPEC                                                                      |  | -                                      |  |                                                                                                                 |  |                  |  |                 |  |            |  |
| MATERIAL<br>-                                                                         |  | FINISH<br>-                            |  | WEIGHT<br>-                                                                                                     |  | A300779C-1622176 |  | -               |  |            |  |
| CUSTOMER DRAWING                                                                      |  |                                        |  |                                                                                                                 |  | SCALE<br>10:1    |  | SHEET<br>1 OF 1 |  | REV<br>BA1 |  |