

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
1		INITIAL CUSTOMER DRAWING	04JUN2018	AFK	LS

VIEW A:  
LAYING DIAGRAM



PRODUCT CODE	PRODUCT PITCH	No. HOLES	LABEL LENGTH	PRINTABLE LENGTH	LABEL HEIGHT
HL104**TS025	12.7 (1/2")	4	45	25	10.4
HL104**TS033	12.7 (1/2")	4	53	33	10.4
HL104**TS038	12.7 (1/2")	4	58	38	10.4
HL104**TS050	12.7 (1/2")	4	70	50	10.4
HL104**TS070	12.7 (1/2")	4	90	70	10.4
HL150**TS025	25.4 (1")	4	45	25	15.0
HL150**TS033	25.4 (1")	4	53	33	15.0
HL150**TS038	25.4 (1")	4	58	38	15.0
HL150**TS050	25.4 (1")	4	70	50	15.0
HL150**TS070	25.4 (1")	4	90	70	15.0
HL203**TS025	25.4 (1")	4	45	25	20.3
HL203**TS033	25.4 (1")	4	53	33	20.3
HL203**TS038	25.4 (1")	4	58	38	20.3
HL203**TS050	25.4 (1")	4	70	50	20.3
HL203**TS070	25.4 (1")	4	90	70	20.3
HL253**TS025	50.8 (2")	4	45	25	25.3
HL253**TS033	50.8 (2")	4	53	33	25.3
HL253**TS038	50.8 (2")	4	58	38	25.3
HL253**TS050	50.8 (2")	4	70	50	25.3
HL253**TS070	50.8 (2")	4	90	70	25.3

MATERIAL LIST

- 1. PAPER CARRIER - WHITE
- 2. CABLE LABEL

NOTES:-

- 1. NO ACCUMULATIVE ERROR THROUGH PACK IS ACCEPTABLE
- 2. PACKAGING AS REQUIRED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AFK	04JUN2018	TE Connectivity	
DIMENSIONS: mm		CHK -	APVD -		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.5 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -		PRE TAPED THERMAL TRANSFER CABLE LABEL ASSEMBLY	
MATERIAL -		FINISH -		APPLICATION SPEC -	
		WEIGHT ---		SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-1905A0025	RESTRICTED TO -
		SCALE ---		SHEET 1 OF 1	REV 1