	4		3
	THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION ALL RIGHTS RESERVED.	-,
D			
С			
Β			
A			

')		
~		

		REVISIONS			
Ρ	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	PART STATUS UPDATED	25JAN2018	RK	ΡS

<u>NOTES:</u>

⚠ MATERIAL: POLYPHENYLENE OXIDE UL94V-0, BLACK.

2 POSITION HAS RDI LOGO OMITTED.

3. FOR USE WITH 6 SERIES BARRIER STRIPS.

.270

.250

2-1437661-7

В

С

D

	x
TC6-16-PFH	4-1437661-7
TC6-15-PFH	4-1437661-6
TC6-14-PFH	1-1776050-4
TC6-13-PFH	1-1776050-3
TC6-12-PFH	4-1437661-5
TC6-11-PFH	7-1437661-4
TC6-10-PFH	4-1437661-4
TC6-09-PFH	4-1437661-2
TC6-08-PFH	4-1437661-0
TC6-07-PFH	3-1437661-8
TC6-06-PFH	3-1437661-7

				2.211		0		100 00 1111	5 115/001
				1.866		5		TC6-05-PFH	3-1437661-4
				1.491		4		TC6-04-PFH	3-1437661-2
				1.116		3		TC6-03-PFH	2-1437661-9
			ØBSOLETE	.741		2		TC6-02-PFH	2-1437661-7
				DIM A	\	NO. OF	POS.	CATALOG NUMBER	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			CHK	23MAY03 5/23/03		ł	57	TE Conr	nectivity Ltd.
DIMENSIONS: INCHES 0 PLC ± - 1 PLC ± - 2 PLC ± -			S YODER APVD S YODER PRODUCT SPEC	APVD 5/23/03 NAME SYODER TC6-XX-PEH TERMINAL BL					CK COVER
		2 PLC ± - 3 PLC ± .010 4 PLC ± - ANGLES ± -	APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWIN		RESTRICTED TO
		FINISH	WEIGHT	A	42	00779	C-	2-1437661-7	—
			CUSTOMER DR	AWING				SCALE 4:1 SHEET	1 OF 1 REV D2

5.991

5.616

5.241

4.866

4.491

4.116

3.741

3.366

2.991

2.616

2.241

16

15

14

13

12

11

10

9

8

7

6

.195

OBSOLETE

OBSOLETE

OBSOLETE

.625 -

А