





P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED	25NOV2009	Y.O	T.K
	D	REVISED	31MAY2022	M.J	T.S



1. MATERIAL: GLASS FILLED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".



40	Y	19	38.0	40.9	42.6	2-1827863-0
40	X	19	38.0	40.9	42.6	1-1827863-0
34	Y	16	32.0	34.9	36.6	2-1827863-7
34	X	16	32.0	34.9	36.6	1-1827863-7
32	X	15	30.0	32.9	34.6	1-1827863-6
30	X	14	28.0	30.9	32.6	1-1827863-5
28	X	13	26.0	28.9	30.6	1-1827863-4
26	Y	12	24.0	26.9	28.6	2-1827863-3
26	X	12	24.0	26.9	28.6	1-1827863-3
24	X	11	22.0	24.9	26.6	1-1827863-2
22	X	10	20.0	22.9	24.6	1-1827863-1
POS	KEY	n	A	B	C	PART NO



40POS(X-KEY): 1-1827863-0

THIS DRAWING IS A CONTROLLED DOCUMENT.
















DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	$\pm 0.3, \pm 5^\circ$
	0 PLC $\pm$
	1 PLC $\pm$
	2 PLC $\pm$
	3 PLC $\pm$
	4 PLC $\pm$
	ANGLES $\pm$
MATERIAL	FINISH
	-

DWN	T. KUDO	16MAR2005
CHK	D. MITSUGI	23AUG2005
APVD	D. MITSUGI	23AUG2005
PRODUCT SPEC	108-78268, 78298	
APPLICATION SPEC	114-5377	
WEIGHT	-	
CUSTOMER DRAWING		



NAME			
DYNAMIC D1100D 2.0mm PITCH			
REC HSG			
22-40POS			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1827863	-
SCALE		SHEET	REV
2:1		1 OF 3	D

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			





22POS(X-KEY): 1-1827863-1

26POS(X-KEY): 1-1827863-3







28POS(X-KEY): 1-1827863-4

30POS(X-KEY): 1-1827863-5

32POS(X-KEY): 1-1827863-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. KUDO 16MAR2005	 TE Connectivity	
DIMENSIONS: mm		CHK D. MITSUGI 23AUG2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.3, ± 5°		APVD D. MITSUGI 23AUG2005	NAME DYNAMIC D1100D 2.0mm PITCH	
		PRODUCT SPEC 108-78268, 78298	REC HSG 22-40POS	
MATERIAL SEE SHEET 1		FINISH -	APPLICATION SPEC 114-5377	RESTRICTED TO -
		WEIGHT -	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-1827863	SCALE 2:1
			SHEET 2 OF 3	REV D

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



34POS(X-KEY): 1-1827863-7

24POS(X-KEY): 1-1827863-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. KUDO 16MAR2005		
DIMENSIONS: mm		CHK D. MITSUGI 23AUG2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±5°		APVD D. MITSUGI 23AUG2005	NAME DYNAMIC D1100D 2.0mm PITCH	
		PRODUCT SPEC 108-78268, 78298	REC HSG	
MATERIAL SEE SHEET 1		FINISH -	22-40POS	
		APPLICATION SPEC 114-5377	SIZE A3	CAGE CODE 00779
		WEIGHT -	DRAWING NO C-1827863	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 2:1	SHEET 3 OF 3
				REV D