





WHEN ORDERING CONTACT ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:


2. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL—
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
3. FOR USE WITH 4/8 INDENT STRIPPER CRIMP—
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL



SECTION X—X



- 1 MATERIAL: COPPER ALLOY PER MIL-C-39029 & MIL-DTL-24308.
- 2 ALL DIMENSIONS APPLY AFTER PLATING.
- 3 ---
- 4 ALL DIAMETERS CONCENTRIC WITH EACH OTHER WITHIN .004 T.I.R.
- 5 PIN MATES WITH SOCKET 205090 (AS 39029/63).
- 6 ALL SURFACES HAVE $\sqrt{63}$ OR BETTER FINISH, UNLESS SHOWN.
- 7 POINT OF PLATING MEASUREMENT .188 [4.78] FROM TIP OF PIN.
- 8 PLATING: GOLD PER ASTM-B-488 (TYPE II) OVER NICKEL PER AMS-QQ-N-290.
- 9 PLATING: GOLD PER ASTM-B-488 (TYPE II) OVER COPPER PER AMS 2418, .000050 MIN THK.
- 10 PLATING: GOLD PER ASTM-B-488 (TYPE II, CLASS 0) OVER NICKEL PER AMS-QQ-N-290.
- 11 PLATING:
MATING AREA: GOLD PER ASTM-B-488 (TYPE II) OVER NICKEL PER AMS-QQ-N-290.
NON MATING AREA: GOLD PER ASTM-B-488 OVER NICKEL PER AMS-QQ-N-290.
- 12 MANUFACTURER'S LOGO ("A" OR "— . .") LOCATION OPTIONAL
- 13 CONTACTS QUALIFIED TO AS39029/64-369
- 14 CONTACTS QUALIFIED TO GSFC-S-311-P-4/10, NASA P/N G-10-P1
- 15 RESTRICTED PART NUMBER.
- 16 CONTACTS MUST MEET DIMENSIONAL & PERFORMANCE REQUIREMENTS OF GSFC-S-311-P-4/08, NASA P/N G-10-P1 & 100% RESIDUAL MAGNETISM.



COLOR BANDS
PART NO 205089-1
AND 2-205089-1 ONLY

- ORANGE COLOR CODE BAND
- BLUE COLOR CODE BAND
- WHITE COLOR CODE BAND

16	WITHOUT COLOR CODE	9	2-205089-6
15			2-205089-4
15			2-205089-2
15			2-205089-1
13	WITHOUT COLOR CODE	8	1-205089-1
13	WITHOUT COLOR CODE	10	1-205089-0
14	WITHOUT COLOR CODE	9	205089-4
13	CONTACT ON TAPE	SAME AS -1	205089-2
13	AS SHOWN	11	205089-1
	DESCRIPTION	PLATING	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. KAISER 25AUG2003	TE Connectivity	
DIMENSIONS: INCHES[mm]		CHK D. MILLER 10-13-03		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MILLER 10-13-03	NAME PIN SIZE 20 CONTACT, AMPLIMITE	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC — APPLICATION SPEC —	SIZE A2	
MATERIAL 1		WEIGHT 0.000000	CAGE CODE 00779	DRAWING NO C-205089
FINISH —		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1
			REV AB	