



213423-3 SHOWN

1. DUST COVER IS INSTALLED FOR SHIPPING. (QTY = 2)
2. KEYING SHOWN IN POSITION "01" FOR ILLUSTRATION ONLY. CONNECTORS SHIPPED WITH KEYING INSTALLED IN POSITION PER TABLE.

COMPONENT	MATERIAL	FINISH
SHELL	DIE CAST ALUMINUM PER ASTM-B-85	CHEMICAL CONVERSION COATING PER MIL-C-5541, CLASS 1A
INSERT RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	CHEMICAL CONVERSION COATING PER MIL-C-5541, CLASS 1A
SCREWS AND LOCKWASHERS	STEEL OR STAINLESS STEEL	CHROMATE OVER ZINC OR PASSIVATED
POLARIZING KEYS	ZINC ALLOY PER ASTM-B-86	ELECTROLESS NICKEL PER MIL-C-26074 CLASS 4, GRADE B
POLARIZING KEY RETAINING PLATE	ALUMINUM ALLOY PER ASTM-B-209	BLUE ANODIZED PER MIL-A-8625
ALL INSERTS	THERMOSET	-

NO CONTACTS INCLUDED	213423-3
NO CONTACTS INCLUDED	213422-2
212930-2 (SZ 22 POSTED SOCKET CONTACT; QTY=150) FOR MODULE A 208265-5 (SZ 20 POSTED PIN CONTACT; QTY=20) FOR MODULE B 222190-1 (SZ 8 TRIAX PIN CONTACT; QTY=4) FOR MODULE C 212930-2 (SZ 22 POSTED SOCKET CONTACT; QTY=150) FOR MODULE D 212930-2 (SZ 22 POSTED SOCKET CONTACT; QTY=100)	213423-1
CONTACTS INCLUDED AND INSTALLED	PART NUMBER

REMARKS	KEY POSITION	PART NO.
UNSEALED INSERTS	"31"	213423-3
SEALED INSERTS	"31"	213423-2
SEALED INSERTS	"31"	213423-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0. PL ± -	1. PL ± -	2. PL ± -	3. PL ± .005	4. PL ± -	ANGLES ± -
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT	SIZE	CAGE CODE	DRAWING NO.	RESTRICTED TO	
			A1	00779	213423		

CUSTOMER DRAWING SCALE NTS SHEET 1 OF 1 REV A

STE TE Connectivity

RCPT ASSY, MIL600, SIZE 3A (150/24C4/150/100)