

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Winter Wans Sep-09-25 CHN 15-Mar-17 Daniel Zhang Ricardo Robane		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DUOPLUG MARK II SIDE LOCKING	
		PRODUCT SPEC 108-18785-I APPLICATION SPEC 1114-18467-I		SIZE A 1	
MATERIAL - - -		WEIGHT - CUSTOMER DRAWING		DRAWING NO C=2306286 SCALE 8:1 SHEET 1 OF 2 RESTRICTED TO REB3	

REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

GWEPT 750°C NO FLAME & UL94-V0, SILVER PLATED VERSION																		
-		X	X	X	X	X	X	X	X	X	9	20.0	24.9	23.5	20.0	3.75	2/3	1-2369990-9 
Red							X	X	X	X	4	7.5	12.4	11.0	7.5	6.25	3/4	1-2369990-4 
Color Code 	10	9	8	7	6	5	4	3	2	1	POS.	A	B	C	D	E	 KEYING	PN Bestell-Nr.
CAVITIES LOADED																		

PA GF, GWEPT 750°C NO FLAME & UL94-V0, TIN PLATED VERSION																		
-	X	0	X	X	0	X	0	X	0	X	10	22.5	27.4	26	22.5	6.25	3/4	1-2306287-0
-	X	X	X	X	X	X	X	X	X	X						3.75	-	2-2306286-0
-	X	X	X	X	X	X	X	X	X	X						3.75	2/3	1-2306286-0
-		X	X	X	X	X	X	X	X	X	9	20	24.9	23.5	20	3.75	2/3	1-2306286-9
Black		X	X	X	X	X	X	X	X	X							2/3	2306286-9
Orange		X	X	0	X	0	X	X	0	X							2/3	4-2306287-9
-		X	0	X	0	X	0	X	0	X							2/3	3-2306287-9
-		X	0	X	X	0	X	0	X	X							2/3	2-2306287-9
-		X	X	0	X	0	X	0	X	X						-	-	1-2306287-9
Green		X	0	X	X	0	X	0	X	X	3.75	2/3	2306287-9					
Brown			X	0	X	0	X	X	X	X	8	17.5	22.4	21	17.5	3.75	2/3	2-2306287-8
Blue			X	X	X	0	X	X	0	X						3.75	2/3	1-2306287-8
			X	0	X	0	X	X	X	X						3.75	2/3	2306287-8
Black			X	X	X	X	X	X	X	X						3.75	2/3	2-2306286-8
-			X	X	X	X	X	X	X	X						11.25	5/6	1-2306286-8
-			X	X	X	X	X	X	X	X						3.75	2/3	2306286-8
				X	0	X	0	X	0	X	7	15	19.9	18.5	15	11.25	5/6	3-2306287-7
Black				X	0	X	0	X	0	X						8.75	4/5	2-2306287-7
-				X	0	X	0	X	0	X						3.75	2/3	1-2306287-7
Blue				X	0	X	0	X	0	X						3.75	2/3	2306287-7
				X	X	X	X	X	X	X						11.25	5/6	2-2306286-7
-				X	X	X	X	X	X	X						3.75	2/3	1-2306286-7
Black				X	X	X	X	X	X	X	3.75	2/3	2306286-7					
Black					X	X	X	X	X	X	6	12.5	17.4	16	12.5	3.75	2/3	5-2306286-6
RED					X	X	X	X	X	X						8.75	4/5	4-2306286-6
-					X	X	X	X	X	X						6.25	3/4	3-2306286-6
-					X	X	X	X	X	X						8.75	4/5	2-2306286-6
-					X	X	X	X	X	X						3.75	2/3	1-2306286-6
-					X	X	X	X	X	X						1.25	1/2	2306286-6
-					X	0	X	X	0	X						3.75	2/3	4-2306287-6
-					X	X	0	X	0	X						8.75	4/5	3-2306287-6
-					X	0	X	X	0	X						4/5	4/5	2-2306287-6
-					X	0	X	X	0	X						3.75	2/3	1-2306287-6
Black					X	0	X	X	0	X	3.75	2/3	2306287-6					
-						X	0	X	0	X	5	10	14.9	13.5	10	3.75	2/3	2-2306287-5
-						X	X	X	0	X						6.25	3/4	1-2306287-5
Blue						X	X	X	0	X						6.25	3/4	2306287-5
-						X	X	X	X	X						-	-	7-2306286-5
Grey						X	X	X	X	X						1.25	1/2	6-2306286-5
-						X	X	X	X	X						1.25	1/2	5-2306286-5
-						X	X	X	X	X						6.25	3/4	4-2306286-5
-						X	X	X	X	X						3.75	2/3	3-2306286-5
Green						X	X	X	X	X						1.25	1/2	2-2306286-5
Red						X	X	X	X	X						6.25	3/4	1-2306286-5
Black						X	X	X	X	X	3.75	2/3	2306286-5					
-							X	0	X	X	4	7.5	12.4	11	7.5	-	-	4-2306286-4
-							X	X	X	X						6.25	3/4	3-2306286-4
-							X	X	X	X						1.25	1/2	2-2306286-4
Red							X	X	X	X						6.25	3/4	1-2306286-4
Black							X	X	X	X						1.25	1/2	2306286-4
-								X	0	X	3	5	9.9	8.5	5	1.25	1/2	3-2306287-3
-									X	0						3.75	2/3	2-2306287-3
Green									X	0						1.25	1/2	1-2306287-3
Blue									X	0						3.75	2/3	2306287-3
Red									X	X						3.75	2/3	5-2306286-3
-									X	X						3.75	2/3	3-2306286-3
-									X	X						1.25	1/2	2-2306286-3
Black									X	X						3.75	2/3	1-2306286-3
Red									X	X						1.25	1/2	2306286-3
Color Code	10	9	8	7	6	5	4	3	2	1	POS.	A	B	C	D	E		PN Bestell-Nr.
CAVITIES LOADED																		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
Winter Wang
15-Mar-17

CHK
Daniel Zhong
15-Mar-17

APVD
Riccardo Robore
15-Mar-17

TE Connectivity

NAME
DUOPLUG MARK II
SIDE LOCKING

SIZE
A1

CAGE CODE
C=2306286

DRAWING NO
114-18467-1

RESTRICTED TO
-

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

±
±0.2
±0.2
±0.2
±0.2

±

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

108-18785-1
APPLICATION SPEC

114-18467-1
ANGLES

MATERIAL
-

FINISH
-

WEIGHT
-

CUSTOMER DRAWING

SCALE
8:1

SHEET
2

OF
2

REV
B31

4805 (3/13)