








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11JAN2020	SR	AP

TE2000 RIBBED



- NOTES:
1. POWER RATING: 2000W
 2. INSULATION RESISTANCE DC 500V - 20 M Ohms MIN.
 3. VOLTAGE RESISTABILITY: AC 2500V, 50Hz, 5s=<1mA
 4. TUBE BORE AND SIDE FACES SHOULD BE FREE OF PAINT
 5. PARTS SHALL BE BLANK, SMOOTH, FREE OF BURRS AND ALL OTHER FOREIGN MATERIAL
 6. FOR FURTHER INFORMATION SEE DATASHEET FOR TE SERIES HIGH POWER WIRE WOUND RESISTOR

TE2000 SMOOTH



RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUPREETH R 11JAN2020	TE Connectivity		
DIMENSIONS:		CHK ALLAN P 11JAN2020			
mm		APVD ALLAN P 11JAN2020	NAME TE 2000W RESISTOR SET		
		PRODUCT SPEC	1 X 12 VALUES 5%		
		APPLICATION SPEC			
		WEIGHT			
MATERIAL		CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779	DRAWING NO C-1879453
			SCALE 1:2	SHEET 1 OF 2	REV A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

R4081 SCHEDULE

SCHEDULE						
SL. NO	VALUE	TCPN	PRODUCT NUMBER	DESCRIPTION	QTY	STYLE
1	1.0Ω	1879456-1	TE2000B1R0J	TE 2000W 1R0 5% Bracket	1	RIBBED
2	2.0Ω	TBC	TE2000B2R0J	TE 2000W 2R0 5% Bracket	1	RIBBED
3	4.0Ω	TBC	TE2000B4R0J	TE 2000W 4R0 5% Bracket	1	RIBBED
4	8.0Ω	TBC	TE2000B8R0	TE 2000W 8R0 5% Bracket	1	RIBBED
5	16Ω	TBC	TE2000B16RJ	TE 2000W 16R 5% Bracket	1	RIBBED
6	32Ω	TBC	TE2000B32RJ	TE 2000W 32R 5% Bracket	1	RIBBED
7	64Ω	TBC	TE2000B64RJ	TE 2000W 64R 5% Bracket	1	RIBBED
8	128Ω	TBC	TE2000B128RJ	TE 2000W 128R 5% Bracket	1	SMOOTH
9	256Ω	TBC	TE2000B256RJ	TE 2000W 256R 5% Bracket	1	SMOOTH
10	512Ω	TBC	TE2000B512RJ	TE 2000W 512R 5% Bracket	1	SMOOTH
11	1.024KΩ	TBC	TE2000B1K024J	TE 2000W 1K024 5% Bracket	1	SMOOTH
12	2.048KΩ	TBC	TE2000B2K048J	TE 2000W 2K048 5% Bracket	1	SMOOTH

KIT TO BE PACKAGED IN TWO CARTONS AND LABELLED AS FOLLOWS:

2176438-1 R40811X12VJ TE 2000W RESISTOR SET 1 X 12 VALUES 5% CARTON 1			
SL. NO	PRODUCT NUMBER	DESCRIPTION	QTY
1	TE2000B1R0J	TE 2000W 1R0 5% Bracket	1
2	TE2000B2R0J	TE 2000W 2R0 5% Bracket	1
3	TE2000B4R0J	TE 2000W 4R0 5% Bracket	1
4	TE2000B8R0	TE 2000W 8R0 5% Bracket	1
5	TE2000B16RJ	TE 2000W 16R 5% Bracket	1
6	TE2000B32RJ	TE 2000W 32R 5% Bracket	1

2176438-1 R40811X12VJ TE 2000W RESISTOR SET 1 X 12 VALUES 5% CARTON 2			
SL. NO	PRODUCT NUMBER	DESCRIPTION	QTY
1	TE2000B64RJ	TE 2000W 64R 5% Bracket	1
2	TE2000B128RJ	TE 2000W 128R 5% Bracket	1
3	TE2000B256RJ	TE 2000W 256R 5% Bracket	1
4	TE2000B512RJ	TE 2000W 512R 5% Bracket	1
5	TE2000B1K024J	TE 2000W 1K024 5% Bracket	1
6	TE2000B2K048J	TE 2000W 2K048 5% Bracket	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.5

1 PLC ±0.1

2 PLC ±0.05

3 PLC ±

4 PLC ±

ANGLES ±0.5°

FINISH -

DWN SUPREETH R 11JAN2020

CHK ALLAN P 11JAN2020

APVD ALLAN P 11JAN2020

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAW ING

TE Connectivity

NAME

TE 2000W RESISTOR SET
1 X 12 VALUES 5%

SIZE

A2

CAGE CODE

00779

DRAWING NO

1879453

RESTRICTED TO

-

SCALE

1:2

SHEET

2

OF

2

REV

A

1471-9 (3/13)