




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-22-148284	09APR2022	WH	LC
	B	REVISED PER ECR-25-239947	24APR2025	NH	JH






ISOMETRIC MATING FACE VIEW
(12 POSITION SHOWN)




ISOMETRIC REAR VIEW
(12 POSITION SHOWN)


1. MATERIAL: NYLON,UL94 V-0, COLOR: NATURAL
2. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION.
3. RECOMMENDED MATING HEADER:[1-2375267-[1,[1-2384268-[]
4. THE HOUSING ACCEPTS TERMINALS: 2377991-1 OR 2377997-1
5. ACCEPT OPTIONAL TPA: 1-2132782-2 OR [1-1744544-[]



FRONT VIEW
(2 POSITION SHOWN)



FRONT VIEW
(3 POSITION SHOWN)



FRONT VIEW
(4 POSITION SHOWN)

45.68	12.42	48.08	12	1-2377130-2
41.72	8.46	44.12	11	1-2377130-1
37.76	12.42	40.16	10	1-2377130-0
33.80	8.46	36.20	9	2377130-9
29.84	12.42	32.24	8	2377130-8
25.88	8.46	28.28	7	2377130-7
21.92	12.42	24.32	6	2377130-6
17.96	8.46	20.36	5	2377130-5
14.36	12.42	16.40	4	2377130-4
10.40	8.46	12.44	3	2377130-3
6.44	4.50	8.48	2	2377130-2
DIM C	DIM B	DIM A	NO OF POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±0.4
±0.25
±
±
±3°
-

DWN
W. HUO
01JUN2021

CHK
D. ZHANG
03JUN2021

APVD
D. ZHANG
03JUN2021

PRODUCT SPEC
108-2297

APPLICATION SPEC
114-13265

WEIGHT
-

CUSTOMER DRAWING

NAME
RECEPTACLE HOUSING, NON-GWT,
SINGLE ROW, ECONOMY POWER II

SIZE
A

CAGE CODE
00779

DRAWING NO.
2377130

RESTRICTED TO
-

SCALE
N/A

SHEET
1

OF
1

REV
B