



P	LTR	DESCRIPTION	DATE	OWN	APVD
G		ECR-06-001266	17JAN2006	M. P.	
G1		REVISED PER ECN-22-133348	10JAN2022	AP	VN
G2		REVISED PER ECN-25-313663	27MAR2025	AP	VN

NUMERAZIONE INDICATIVA, POSIZIONE CONDUTTORI
(INDICATIVE CIRCUIT NUMBER)



GUIDE PER IL MONTAGGIO A PANNELLO
(SEATS FOR MOUNTING PANNEL)
CHIAVI DI POLARIZZAZIONE VEDERE TABELLA
(POLARIZATIONS KEYS SEE DWG.)



			SLIDE	1	4	BLACK	PA 66 30% C.V.		//
			SEALING	1	3	RED	SILICON RUBBER		//
			SECONDARY LOCK	2	2	BLACK	PBT 15% C.V.		//
OBSOLETE	SI, ENTRAMBI I LATI (BOTH SIDES)	2-12 8-18	MALE HSG.	1	1	BLACK	PA 66 30% C.V.	G	282278-4
	SI, ENTRAMBI I LATI (BOTH SIDES)	2-12 8-18	MALE HSG.	1	1	GREEN	PA 66-30% C.V.	G	282278-3
OBSOLETE	NO	2-12 8-18	MALE HSG.	1	1	BLUE	PA 66 30% C.V.	G	282278-2
	SI, ENTRAMBI I LATI (BOTH SIDES)	3-13 9-19	MALE HSG.	1	1	GREY	PA 66-30% C.V.	G	282278-1
	GUIDE MONT. A PANNELLO (SEATS FOR MOUNT. PANNEL.)	POSIZ. POLARIZ POLARYTY POS	COMPONENTE (COMPONENT)	Q.TY	ITEM	COLORE (COLOUR)	MATERIALE (MATERIAL)	REV.	NUMERO PART NUMBER

1) LE POSIZIONI 1, 10, 11 E 20 SONO ATTRIBUITE AI CONTATTI DI POTENZA
P/N 2-962916-1. LE RESTANTI SONO ATTRIBUITE AI CONTATTI DI SEGNALE
P/N 282288-1 E 282289-1.
(POS. ARE SUITABLE FOR CONTACT P/N 2-962916-1, ALL OTHER CAVITIES ARE
SUITABLE FOR CONTACTS P/N P/N 282288-1 E 282289-1).

2) MARCHI DI FABBRICA, CODICE FORNITORE E DATARIO
(TRADE MARCK, SUPPLIER CODE AND DATE CODE).

3) 282278-3 SUPERATO DA 282278-4
(282278-3 SUPERSEDED BY 282278-4).

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±0.3
1 PLC	±0.3
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±1°
MATERIAL	FINISH

CHK	M. PALMA	06 JUN 2005
APVD	O. CANUTO	06 JUN 2005
PRODUCT SPEC	A. GENTA	06 JUN 2005
APPLICATION SPEC	108-20117	
WEIGHT		

CUSTOMER DRAWING

TE Connectivity

20 PO. SEALED SECTIONING MALE
CONNECTOR KIT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	C=282278	-
SCALE	SHEET	OF	REV
-	1	1	G2