






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By Tyco Electronics JAPAN G.K. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-	A1	REDRAWN W/CHANGE	ECR-13-000281	16JAN2013	TS	KB



⊕ 0.3	X	Y
-------	---	---



SECT. A-A

- 1. TO BE MEASURED BETWEEN [Z] AND 2.
  - 2. TO BE MATE WITH CAP HOUSING SMOOTHLY.
  - 3. APPLIED CONTACT PART NUMBER ; 175266 AND 175267.
  - 4. APPLICABLE PRODUCT SPECIFICATION NUMBER ; 108-5359.
  - 5. RETAINER COLOR ; ALL WHITE
- 1. [Z] 面から2mmの範囲で測定。
  - 2. 相手ハウジングと所定の機能を満足して嵌合できること。
  - 3. 内装するリセプタクルコンタクト型番 ; 175266 及び 175267
  - 4. 適用製品規格番号 ; 108-5359
  - 5. リテーナは全て白色。

OBSOLETE	灰 (DARK GRAY)	316013-6
	黒 (BLACK)	316013-2
	白 (WHITE)	316013-1
	色 5 COLOR	型番 PART NUMBER

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
10 ≥	: ±0.2
30 ≥ > 10	: ±0.25
100 ≥ > 30	: ±0.3
ANGLE : ±3°	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 16JAN2013	<b>STE</b> TE Connectivity													
DIMENSIONS: mm		CHK K.BETSUI 16JAN2013														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.BETSUI 16JAN2013	NAME													
<table border="1"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC	040 SERIES PAIRMATE CONNECTOR	
0 PLC	± -															
1 PLC	± -															
2 PLC	± -															
3 PLC	± -															
4 PLC	± -															
ANGLES	± -															
MATERIAL PBT		FINISH -	16POSITION PLUG HOUSING ASSEMBLY													
SEE NOTE 4		APPLICATION SPEC	SIZE	RESTRICTED TO												
CUSTOMER DRAWING		WEIGHT -	A3 00779 C-316013	-												
		SCALE 2:1	SHEET 1 OF 1	REV A1												