

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16	R	REVISED PER ECR-09-010021	05MAY09	DW RZ

PART NUMBER	KEYING TYPE
501798-1	A
501798-2	B
501798-3	M
501798-4	S
501798-5	A
501798-6	B
501798-7	M
501798-8	S
501798-9	A
1-501798-0	B

PART NUMBER	KEYING TYPE	STATUS	REASON
501798-5	A	OBSOLETE	2
501798-6	B	OBSOLETE	2
501798-7	M	OBSOLETE	2
501798-8	S	OBSOLETE	2
501798-9	A	OBSOLETE	2
1-501798-0	B	OBSOLETE	2

- DIMENSIONS IN [] ARE IN INCHES.
- INCLUDES FSD DUST COVER WITH STRAP AND TWO BAYONET DUST COVERS.
- ASSEMBLY COLOR IS BEIGE.
- THREADED INSERTS INSTALLED IN BOTH PANEL AND BOARD MOUNTING EARS.

2.5mm BAYONET CONNECTION

12.70 [.500]

3.68 [.145]

17.78 [.700]

37.34 [1.470]

48.13 [1.895]

58.93 [2.320]

5.79 ±0.08 [.228 ±.003]

4-40 UNC 4 HOLES

18.16 [.715]

11.48 [.452]

11.74⁰_{-0.61} [.462^{+0.000}_{-.024}]

3.68 [.145]

32.87 [1.294]

42.34 [1.667]

9.09 [.358]

12.32 [.485]

5.00 [.197]

38.10 [1.500]

48.13 [1.895]

3.18 [.125] DIA 2 HOLES

SEE TABLE FOR KEYING TYPE

SUGGESTED MOUNTING PATTERN

RESTRICTED RELEASE
 DRAWING MAY CHANGE WITHOUT
 CUSTOMER NOTIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	D.KNOWLDEN	4-23-88	 AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS:		CHK	B.BRIGGS	4-23-88		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D.THOMPSON	4-23-88		
0 PLC ±- 1 PLC ±- 2 PLC ±0.13[.005] 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC	-			
MATERIAL		APPLICATION SPEC	-		SIZE	A2
PBT MOLDING COMPOUND		WEIGHT	-		CAGE CODE	00779
		CUSTOMER DRAWING			DRAWING NO	C=501798
		SCALE	2:1		SHEET	1 OF 1
		REV	R		RESTRICTED TO	-

AMP 1471-9 REV 27JUN96 Translated 061212.064721 (YYMDD.HHMMSS) from Computervision, Inc., Medusa Revision 12.2.5T

501798