SPECIFICATION CONTROL DRAWING



75 OHM, AWG 20, 19 STRANDS OF AWG 32, DATA BUS CABLE

Date: С Revision:

7520D1831

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.

CONSTRUCTION DETAILS

ELECTRICAL CHARACTERISTICS

DIMENSIONS ARE NOMINAL VALUES IN INCHES, UNLESS OTHERWISE DESIGNATED.

.0375

.074

.165

.199

CHARACTERISTIC IMPEDANCE 75 ± 5 ohms, Method C at 1 MHz MUTUAL CAPACITANCE 24.0 pF/ft. (nominal)

VELOCITY OF PROPAGATION

66% (nominal)

CONDUCTORS

AWG 20. 19 Strands of AWG 32, Tin-Coated Copper

DIELECTRICS

Radiation-Crosslinked. **HDPE**

SHIELD

JACKET

Zerohal

AWG 38,

Tin-Coated Copper

Colors - White/Blue

ADDITIONAL REQUIREMENTS

ELECTRICAL

CONDUCTOR RESISTANCE 9.88 ohms/1000 ft. (nominal)

(prior to cabling)

10,000 megohms (minimum) for 1000 ft. INSULATION RESISTANCE

JACKET FLAWS

SPARK TEST 1.0 kV (rms) IMPULSE TEST 6.0 kV (peak) VOLTAGE WITHSTAND (DIELECTRIC) 1500 volts (rms)

ENVIRONMENTAL

FLAMMABILITY Method B 225°C HEAT SHOCK

LOW TEMPERATURE-COLD BEND -30°C/5.50 inch mandrel **VOLTAGE WITHSTAND** 1000 volts (rms), 1 minute

(Post Environmental)

PHYSICAL

INSULATION (DIELECTRIC)

(prior to cabling)

ELONGATION 200% (minimum) TENSILE STRENGTH 1800 lbf/in² (minimum)

JACKET

ELONGATION 150% (minimum) TENSILE STRENGTH 1200 lbf/in2 (minimum) JACKET THICKNESS .017 inch (nominal) SHIELD COVERAGE 90% (minimum)

Outer jacket color will be black designated by a "-0" in accordance with MIL-STD-681 appended to the part number, (e.g. 7520D1831-0).

Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.

WFIGHT 23.5 lbs/1000 ft. (nominal)

ENGINEERING REFERENCE

TEMPERATURE RATING 105°C (maximum)

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

Zerohal, Cheminax, Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks

