


THREE CONDUCTOR CABLE, MODIFIED FLUOROPOLYMER INSULATED, SHIELDED AND JACKETED,
135°C, 600 VOLT, LIGHTWEIGHT

The complete requirements for procuring the wire described herein shall consist of this document.



Part Description	Wire Size Code	Screen Shield Size (mm)	Finished Cable				NSN 6145-99-038-	Def Stan 61-12(Part 33) Supplement 001 Table 6		
			Jacket Thickness Min. (mm)	Overall Diameter (mm)		Weight (kg/km)		Max. OD (mm)	Max. Weight (kg/km)	
				Target	Max.	Target				Max.
55D1134-26-*/*/-*	001	0.10	0.15	2.42	2.52	12.18	13.35	4032	2.63	14.16
55D1134-24-*/*/-*	002	0.10	0.15	2.63	2.73	14.89	16.15	4033	2.79	16.92
55D1131-22-*/*/-*	004	0.10	0.15	3.00	3.10	20.00	21.36	4034	3.21	22.56
55D1131-20-*/*/-*	006	0.10	0.15	3.51	3.61	29.37	31.20	4035	3.74	32.08
55D1131-18-*/*/-*	010	0.10	0.15	4.04	4.19	38.95	42.55	4036	4.30	44.03
55D1131-16-*/*/-*	012	0.10	0.15	4.40	4.55	49.23	52.40	4037	4.83	54.43
55D1131-14-*/*/-*	020	0.10	0.15	5.14	5.34	68.36	74.10	4038	5.46	74.89
55D1131-12-*/*/-*	030	0.10	0.15	6.15	6.35	100.80	106.47	4039	6.45	109.33

COLOUR CODE: The '*' in the part number shall be replaced by a standard colour code designator in accordance with Mil Std 681.

e.g. 55D1134-24-2/6/4-9, cores red, blue and yellow, jacket white.

Unless otherwise specified by the purchaser component colours to be red, blue and yellow.

NOTE: Nato Stock Numbers (NSN) apply to red/blue/yellow - white jacket cable only.

PERFORMANCE REQUIREMENTS: To be tested to and meet the requirements of the issue in effect of Def Stan 61-12(Part 33) and Supplement 001, Table 6.

MARKING REQUIREMENT: Every 400 ± 100 mm Mark shall be, e.g. 55D113#-XX DSP33/001-1Z-YYY-3SJ-*/*/-*-GB-SS-V

Where: "#" = Conductor material either 4 or 1 (see above part description).

"XX" = AWG size from part description.

"Z" = 'P' for size 26 and 24 and 'T' for size 22 to 12.

"YYY" = Wire Size Code

NOTE: Colour Code Designator "*/*/-*" is NOT required for red/blue/yellow - white cable. and "V" = the Year Code in accordance with the table below.

Code:	10	11	12	13	14	15	16
Year:	2010	2011	2012	2013	2014	2015	2016

This document does not cover Armament cables, refer to 55DA113Y.

APPROVAL: Electronic sign off - no signatures will appear.

Tyco Electronics UK Ltd
Faraday Road
Dorcan
SWINDON
SN3 5HH
UK

Registration Number:
550926 London, England

This drawing and the information set forth hereon are the property of Tyco Electronics UK Ltd, and are to be held in trust and confidence. Publication, duplication, disclosure or use for any purpose not expressly authorised in writing by Tyco Electronics UK Ltd is prohibited.

This specification sheet takes precedence over documents referenced herein. As Tyco Electronics UK Ltd. reserve the right to make changes in construction without notice please contact Tyco Electronics UK Ltd to ensure that this document is the latest issue

Tel: 0800 267666
Fax: 01793 572516

Website: www.tycoelectronics.com
Email: picuk@tycoelectronics.com