	4		5	
	THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20	
D	С СОРУRIGHT 20 ВУ -	ALL RIGHTS RESERVED.		
C				35.8
В				
A				

3

4

2

L OC


DIST		REVISIONS						
	P	LTR	DESCRIPTION	DATE	DWN	APVD		
		F7	REVISED PER ECR-17-014951	160C T 2017	BDA	KR		

1

1 NEUES MATERIAL (PHOSPHOR UND HALOGEN FREI)

- 2 MATERIAL CORRESPONDING TO THE REQUIRMENT OF IEC60335-1 (INCL. GWT 750 C WITHOUT FLAME)
- (3) COLOR OF HOUSINGS MAY RANGE FROM CLEAR TO GREEN OR YELLOW DUE TO HYGROSCOPIC NATURE OF RESIN.HOWEVER IT DOESN'T AFFECT THE FORM, FIT AND FUNCTION OF THE PRODUCT.
- CSA CERTIFICATION LOGO LOCATED AT LEAST ONE SIDE OF THE HOUSING APPROXIMATELY AS SHOWN.
- 5 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED. CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.

		92	6298-7	PA66 UL94 V-0	NATURAL	2
		926298-6		PA6.6 UL94 V2	NATURAL	2
		926298-5		PA 6.6 UL94 V	2 NATURAL	
		926298-4		PA6.6 UL94 V-0 weiß		
		926298-3		PA6.6 UL94 V-0 NATURAL		
		92	6298-2	PA6.6 UL94 V-	0 SCHWARZ /	1
		92	6298-1	PA66 UL94 V-2	NATURAL	3
		PA	RT NUMBER	MATERIAL		,
THIS DRAWING IS A CONTROLLED DOCUMENT.		рим 10FEB2014 ККВ Сникр 10FEB2014		TE TE Connectivity		
DIMENSIONS: TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.2 2 PLC ±- 3 PLC ±-		KKB 10FEB20 RRP 10FEB20 PRODUCT SPEC 108-1031 APPLICATION SPEC	U	NIVERSAL MATE- WAY PLUG	N-LOK	
4 P ANG		114 - 18011 WEIGHT _	SIZE CAGE	code drawing no		RESTRICTED TO
-	-	CUSTOMER DRAWING	• '	SCALE	2:1 SHEET 1 OF	^{₽₽} ₽7



Α

С