

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2005 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
JDIST
A

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

A

RELEASED

09NOV05

T.T

Y.Y

6746754-1: AS SHOWN

MOUNTING SURFACE

BUTTON STROKE


COLOR:
BLACKSECT A-A
(SCALE 2:1)

TABLE 1

POST LENGTH	5	3.5	4.25
CIRCUIT NO.	1,17,34,35,51,68	36,67	OTHERS

- ① REFER TO TABLE 1 FOR POST CONTACT LENGTH.
 ② RECOMMENDED TIGHTENING TORQUE
 :FROM 0.15N·m(1.5kg·cm) TO 0.2N·cm(2kg·cm)
 ③ APPLIED CARD: PCMCIA ATTRIBUTE PC CARD.
 ④ DOUBLE SLOT INSTALLED SCREW (M2, P=0.4) (4PLACES)
 (METRIC COARSE SCREW THREADS, APPLICABLE M2xL12)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: ㎜TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

① PLC	±	± 0.5
② PLC	±	
③ PLC	±	
④ PLC	±	
ANGLES	± 1'	

MATERIAL
材料FINISH
仕上

DWN T.TSUZAKI 28OCT05

CHK T.FUTATSUGI 09NOV05

APVD Y.YAMAMOTO 09NOV05

PRODUCT SPEC
製品規格 108-78192APPLICATION SPEC
取付適用規格

WEIGHT 35 gr

CUSTOMER DRAWING

1	INSULATOR SHEET	⑥
2	SPRING PIN	⑤
4	NUT (M2)	④
1	SHUTTER SUB ASSEMBLY	③
1	EJECTOR SUB ASSEMBLY	②
1	HEADER MAIN ASSEMBLY	①
QTY	NAME	ITEM

tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, JapanCARD BUS
DOUBLE SLOT TOP MOUNT PUSH-PUSH TYPE

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-6746754	

SCALE
尺度 1:1

SHEET 1 OF 2

REV A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2003 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	J
-----	---

	DIST

REVISIONS

变更

	P	
--	---	--

LTR

DESCRIPTION

DATE _____

DWN

APVD

SEE SHEET 1

6746754-1: AS SHOWN

0.6mm PITCH CARD EDGE CONNECTOR
FOR THIS CARDBUS PRODUCTS

PARTS NUMBER

6123215-1

DESCRIPTION

HARD TRAY ASSY

6376045-1

ON TAPING(EMBOSS)

APPLICABLE P.C.BOARD LAYOUT
(VIEW FROM CONN. MOUNTING SIDE)

VIEW D

EJECTOR MOUNT AREA (6PLACES)
/ NO ELECTRONICS COMPONENTS
| NO SIGNAL LINES etc.

VIEW D

-CONN. MOUNTING SIDE

VIEW B-B

VIEW D

[illegible]