


SEE NOTE 1 ↔

ITEM	PART/DRG NO	QTY	DESCRIPTION
1	01-703-0050	2	M8 x 25 LONG SOCKET HEAD CAP SCREW - STEEL
2	01-712-0013	1	BRIDGE HANDLE PLAIN BORE - M8 x 132 CRS
3	01-803-0016	2	ENGRAVING LABEL - WHITE/BLACK/WHITE - 80x35mm
4	01-807-0118	1	SINGLE SIDED FOAM TAPE - 10mm x 2mm x 25m REEL (FOR APPROX REQUIRED LENGTH, SEE NOTE)
5	01-807-0371	1	LINK BOX ENCLOSURE COVER 2-WAY (MK2 & MK3 LINKBOX)
6	01-807-0433	1	2-WAY LINK BOX ENCLOSURE SET - MK2 & MK3 LINKBOX (UR3030TMB)
7	01-811-0002	1	DIVING BELL LID 2-WAY (MK2 LINK BOX)
8	BAH-018110223	2	PRE-CAST LINKBOX 3-CORE STRAIGHT JOINT UPPER HOUSING - 3mm VIRGIN ABS
9	BAH-018110224	2	PRE-CAST LINKBOX 3-CORE STRAIGHT JOINT LOWER HOUSING - 3mm VIRGIN ABS
10	BAH-028110229	1	300mm² 2-WAY 3-CORE PRE-CAST LINKBOX BODY BUILD - NO LINKS
11	BAH-028110233	1	2-WAY PRE-CAST 3-CORE & 4-CORE LINK / ACCESSORY INSTALLATION TOOLBOX (SP)



NOTES :

1. SINGLE SIDED FOAM TAPE TO BE APPLIED TO FLANGES OF STRAIGHT JOINT LOWER HOUSING. LENGTH REQUIRED APPROX 2600mm



Material	VARIES	Part Description	- IF IN DOUBT ASK - DO NOT SCALE -
Finish	VARIES	300mm² 2-WAY 3-CORE PRE-CAST MK2 LINKBOX - NO LINKS (SP)	
Tolerances (UOS)	N/A		
B&H Short Desc.	1712/NLSP		

C	BAH-01800507 (x2), BAH-01811037 (x1), BAH-01811038 (x1), BAH-01811039 (x1), BAH-01811029 (x1), BAH-038070347 (x2), BAH-018070410 (x6) & BAH-018110232 (x1) REMOVED AND REPLACED WITH BAH-028110233 (x1)	BH-01127	12/11/15
	INSTALLATION INSTRUCTION BAH-018110232 (x1) ADDED	BH-01126	
B	PICTORIAL CHANGE ONLY - TERMINAL COVER NUMBERS REMOVED	BH-01123	14/10/15
A	FIRST ISSUE	BH-01118	05/10/15
Revision	Description	Name/DMR	Date
Design/Drawn	D M EATON	Date	29-Sep-15
Scale (UOS)	1:12	Part Weight	73.55kg
TCPN	EHO993-000	Drawing/Part No	BAH-028110230
Drawing Type	CUSTOMER	Rev	C