

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2016

© COPYRIGHT 2013 BY TECONNECTIVITY

ALL RIGHTS RESERVED.

LOC - DIST -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE	31MAY2016	JF	DM

5 DATE CODE: MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS. EX: A=JANUARY. YEAR IS REPRESENTED BY THE LAST DIGIT. EX: 7=2017.

4 PART MODIFICATION: END CAP.

3. THIS PLUG MATES WITH DTM04-4P-XXXX RECEPTACLE. (XXXX= ALL MODIFICATIONS).

2 MATERIAL:
 PLUG HOUSING: PA66 GF15 (GREY)
 END CAP: PA66 GF15 (GREY)
 GROMMET: VMQ (RED-ORANGE)

1. SECONDARY WEDGE LOCK SOLD SEPARATELY: WM-4S-XXXX (XXXX= ALL MODIFICATIONS)

NOTES: UNLESS OTHERWISE SPECIFIED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.FIERRO 20MAY2016																				
DIMENSIONS: INCHES [mm]		CHK S.BEARD 27MAY2016																				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.MEYER 27MAY2016	NAME 4 WAY PLUG -E003 MOD. DTM SERIES																			
<table border="0"> <tr> <td>0 PLC</td> <td>±</td> <td></td> </tr> <tr> <td>1 PLC</td> <td>±</td> <td></td> </tr> <tr> <td>2 PLC</td> <td>±</td> <td></td> </tr> <tr> <td>3 PLC</td> <td>±.025 [0.64]</td> <td></td> </tr> <tr> <td>4 PLC</td> <td>±</td> <td></td> </tr> <tr> <td>ANGLES</td> <td></td> <td>±0°30'0"</td> </tr> </table>		0 PLC	±		1 PLC	±		2 PLC	±		3 PLC	±.025 [0.64]		4 PLC	±		ANGLES		±0°30'0"	PRODUCT SPEC 108-151010	SIZE A3	
0 PLC	±																					
1 PLC	±																					
2 PLC	±																					
3 PLC	±.025 [0.64]																					
4 PLC	±																					
ANGLES		±0°30'0"																				
MATERIAL		APPLICATION SPEC 0425-015-0000	CAGE CODE 4AFU8	DRAWING NO DTM06-4S-E003	RESTRICTED TO -																	
FINISH -		WEIGHT 5.7g	SCALE 2:1																			
		CUSTOMER DRAWING		SHEET 1	OF 1																	
				REV A																		

1470-19 (3/11)