



REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|-----------|-----|------|
| | A | NEW DRAWING | 29FEB2024 | AN | VN |
| | | | | | |
| | | | | | |

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

| SIZES | AS SUPPLIED | | AS RECOVERED | | | | | | | |
|-------------|--------------|-------|--------------|-------|--------------|-------|--------------|-------|--------------|-------|
| | D MINIMUM | | A MAXIMUM | | B MINIMUM | | C MINIMUM | | E NOMINAL | |
| | mm. | in. |
| RAYRIM-NR6 | 0.80 | 0.031 | 0.60 | 0.024 | 0.50 | 0.020 | 3.50 | 0.138 | 1.25 | 0.049 |
| RAYRIM-NR7 | 1.60 | 0.063 | 1.00 | 0.039 | 0.90 | 0.035 | 4.80 | 0.189 | 1.25 | 0.049 |
| RAYRIM-NR8 | 2.50 | 0.098 | 2.00 | 0.079 | 0.90 | 0.035 | 6.60 | 0.260 | 2.25 | 0.089 |
| RAYRIM-NR9 | 4.50 | 0.177 | 4.20 | 0.165 | 0.90 | 0.035 | 13.50 | 0.531 | 2.20 | 0.087 |
| RAYRIM-NR12 | 5.00 | 0.197 | 3.20 | 0.126 | 0.80 | 0.031 | 6.00 | 0.236 | 1.15 | 0.045 |

PRODUCT INFORMATION


- 1 FLAME RETARDED
- 2 SECTION: HEAT-SHRINKABLE, THERMALLY STABILISED IRRADIATED, POLYOLEFIN
ADHESIVE: RAYCHEM HOT-MELT ADHESIVE
- 3 STANDARD SUPPLIED LENGTH: 1.2 METRES
- 4 STANDARD COLOUR IS BLACK AND ALSO AVAILABLE IN WHITE
- 5 LONGITUDINAL CHANGE +1 TO -10%
- 6 "D" ONLY APPLICABLE TO UNMODIFIED 1.2 METRES LENGTH
- 7 TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES(mm)

| CUT LENGTH | TOLERANCE |
|-------------------|-----------|
| UPTO TO 9.90mm | ±1.50mm |
| 10mm TO 24.90mm | ±1.50mm |
| 25mm TO 54.90mm | ±1.50mm |
| 55mm TO 99.90mm | ±3.00mm |
| 100mm TO 149.90mm | ±4.00mm |
| 150mm TO 499.90mm | ±5.00mm |
| 500mm AND GREATER | ±25.40mm |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm(inches)



MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±
- 1 PLC ±
- 2 PLC ±0.1
- 3 PLC ±0.01
- 4 PLC ±0.001
- ANGLES ±
- FINISH -

| | |
|------------------|------------|
| DWN | 29FEB2024 |
| AYESHABANDU N | |
| CHK | 29FEB2024 |
| BASAVARAJA D A | |
| APVD | 29FEB2024 |
| VLADIMIR NEMEC | |
| PRODUCT SPEC | RK-6182 |
| APPLICATION SPEC | 114-120015 |
| WEIGHT | - |
| CUSTOMER DRAWING | |



NAME
RAYRIM EDGING STRIP

| | | | |
|-------|-----------|------------|---------------|
| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
| A3 | - | RAYRIM | - |
| SCALE | SHEET | OF | REV |
| NTS | 1 | 1 | A |