

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	08JUN2015	GY	CW
B		ECR-20-012069	08MAY2021	BS	CW

TYPE 1

Hood with TE Logo

TYPE 2

Hood without TE Logo

* Without TE Logo

All dimension is same as TYPE 1, except those defined in this TYPE

NOTES:
 1. TECHNICAL CHARACTERISTICS:
 HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
 SURFACE TREATMENT: SEE TABLE
 DEGREE OF PROTECTION: IP68 (MATED)

注释
 1. 技术参数:
 壳体材料: 铝合金
 表面处理: 见表格
 防护等级: IP68 (配合)

T1910100121-100	POWDER COATED BLACK	H10BPR-TSH-PG21	PG21	TYPE 2
T1910102132-000	POWDER COATED GRAY	H10BPR-TSH-M32	M32	TYPE 1
T1910102129-000	POWDER COATED GRAY	H10BPR-TSH-PG29	PG29	
T1910102125-000	POWDER COATED GRAY	H10BPR-TSH-M25	M25	
T1910102121-000	POWDER COATED GRAY	H10BPR-TSH-PG21	PG21	
T1910102120-000	POWDER COATED GRAY	H10BPR-TSH-M20	M20	
T1910102116-000	POWDER COATED GRAY	H10BPR-TSH-PG16	PG16	
T1910101132-000	POWDER COATED SILVER WHITE	H10BPR-TSH-M32	M32	
T1910101129-000	POWDER COATED SILVER WHITE	H10BPR-TSH-PG29	PG29	
T1910101125-000	POWDER COATED SILVER WHITE	H10BPR-TSH-M25	M25	
T1910101121-000	POWDER COATED SILVER WHITE	H10BPR-TSH-PG21	PG21	
T1910101120-000	POWDER COATED SILVER WHITE	H10BPR-TSH-M20	M20	
T1910101116-000	POWDER COATED SILVER WHITE	H10BPR-TSH-PG16	PG16	
T1910100132-000	POWDER COATED BLACK	H10BPR-TSH-M32	M32	
T1910100129-000	POWDER COATED BLACK	H10BPR-TSH-PG29	PG29	
T1910100125-000	POWDER COATED BLACK	H10BPR-TSH-M25	M25	
T1910100121-000	POWDER COATED BLACK	H10BPR-TSH-PG21	PG21	
T1910100120-000	POWDER COATED BLACK	H10BPR-TSH-M20	M20	
T1910100116-000	POWDER COATED BLACK	H10BPR-TSH-PG16	PG16	
PART NUMBER	SURFACE TREATMEN	DESCRIPTION	PG/M THREAD	TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN Gino Yao 08JUN2015	 TE Connectivity
mm	0 PLC ±	CHK Chris Wang 08JUN2015	
	1 PLC ±	APVD Xiang Xu 08JUN2015	
	2 PLC ±	PRODUCT SPEC	
	3 PLC ±	108-137014	NAME H10BPR-TSH-PG/M
	4 PLC ±	114-137014	SIZE A2
ANGLES	±	114-137014	CAGE CODE -
FINISH	-	WEIGHT -	DRAWING NO. C-T191010XXXXX00
MATERIAL	-	Customer Drawing	RESTRICTED TO -
	-	SCALE 1:1	SHEET 1 OF 1
	-	REV B	

1471-9 (3/13)