



Ausführung A



Ausführung B
(Fehlende Maße siehe Ausführung A)



SUPERSEDED BY 1393434

V23540-M1026-S509	V23540-M1026-Y209	D - E	türkisblau
V23540-M1026-S508	V23540-M1026-Y208	A - H	orange
V23540-M1026-S507	V23540-M1026-Y207	D - F	lila
V23540-M1026-S506	V23540-M1026-Y206	B - H	grau
V23540-M1026-S505	(PN 2-1393434-2) V23540-M1026-Y205	D - G	braun
(PN 1-1393434-6) V23540-M1026-S504	(PN 2-1393434-1) V23540-M1026-Y204	C - H	grün
(PN 1-1393434-5) V23540-M1026-S503	(PN 2-1393434-0) V23540-M1026-Y203	A - E	gelb
(PN 1-1393434-4) V23540-M1026-S502	(PN 1-1393434-9) V23540-M1026-Y202	B - F	signalblau
(PN 1-1393434-3) V23540-M1026-S501	(PN 1-1393434-8) V23540-M1026-Y201	C - G	beige
(PN 1-1393434-2) V23540-M1026-S500	(PN 1-1393434-7) V23540-M1026-Y200	D - H	schwarz
Mit Kabelabgang 90° Ausführung A	Mit Kabelabgang 45° Ausführung B	Geometrisch	Farbe
Bestell - Nummer		Kodierung	

Passend zu Stiftleiste : V23540-M1126-B5** (PN 4-1393375-3 bis -9 und PN 5-1393375-0)
 V23540-M1626-D5** (PN 5-1393375-3 /*-5/*-7/*-8 und 6-1393375-0 /*-2 bis -5)
 V23540-M1626-F5**
 (PN 6-1393375-7 /*-8 und 7-1393375-0 /*-1/*-3/*-5 bis *-9)
 V23540-M1026-Y1
 (PN 4-1393476-3 / 5-1393476-0 / *-1)

Hierzu passend Buchsengehäuse V23540-M1026-Q50*

Teile-Nr. nach Mittelschrift DIN 1451

Gezeichnet: Kodierung D-H

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden.
 Zuwiderhandlungen verpflichten zu Schadensersatz. Alle Rechte vorbehalten, insbesondere im Falle der Patenterteilung oder GM-Eintragung.
 The reproduction, transmission or use of this document or its contents is not permitted without express written authority.
 Offenders will be liable for damages.
 All rights, including rights created by patent grant or registration of an utility model or design, reserved.

*) Längen: DIN 16901-130 ; Winkel, Form und Lage: DIN ISO 2768-mH

Tol.: ISO 8015	Maßstab 2:1	Format DIN A1
Kappe: PBT-GF30, Farbe:sh. Tabelle Hebel: PBT-GF20, Farbe: türkisblau		
Maßbild		
Abdeckkappe mit Hebel 26 polig		
Tyco		Blatt 1-
V23540-M1026-S500-*27		Bl.
Zust. Mitteilung	Datum	Name