

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION FEB , 2017.
 © COPYRIGHT 2017 By TE Connectivity ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	NEW DRAWING FORMAT	16FEB2016	GK	DB
	F	LINER CHANGE	07SEP2018	GK	DB

LABEL AND LINER DESIGN

87.3 [3.436]
 3.0 [.118]
 27.9 [1.100]
 12.7 [.500]
 25.4 [1.000]
 R1.5 [R.060]
 36.5 [1.437]
 42.2 [1.661]
 1.6 [.062]
 2.9 [.112]
HIGH OPACITY WHITE COLOR
 CLEAR (COLORLESS)
 AUTO ALIGN HOLES IN LINER
 2.5 [.100]
 R0.8 [R.030]
 9.1 [.360]
 10 [.393]

PRESENTATION

$\phi 90 \pm 10$
 [3.543 ± .393]
 $\phi 25.4$
 [1.000]

**OUTSIDE WOUND LABEL ACROSS: 3
 PER ROLL QTY: 2,500**

All dimensions in mm [Inch]

TE PN: CN2899-000

MATERIAL	CLEAR VINYL
ADHESIVE TYPE	ACRYLIC PERMANENT
LINEAR	WHITE KRAFT

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16FEB2017	
LABEL HEIGHT:	±0.3 [.012]	DIMENSIONS: mm [INCHES]		GOPALAKRISHNA HV	
LABEL WIDTH:	±0.3 [.012]			CHK D.BURGAT 16FEB2017	
WEB WIDTH:	±0.8 [.031]			APVD D.BURGAT 16FEB2017	
VERTICAL REPEAT:	±0.8 [.031]*			NAME	
HORIZONTAL REPEAT:	±0.8 [.031]*	MATERIAL FINISH SEE TABLE GLOSSY		TE Connectivity	
PRINT POSITIONING:	±0.8 [.031]*			PRODUCT SPEC TTD5-211	
LEFT MARGIN:	±0.4 [.016]			APPLICATION SPEC -	
QUANTITY:	-0 % +2 % *NON ACCUMULATING			WEIGHT 0.129 g SIZE A2 CAGE CODE 00779 DRAWING NO. SBP100143WE2.5-T200	
UL-MARKING AND LABELLING SYSTEMS PGIS2 - Marking and Labeling Systems, Limited Use - Component (UL 969) File: MH61871 Product design: SBP Ribbon: TMS-XXX-RIBBON-4RPSCE		RESTRICTED TO CUSTOMER DRAWING		SCALE NTS SHEET 1 of 1 REV F	

1471-9 (1/15)

CN2899-000