

7-1589449-9	1589449	USS004SC2DMC50	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 50 centimeters.
8-1589449-0	1589449	USS004SC2DC008	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 8 inches.
8-1589449-1	1589449	USS004SC2DMC30	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 30 centimeters.
8-1589449-2	1589449	USS004SC4DXC30	Unshrouded, 1 row, strip, 4 position, receptacle, 34 AWG 7 strand, white PTFE wire, 30 centimeters.
8-1589449-3	1589449	USS004SC2DMC40	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 40 centimeters.
8-1589449-4	1589449	USS004SC2DM012T	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), accepts guide post in position 1.
8-1589449-5	1589449	USS004SC2DTC20T	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, white ETFE M22759/33 wire, 20 centimeters, accepts guide post in position 1.
8-1589449-6	1589449	USS015SC1DC036T	Unshrouded, 1 row, strip, 15 position, receptacle, 30 AWG solid, color coded PTFE wire, 36 inches, accepts guide post in position 1.
8-1589449-7	1589449	USS015SC1DC036W	Unshrouded, 1 row, strip, 15 position, receptacle, 30 AWG solid, color coded PTFE wire, 36 inches, accepts guide post in position 1 & 14.
8-1589449-8	1589449	USS009SC2DM012T	Unshrouded, 1 row, strip, 9 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, accepts guide post in position 1.
8-1589449-9	1589449	USS004SC2DM024T	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, accepts guide post in position 1.
9-1589449-0	1589449	USS009SC2DM024T	Unshrouded, 1 row, strip, 9 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, accepts guide post in position 1.
9-1589449-1	1589449	USS009SC2DT012T	Unshrouded, 1 row, strip, 9 position, receptacle, 30 AWG 7 strand, white ETFE M22759/33 wire, 12 inches, accepts guide post in position 1.
9-1589449-2	1589449	USS015SC2DC006T	Unshrouded, 1 row, strip, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 1.
9-1589449-3	1589449	USS025SC2DC006T	Unshrouded, 1 row, strip, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 1.
9-1589449-4	1589449	USS037SC2DC006T	Unshrouded, 1 row, strip, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 1.
9-1589449-5	1589449	USS037SC2DC006U	Unshrouded, 1 row, strip, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 2.
9-1589449-6	1589449	USS037SC2DC006V	Unshrouded, 1 row, strip, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 3.
9-1589449-7	1589449	USS037SC2DC006W	Unshrouded, 1 row, strip, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide posts in positions 1 and 36.
9-1589449-8	1589449	USS037SC2DC006Y	Unshrouded, 1 row, strip, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide posts in positions 1 and 35.
9-1589449-9	1589449	USS037SC2DC006Z	Unshrouded, 1 row, strip, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide posts in positions 2 and 35.
1589964-1	1589449	USS051SC2DC006T	Unshrouded, 1 row, strip, 51 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 1.
1589964-2	1589449	USS051SC2DC006U	Unshrouded, 1 row, strip, 51 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 2.
1589964-3	1589449	USS051SC2DC006V	Unshrouded, 1 row, strip, 51 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, accepts guide post in position 3.
1589964-4	1589449	USS004SC2DCM01T	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 1 meter, accepts guide post in position 1.
1589964-5	1589449	USS004SC0DC006T	Unshrouded, 1 row, strip, 4 position, receptacle, 28 AWG solid, color coded PTFE wire, 6 inches, accepts guide post in position 1.
1589964-6	1589449	USS004SC0DC012	Unshrouded, 1 row, strip, 4 position, receptacle, 28 AWG solid, color coded PTFE wire, 12 inches.
1589964-7	1589449	USS004SC1DC012	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG solid, color coded PTFE wire, 12 inches.
1589964-8	1589449	USS037SC2DC024	Unshrouded, 1 row, strip, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches.
1589964-9	1589449	USS025SC2DC024	Unshrouded, 1 row, strip, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches.
1-1589964-0	1589449	USS015SC2DC024	Unshrouded, 1 row, strip, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches.
1-1589964-1	1589449	USS004SC2DCM02	Unshrouded, 1 row, strip, 4 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 2 meters.
2511075-1	1589449	USS009SC2DM012V	Unshrouded, 1 row, strip, 9 position, receptacle, 30 AWG 7 strand, color coded Teflon wire, MIL-STD-681, 12 inches, accepts guide post in position 3