

TE P/N	TE CD	Nanonics P/N	Part Description
1589818-1	1589818	STL015W5CN	Dualobe, 2 row, LCP, 15 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589818-2	1589818	STL025W5CN	Dualobe, 2 row, LCP, 25 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589818-3	1589818	STM009W5LQ	Dualobe, 2 row, metal, 9 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.2 x .200 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1589818-4	1589818	STM015W5PQ	Dualobe, 2 row, metal, 15 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
1589818-5	1589818	STM025W5CN	Dualobe, 2 row, metal, 25 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589818-6	1589818	STM025W5PQ	Dualobe, 2 row, metal, 25 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
1589818-7	1589818	STM025W5SN	Dualobe, 2 row, metal, 25 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589818-8	1589818	STM037W5CN	Dualobe, 2 row, metal, 37 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589818-9	1589818	STM051W5CN	Dualobe, 2 row, metal, 51 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589818-0	1589818	STM065W5CN	Dualobe, 2 row, metal, 65 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589818-1	1589818	STL015W5SN	Dualobe, 2 row, LCP, 15 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589818-2	1589818	STM009W5PQ	Dualobe, 2 row, metal, 9 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.2 X .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews,
1-1589818-3	1589818	STM037W5LQ	Dualobe, 2 row, metal, 37 position, receptacle, vertical mount, thru hole termination, .090 long, gold leadframe, 1.2 x .200 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.