

HD6/14.DH



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks
→ Railway Terminal Blocks

General Information

Extended Product Type:	HD6/14.DH
Product ID:	1SNA162971R2700
EAN:	3472591629712
Catalog Description:	HD6/14.DH - Quick connect terminal blocks - Component holder - Beige
Long Description:	- Terminal block for screw and solder diodes type SKN2.5 or SKNa2, - Connection by 2 tabs for quick disconnects 6.3 x 0.8 mm 0.248 x 0.031 in on each side, - NF F 61-017 designation: BG0014-2G2G (1SNA162971R2700).

Ordering

Color:	Beige
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0205_CHD3
Instructions and Manuals:	1SNC160001C0205_CHD3

Dimensions

Product Net Width:	14 mm
Product Net Height:	54 mm
Product Net Depth / Length:	38 mm
Product Net Weight:	20 g

Technical

Rated Cross-Section:	6 mm ²
Spacing:	14 mm
Connection Type:	Quick-connect
Function:	Component holder
Number of Levels:	1
Rated Current (I_n):	Main Circuit 25 A
Dielectric Test Voltage:	2950 V
Insulation Material:	Polyamide
Mounting on DIN Rail:	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Technical UL/CSA

Connecting Capacity UL/CSA: Stranded 10 AWG

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001U1000

EAC Certificate: 1SND161009A1100

Environmental Information: 1SND220040E1002

Instructions and Manuals: 1SNC160001C0205_CHD3

RoHS Information: 1SND230014F0201

Classifications

Object Classification Code: X

ETIM 4: EC000902 - (Knife) disconnect terminal block

ETIM 5: EC000902 - (Knife) disconnect terminal block

ETIM 6: EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units: 10 piece

Package Level 1 Width: 66 mm

Package Level 1 Depth / Length: 150 mm

Package Level 1 Height: 41 mm

Package Level 1 Gross Weight: 0.2 kg

Package Level 1 EAN: 3472591629712

Package Level 2 Units: 350 piece

Package Level 3 Units: 16800 piece

Product Packing Type: Box



