

Products → Low Voltage Products and Systems → Connection Devices → Test Blocks → Prewired Voltage Plugs

## General Information

<b>Extended Product Type:</b>	COR-T-4-4
<b>Product ID:</b>	1SNA167935R1000
<b>EAN:</b>	3472591679359
<b>Catalog Description:</b>	COR-T-4-4 Prewired Voltage Plugs
<b>Long Description:</b>	<ul style="list-style-type: none"><li>— Standard voltage plugs are compatible with Essailec® voltage sockets.</li><li>— Plugs are ready to use with contact pins (BRE...) , coding, cables and test plugs assembled to ease your test operations.</li></ul>

## Ordering

<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC169001C0211
<b>Instructions and Manuals:</b>	1SNC169001C0210

## Dimensions

<b>Product Net Width:</b>	44 mm
<b>Product Net Height:</b>	63 mm
<b>Product Net Depth / Length:</b>	2232 mm
<b>Product Net Weight:</b>	500 g

## Technical

<b>Function:</b>	Voltage transformers application
<b>Rated Current (<math>I_n</math>):</b>	Main Circuit 15 A
<b>Rated Short-time Withstand Current (<math>I_{cw}</math>):</b>	for 1 s 800 A
<b>Rated Voltage (<math>U_r</math>):</b>	400 V
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	4000 V
<b>Pollution Degree:</b>	3
<b>Insulation Material:</b>	Polycarbonate
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Environmental

<b>Ambient Air Temperature:</b>	Operation -10 ... +55 °C Storage -25 ... +70 °C
---------------------------------	--

Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225003U1001
<b>EAC Certificate:</b>	1SND160001A1100
<b>Instructions and Manuals:</b>	1SNC169001C0210

Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000902 - (Knife) disconnect terminal block
<b>ETIM 5:</b>	EC000902 - (Knife) disconnect terminal block
<b>ETIM 6:</b>	EC000902 - (Knife) disconnect terminal block

Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	184 mm
<b>Package Level 1 Depth / Length:</b>	210 mm
<b>Package Level 1 Height:</b>	94 mm
<b>Package Level 1 Gross Weight:</b>	0.5 kg
<b>Package Level 1 EAN:</b>	3472591679359
<b>Package Level 2 Units:</b>	8 piece
<b>Package Level 3 Units:</b>	192 piece
<b>Product Packing Type:</b>	Box

