

# BJS61-5



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Jumper Bars

## General Information

<b>Extended Product Type:</b>	BJS61-5
<b>Product ID:</b>	1SNA168484R2600
<b>EAN:</b>	3472591684841
<b>Catalog Description:</b>	BJS61-5 Jumper Bars
<b>Long Description:</b>	- Not assembled screw jumpers bar, - Perforated jumper bar without captive screw and spacer, - Use the fastening kits or screw and washer to connect this jumper bar onto the blocks.

## Ordering

<b>Color:</b>	Grey
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85389099

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-J Accessories
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-J Accessories

## Dimensions

<b>Product Net Width:</b>	6 mm
<b>Product Net Height:</b>	1 mm
<b>Product Net Depth / Length:</b>	5 mm
<b>Product Net Weight:</b>	1.8 g

## Technical

<b>Spacing:</b>	6 mm
<b>Function:</b>	Jumper Bars
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 32 A
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Suitable For:</b>	HD2.5/6

## Environmental

**Ambient Air Temperature:** Operation -55 ... +110 °C

## Certificates and Declarations (Document Number)

**Instructions and Manuals:** 1SNC160001C0207-CH-J Accessories

## Classifications

**Object Classification Code:** X

---

**ETIM 4:** EC000489 - Cross-connector for terminal block

---

**ETIM 5:** EC000489 - Cross-connector for terminal block

---

**ETIM 6:** EC000489 - Cross-connector for terminal block

## Container Information

**Package Level 1 Units:** 10 piece

---

**Package Level 1 Gross Weight:** 0.018 kg

---

**Package Level 1 EAN:** 3472591684841

---

**Package Level 2 Units:** 2500 piece

