



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

TE P/N	TE CD	Nanonics P/N	Part Description
1589057-1	1589057	QCM019PC0DC012	Quick disconnect, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 12 inches.
1589057-3	1589057	QCM019PC2DC003	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 inches.
1589057-4	1589057	QCM019PC2DC006	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches.
1589057-5	1589057	QCM019PC2DC012	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches.
1589057-6	1589057	QCM019PC2DC020	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches.
1589057-8	1589057	QCM019PC2DMC46	Quick disconnect, circular, metal, 19 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 46 centimeters.
1589057-9	1589057	QCM019PC2DXC30	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, white PTFE wire, 30 centimeters.
1-1589057-0	1589057	QCM019PC2DMM01	Quick disconnect, circular, metal, 19 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 1 meter.
1-1589057-1	1589057	QCM019PC2DCC10	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 10 centimeters.
1-1589057-2	1589057	QCM019PC2DMC150	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 150 centimeters.
1-1589057-3	1589057	QCM019PC2DC016	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 16 inches.
1-1589057-4	1589057	QCM019PC2DMC40	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 40 centimeters.
1-1589057-5	1589057	QCM019PC0DC036	Quick disconnect, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 36 inches.
1-1589057-6	1589057	QCM019PC0DM012	Quick disconnect, circular, metal, 19 position, plug, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches.
1-1589057-7	1589057	QCM019PC2DC084	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 84 inches.
1-1589057-9	1589057	QCM019PC2DC024	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches.