

TE P/N	TE CD	Nanonics P/N	Part Description
1589810-1	1589810	SSG051T2AQ	Dualobe, 1 row, gold, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 X .160 mounting screw, thread for 1.2 jackscrews.
1589810-2	1589810	SSM037T2AQ	Dualobe, 1 row, metal, 37 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1589810-3	1589810	SSM051T2AQ	Dualobe, 1 row, metal, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1589810-4	1589810	SSL005T2HN	Dualobe, 1 row, LCP, 5 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589810-5	1589810	SSM009T2HN	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589810-6	1589810	SSM009T2SN	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589810-7	1589810	SSM015T2AQ	Dualobe, 1 row, metal, 15 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1589810-8	1589810	SSM015T2HN	Dualobe, 1 row, metal, 15 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589810-9	1589810	SSM025T2AQ	Dualobe, 1 row, metal, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589810-0	1589810	SSM025T2HN	Dualobe, 1 row, metal, 25 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589810-1	1589810	SSM037T2HN	Dualobe, 1 row, metal, 37 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589810-2	1589810	SSM051T2HN	Dualobe, 1 row, metal, 51 position, receptacle, horizontal mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.