

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → End Stops

General Information

Extended Product Type:	BAMH
Product ID:	1SNA114836R0000
EAN:	3472591148367
Catalog Description:	BAMH End Stops - Grey
Long Description:	Multi rail end stop.

Ordering

Color:	Grey
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	9.1 mm
Product Net Height:	43 mm
Product Net Depth / Length:	44.5 mm
Product Net Weight:	13 g

Technical

Spacing:	9.1 mm
Function:	End Stops
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Recommended Screw Driver:	5.5 mm
Tightening Torque:	acc. IEC 60947-1 0.8 N·m Manufacturer 1 N·m

Suitable For: 131ETTM4TM4
D2.5/5.A.L.L
D2.5/5.A.LL.L
D2.5/5.A.LLP.L
D2.5/5.A.N.L
D2.5/5.A.NL.L
D2.5/5.A.NLP.L
D2.5/5.A.NTLP.L
D2.5/5.D2.L
D2.5/5.DD.L
D2.5/5.DE.L
D2.5/5.DE1.D.L
D2.5/5.DE1.L
D2.5/5.DE2.D2.L
D2.5/5.DE2.L
D2.5/5.DL.L
D2.5/5.L.L
D2.5/5.LL.L
D2.5/5.LLP.L
D2.5/5.N.L
D2.5/5.NL.L
D2.5/5.NLP.L
D2.5/5.NTLP.L
D2.5/5.T1.L
D2.5/5.T1.P.L
D2.5/5.T3.L
D2.5/5.T3.P.L
D4/6.A.LL
M120/35.AF
M120/35.F
M120/35.FF
M300/42.AF
M300/42.F
M300/42.FF
M35/26.AF
M35/26.F
M35/26.FF
M70/31.AF
M70/31.F
M70/31.FF

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

RoHS Information: 1SND230479F0206

Classifications

Object Classification Code:	X
E-nummer:	2925485
ETIM 4:	EC001041 - End bracket for terminal block
ETIM 5:	EC001041 - End bracket for terminal block
ETIM 6:	EC001041 - End bracket for terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	200 mm
Package Level 1 Depth / Length:	300 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.65 kg
Package Level 1 EAN:	3472591148367
Package Level 2 Units:	1000 piece
Package Level 3 Units:	24000 piece
Product Packing Type:	Bag

