

# D2.5/6 DPA



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

## General Information

<b>Extended Product Type:</b>	D2.5/6 DPA
<b>Product ID:</b>	1SNA115532R0000
<b>EAN:</b>	3472591155327
<b>Catalog Description:</b>	D2.5/6 DPA Screw Clamp Terminal Blocks
<b>Long Description:</b>	D2.5/6.DPA Screw Clamp Terminal Blocks - Feed-through + ground - Grey, Green-Yellow, 2.5mm <sup>2</sup> Rated Cross Section, 6mm Spacing G32, TH 35-7.5, TH 35-15 Rail.

## Ordering

<b>Minimum Order Quantity:</b>	25 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-A screw clamp
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-A screw clamp

## Dimensions

<b>Product Net Width:</b>	6 mm
<b>Product Net Height:</b>	81 mm
<b>Product Net Depth / Length:</b>	43.5 mm
<b>Product Net Weight:</b>	16 g

## Technical

<b>Connection Type:</b>	Screw clamp
<b>Number of Levels:</b>	3
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225026U1000
--	-----------------

<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220020E1002
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-A screw clamp
<b>RoHS Information:</b>	1SND230023F0208

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000897 - Feed-through terminal block
<b>ETIM 5:</b>	EC000897 - Feed-through terminal block
<b>ETIM 6:</b>	EC000897 - Feed-through terminal block

## Container Information

<b>Package Level 1 Units:</b>	25 piece
<b>Package Level 1 Width:</b>	81 mm
<b>Package Level 1 Depth / Length:</b>	200 mm
<b>Package Level 1 Height:</b>	53 mm
<b>Package Level 1 Gross Weight:</b>	0.4 kg
<b>Package Level 1 EAN:</b>	3472591155327
<b>Package Level 2 Units:</b>	300 piece
<b>Package Level 3 Units:</b>	14400 piece
<b>Product Packing Type:</b>	Box

