

HD10/12.F5



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks
→ Railway Terminal Blocks

General Information

Extended Product Type:	HD10/12.F5
Product ID:	1SNA295394R2300
EAN:	3472592953946
Catalog Description:	HD10/12.F5 - Stud terminal blocks - 1 stud M5 - Beige
Long Description:	- 1 stud terminal M5 x 19.5 mm 0.768 in, - Equipment: H 130 self locking nut + TREP 3L washer + washer.

Ordering

Color:	Beige
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0205_CHD3
Instructions and Manuals:	1SNC160001C0205_CHD3

Dimensions

Product Net Width:	12 mm
Product Net Height:	50 mm
Product Net Depth / Length:	34.5 mm
Product Net Weight:	11 g

Technical

Rated Cross-Section:	10 mm ²
Spacing:	12 mm
Connection Type:	Stud
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Stud / Flexible 1x 0.5 ... 10 mm ²
Rated Current (I_n):	Main Circuit 57 A
Insulation Material:	Polyamide
Mounting on DIN Rail:	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Tightening Torque:	acc. IEC 60947-1 2.5 N·m

Technical UL/CSA

Connecting Capacity UL/CSA:	Stranded 8 AWG
-----------------------------	----------------

Flammability According to UL94:	V0
---------------------------------	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
--------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225049U1000
---------------------------------	-----------------

EAC Certificate:	1SND161009A1100
------------------	-----------------

Environmental Information:	1SND220039E1002
----------------------------	-----------------

Instructions and Manuals:	1SNC160001C0205_CHD3
---------------------------	----------------------

RoHS Information:	1SND230014F0201
-------------------	-----------------

Classifications

Object Classification Code:	X
-----------------------------	---

ETIM 4:	EC000897 - Feed-through terminal block
---------	--

ETIM 5:	EC000897 - Feed-through terminal block
---------	--

ETIM 6:	EC000897 - Feed-through terminal block
---------	--

Container Information

Package Level 1 Units:	50 piece
------------------------	----------

Package Level 1 Width:	200 mm
------------------------	--------

Package Level 1 Depth / Length:	300 mm
---------------------------------	--------

Package Level 1 Height:	5 mm
-------------------------	------

Package Level 1 Gross Weight:	0.55 kg
-------------------------------	---------

Package Level 1 EAN:	3472592953946
----------------------	---------------

Package Level 2 Units:	500 piece
------------------------	-----------

Package Level 2 Width:	300 mm
------------------------	--------

Package Level 2 Depth / Length:	500 mm
---------------------------------	--------

Package Level 2 Height:	150 mm
-------------------------	--------

Package Level 3 Units:	24000 piece
------------------------	-------------

Product Packing Type:	Bag
-----------------------	-----

